



REDJACKET SERIES

Grizzly

60 HZ, ½ - 1 ½ HP, 4" SUBMERSIBLE PUMPS

Rugged and reliable,
the Red Jacket Grizzly submersible
pump is designed to exceed performance
requirements in the most demanding
applications.

FEATURES AND BENEFITS

- Engineered thermoplastic discharge head and base provides corrosion and impact resistance
- Pump casing constructed with a press and roll process for superior reliability
- 303 stainless steel pump casing, shaft, and coupling for durability in aggressive conditions
- Floating Stage hydraulic design minimizes internal leakage resulting in increased pump efficiency
- Powered by CentriPro motors featuring built-in lightning and thermal overload protection, a Kingsbury thrust bearing rated up to 1500 lbs, Copper Class F windings, and stainless construction



 **GOULDS**
WATER TECHNOLOGY
a xylem brand

WATER END LENGTHS AND WEIGHTS


Order Number	Required HP	Stages	Length (in.)	Weight (lbs.)
6G17	½	17	22.5	5
6G19	¾	19	25.2	7
6G24	1	24	29.7	8
8G12	½	12	17.6	4
8G16	¾	16	21.2	5
8G21	1	21	26.3	7
8G25	1½	25	29.9	12
12G8	½	8	14.2	4
12G9	½	9	15.1	5
12G12	¾	12	17.8	5
12G14	1	14	19.7	6
12G18	1½	18	24.0	7
20G5	½	5	11.4	3
20G6	¾	6	12.3	3
20G8	1	8	14.2	4
20G11	1½	11	16.9	5
25G7	1	7	14.9	4
25G10	1½	10	18.2	5

SPECIFICATIONS

Model	Flow Range GPM	HP Range	Best Eff. GPM	Discharge Connection	Min. Well Size	Rotation ^①
6G	1.2 – 8.5	½ – 1	5	1¼"	4"	CCW
8G	1.5 – 10	½ – 1½	7	1¼"	4"	CCW
12G	3 – 13	½ – 1½	10	1¼"	4"	CCW
20G	6 – 25	½ – 1½	18	1¼"	4"	CCW
25G	8 – 31	1 – 1½	22	1¼"	4"	CCW

① Rotation is counterclockwise when viewed from pump discharge end

PERFORMANCE AREA CURVE



Xylem Inc.
 2881 East Bayard Street Ext., Seneca Falls, NY 13148
 Phone: (866) 325-4210 • Fax: (888) 322-5877
goulds.com/red-jacket

Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license.
 Red Jacket Series is a trademark of Xylem Inc. or one of its subsidiaries.
 © 2021 Xylem Inc. GRIZZLYSALES February 2021