



Series “Core 4” control panels

Simplex and duplex, single and three phase control
for 3885 (WE), 3886 (WS), 3887 (WS BF/BHF), and 3888 (D3/D4)

Series “Core 4” control panels provide outstanding, automatic, liquid level control to help manage and maintain pump operation for a variety of effluent, sewage, and water transfer applications.



Features

- Rugged, NEMA 4X construction withstands even the most severe weather conditions and prevents corrosion
- Solid-state control board displays float status for ease of installation and trouble-shooting
- Hinged door with lockable stainless-steel latch for safe operation indoors and out
- Through-door mounted alarm test switch ensures proper operation of the alarm circuit without the need to open the panel
- Panel can be wired for a single power feed and control circuit, or the control circuit can be wired to a separate power supply to ensure alarm integrity in case of a tripped pump breaker
- Top-mounted, high intensity, flashing red light provides 360° visibility
- Auxiliary alarm contacts provided for remote alarm connection
- Field wiring diagram, panel schematic and installation instructions included
- Entire unit is UL and CUL listed



Applications

- Residential
- Sewage
- Effluent
- Water transfer

Product specifications

- Hand-off-automatic (H-O-A) pump selection switch(es)
- On-off control circuit switch
- Float switches:
 - Normally open (pump down) mechanical float switches with 20' cords
 - Simplex panels (three switches)
 - Duplex panels (four switches)
- Duplex panels include alternation
- NEMA 4X:
 - Flashing red alarm light
 - Fiberglass enclosure with gasketed, hinged door and stainless-steel hardware
 - Alarm horn (95db)
- Solid state printed circuit control board with float indicator lights
- Auxiliary alarm dry contact
- Elapsed time meter(s)
- Cycle counter(s)
- Single phase
 - Field adjustable for 115/208/230V, 60Hz
- Three phase
 - Field adjustable for 208/230/460/575 V, 60 Hz
 - 115V control circuit transformer
 - Adjustable motor overload protectors

Nomenclature

Character	1 & 2	3	4	5, 6, 7, 8
	C4 = Core Four	S = Simplex	1 = Single Phase	Amp Range
		D = Duplex	3 = Three Phase	0-20
				21-36
				0-20
				21-27
				28-36
				1.6-2.5
				2.5-4.0
				4.0-6.3
				6.3-10
				10-16
				16-20
				20-25
				22-32

Panel model information

Single phase panels		Three phase panels	
Order number	Amp range	Order number	Amp range
C4S10020	0-20	C4S31625	1.6-2.5
C4S12136	21-36	C4S32540	2.5-4.0
C4D10020	0-20	C4S34063	4.0-6.3
C4D12127	21-27	C4S36310	6.3-10
C4D12836	28-36	C4S31016	10-16
		C4S31620	16-20
		C4S32025	20-25
		C4S32232	22-32
		C4D31625	1.6-2.5
		C4D32540	2.5-4.0
		C4D34063	4.0-6.3
		C4D36310	6.3-10
		C4D31016	10-16
		C4D31620	16-20
		C4D32025	20-25
		C4D32232	22-32



Learn more about
Series Core 4
control panels



Xylem Inc.

www.xylem.com/goulds

This information is subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

©2025 Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are the property of their respective owners.

GWT-C4Pan-SS-120063 R2 6/2025

xylem
Let's Solve Water