

N5100 INDUSTRIAL AIR DRIVEN DIAPHRAGM PUMP

			Check Valve							
Model No.	MAX Flow GPM (LPM)	Diaphragm	Check Valve	Check Valve	Check Valve Spring	Liquid IN	Liquid OUT	Gas Inlet Fitting	Body Material	Compliance
			Body	Seal / O-Ring						
N5100020	2 (7.6)	FKM	FKM / Acetal	FKM	KM O-ring	3/8 HB Strt	3/8 HB Strt	1/4 HB Strt	Acetal	CE
N5100022	2 (7.6)	FKM	FKM / Acetal	FKM	KM O-ring	3/8 HB Strt	3/8 HB Strt	1/4 HB Strt	Acetal	CE
N5100040	2 (7.6)	EP/PP Blend	EP/PP / Acetal	EP	DM O-ring	3/8 HB Strt	3/8 HB Strt	1/4 HB Strt	Acetal	CE
N5100050	2 (7.6)	Geolast	Geolast/Acetal	Geolast	st O-ring	3/8 HB Strt	3/8 HB Strt	1/4 HB Strt	Acetal	CE
N5110040	2 (7.6)	EP/PP Blend	EP-PP Blend / PP	EP	DM O-ring	3/8 HB Strt	3/8 HB Strt	1/4 HB Strt	GF PP	CE