



This document provides technical information relating to this specific Flojet model. General information, references and further resource locations are also included. VersiJet industrial pumps are designed to be durable and long-lasting, capable of satisfying pumping needs for a wide variety of applications. Typical pump uses are liquid transfer, spraying, cooling, circulation, filtration and dispensing.

#### Features

- Heavy duty, coated motor
- Long life co-mold diaphragm
- Efficient, quiet operation
- Self-priming
- Runs dry without damage


#### Contents

|                   |                                                                     |
|-------------------|---------------------------------------------------------------------|
| Pump unit:        | VersiJet 115V 4GPM SW 60 PSI BP<br>VersiJet 115V 15LPM SW 4.1BAR BP |
| Port fittings:    | 2 X 3/4" (19mm) straight hosebarb                                   |
| Strainer:         | Not included                                                        |
| IOM:              | Included (PN 81000480)                                              |
| Carton type:      | Plain box                                                           |
| Master pack qty.: | 4                                                                   |

#### Dimensional drawing

Inches [mm]

Notes: Additional envelope space required to allow port clips to extend, wires to bend, port fittings and hoses, etc.



Specifications

General

|                          |                                                                                                                                          |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Part number:             | Q40FF-118S-2P                                                                                                                            |
| Aftermarket replacement: | Q40FF-118S-2P                                                                                                                            |
| Replaces:                | 04300042A / 04300043A                                                                                                                    |
| Application:             | Industrial fluid transfer & spray                                                                                                        |
| Design:                  | 4 chamber diaphragm<br>Quick connect ports<br>TENV permanent magnet motor<br>Noise dampening baseplate<br>Thermal motor protection (TCO) |

Materials (\*designates wetted path)

|                        |                             |
|------------------------|-----------------------------|
| Upper housing*:        | Glass-filled polypropylene  |
| Lower housing*:        | Cast aluminum               |
| Check valve retainer*: | Polypropylene               |
| Diaphragm*:            | Santoprene                  |
| Check valves*:         | EPDM                        |
| Switch diaphragm*:     | EPDM                        |
| Bypass diaphragm*:     | EPDM                        |
| PH seals*:             | EPDM                        |
| PH fasteners:          | Stainless steel             |
| Baseplate:             | Nylon with rubber feet      |
| Motor casing:          | Case aluminum; coated steel |

Hydraulic performance (at nominal voltage)

|                          |                            |
|--------------------------|----------------------------|
| Open flowrate:           | 4 GPM open flow (15 LPM)   |
| Pressure switch cut-off: | 60 PSI (4.1 BAR)           |
| Max operating pressure:  | 60 PSI (4.1 BAR)           |
| Max inlet pressure:      | 30 PSI (2.2 BAR)           |
| Internal bypass:         | Yes                        |
| Fluid temperature range: | 32°F - 140°F (0°C - 60°C)  |
| Self-priming capability: | Up to 8ft (2.4m) dry prime |
| Run-dry capable:         | Yes                        |

Electrical performance (at nominal voltage)

|                   |                                    |
|-------------------|------------------------------------|
| Nominal voltage:  | 115 VAC                            |
| Voltage range:    | 104 VAC – 126 VAC                  |
| Max current draw: | 1.3 Amps @ 60 PSI (4.1 BAR)        |
| Fuse size:        | Not applicable                     |
| Duty cycle:       | Intermittent (See heat-rise chart) |
| Leads:            | 14" (355mm), 18 AWG<br>(0.75mm^2)  |
| Wire connection:  | Stripped wire                      |


Compliance

|                    |              |
|--------------------|--------------|
| CE:                | No           |
| UR:                | Yes          |
| RCM:               | No           |
| UKCA:              | No           |
| WEEE:              | No           |
| Country of Origin: | Mexico       |
| HTS Code:          | 8413.50.0050 |

Other information


|                         |                                     |
|-------------------------|-------------------------------------|
| Other Information:      | Industrial                          |
| Ambient temp range:     | 32°F - 140°F (0°C - 60°C)           |
| IP rating:              | IPX6                                |
| Carton dimensions:      | 11.25x5.47x5.07"<br>(286x139x129mm) |
| Master pack dimensions: | 12x12x11.5" (305x305x292mm)         |
| Weight (pump only):     | 5.2 lbs (2.4 kg)                    |
| UPC code:               | 705474223619                        |

Flow curve



Representative curve of unit operated at nominal voltage. Performance will vary somewhat unit to unit. Switch cut-off represents the point on the flow curve at which the integrated pressure switch will turn off the pump. Flow rate at zero pressure represents Open Bucket..

Temperature rise




Tested @ elevated ambient temp of 140°F (60°C) @ max run pressure. Est. Casing Temp @ Trip Point may vary (+/-10°C). If there is a concern about the ability of the pump to run continuously for long periods of time, then in-application testing is highly recommended.

Pump service kits & spares

| Item                        | Description                                                           |
|-----------------------------|-----------------------------------------------------------------------|
| 1. Port clips               | 2 port clips per kit                                                  |
| 2. Check valve assembly     | Check valve housing with suction and discharge check valves installed |
| 3. Diaphragm/drive assembly | Wobble plate/diaphragm assembly                                       |
| 4. Baseplate/mounting feet  | Baseplate w/rubber mounting feet installed                            |

Exploded view



Available Flojet industrial options

In addition to the unit described in this datasheet Flojet also offers the following configurations (will vary somewhat by region and model type) and options:

- Voltages: 12, 24, & 36 VDC 115 & 230 VAC
- Flowrate range: 1 - 6 GPM (3.8 - 22.7 LPM)
- Switch setting range: 25 - 150 PSI (1.7 - 10.3 Bar)
- Pump configurations:
  - Switch; Bypass; Switch & Bypass; Switch, No Bypass; No Switch, No bypass
  - EP/PP and other blended diaphragm materials
  - EPDM, FKM, and other valve/seal materials
  - Some models available with transducers or vacuum switches
  - Various customer options dependent on volumes

Installation & operation

For guidance on proper installation and operation of this pump, as well as for any warnings or cautions involving use, please consult the appropriate IOM for the pump. Printed IOMs are supplied with the pumps and are also available online.

Resources & contact information

|           |                                    |                   |                                                                |
|-----------|------------------------------------|-------------------|----------------------------------------------------------------|
| IOM:      | On website; hard copies with pumps | Customer service: | Refer to contact info at our website                           |
| Warranty: | Information included in IOM        | Website:          | <a href="http://www.xylem.com/flojet">www.xylem.com/flojet</a> |

Note: Specifications provided for guidance only. We reserve the right to change specifications without prior notice.