



Flygt 2201 SH

60 Hz

CLASSIC DEWATERING PUMP WITH A HIGHER HEAD CAPABILITY

With the Flygt 2201SH, a tried-and-true dewatering pump reaches new heights. As rugged, dependable and high-performing as its siblings in the Flygt 2201 series, this new addition is purpose-designed to pump at ultra-high head up to 500 feet (140 meters).

The Flygt 2201SH is a two-stage hydraulic pump with double adjustable impellers. Resistant to abrasion and wear, it can also pump higher heads than most of our competitors with its dual-stage impellers.

The Flygt 2201 series of submersible pumps delivers high performance and reliability day after day, year after year. These pumps provide a versatile solution for construction and mining applications, and are ideal for jobs both large and small that require reliable, flexible dewatering. The 2201SH extends the series with a durable adaptation for pumping at ultra-high heads.

The signature Dura-Spin™ safeguards against wear. The unique closed impeller and the suction cover with Dura-Spin grooves work together, sweeping abrasive particles away from the impeller neck.

The two-stage design with its conical trim sleeve is based on proven hydraulics from Flygt. This fast and easy impeller-adjustment feature restores clearances to near-original condition, boosting pump performance. And sturdier-than-ever cable entry ensures safe, continuous operation.

Flygt 2201SH - Delivers more performance when the pressure's on.



FLYGT
a xylem brand

