


<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.:</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



## 2-11B

# Marlow Series e-530SL

### Centrifugal Pumps - Base Mounted

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

Stainless Steel Fitted

**FEATURES**

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

175 psi (12 bar) W.P.  
w/ 125# ANSI flange drilling


**TYPE OF SEAL**

- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note:** Equipped with NEOPRENE coupling



<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.:</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



## 2-11B

# Marlow Series e-530SL

### Centrifugal Pumps - Base Mounted

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

Stainless Steel Fitted

**FEATURES**

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

175 psi (12 bar) W.P.  
 w/ 125# ANSI flange drilling


**TYPE OF SEAL**

- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note:** Equipped with NEOPRENE coupling



<b>JOB:</b>  <b>UNIT TAG:</b> <b>ENGINEER:</b> <b>CONTRACTOR:</b>	<b>REPRESENTATIVE:</b>  <b>ORDER NO.:</b> <b>SUBMITTED BY:</b> <b>APPROVED BY:</b>	<b>DATE:</b> <b>DATE:</b> <b>DATE:</b>
---	--	--



## 2-11B

# Marlow Series e-530SL

### Centrifugal Pumps - Base Mounted

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**

Stainless Steel Fitted

**FEATURES**

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


**MAXIMUM WORKING PRESSURE**

175 psi (12 bar) W.P.  
 w/ 125# ANSI flange drilling

**TYPE OF SEAL**


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

**Note:** Equipped with NEOPRENE coupling



Marlow Series e-530SL 2-11B Centrifugal Pump Submittal

M-501.30



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	2"	7/8 (23)	6-1/4 (159)
Suction	3"	1-1/8 (29)	8 (203)

FLANGES ARE 125# ANSI - STANDARD  
250# ANSI - AVAILABLE

DIMENSIONS - Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HH	HL	HM MAX	HO	HP	Y	Z
<b>"S" FRAME</b>														
182T	16 (406)	42-1/4 (1073)	34 (864)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (410)	7/8 (22)	6-1/2 (165)	19-1/4 (489)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
184T	16 (406)	42-1/4 (1073)	34-3/4 (883)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (410)	7/8 (22)	6-1/2 (165)	19-1/4 (489)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
213T	16 (406)	42-1/4 (1073)	37-1/4 (946)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (410)	7/8 (22)	6-1/2 (165)	19-7/8 (505)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
215T	16 (406)	42-1/4 (1073)	38-3/4 (984)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (410)	7/8 (22)	6-1/2 (165)	19-7/8 (505)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
254T	16 (406)	42-1/4 (1073)	42-1/2 (1080)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (410)	7/8 (22)	6-1/2 (165)	20-7/8 (530)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
<b>"L" FRAME</b>														
286TS	16 (406)	46-1/2 (1181)	49 (1245)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/8 (105)	22 (559)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
324TS	16 (406)	51-3/4 (1314)	50-7/8 (1292)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/8 (105)	23-1/8 (587)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
326TS	16 (406)	51-3/4 (1314)	52-3/8 (1330)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/8 (105)	23-1/8 (587)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
364TS	24 (610)	56 (1422)	54-1/4 (1378)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	4-3/4 (121)	26-3/4 (679)	24-1/2 (622)	6 (152)	5-1/2 (140)	6-1/2 (165)
365TS	24 (610)	56 (1422)	54-7/8 (1394)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	4-3/4 (121)	26-3/4 (679)	24-1/2 (622)	6 (152)	5-1/2 (140)	6-1/2 (165)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub>	HH	HL	HM MAX	HO	HP	Y	Z
<b>"S" FRAME</b>														
182T	16 (406)	42-1/4 (1073)	37-5/8 (956)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (409)	7/8 (22)	6-1/2 (165)	19-1/4 (489)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
184T	16 (406)	42-1/4 (1073)	38-3/8 (975)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (409)	7/8 (22)	6-1/2 (165)	19-1/4 (489)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
213T	16 (406)	42-1/4 (1073)	40-7/8 (1038)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (409)	7/8 (22)	6-1/2 (165)	19-7/8 (505)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
215T	16 (406)	42-1/4 (1073)	42-3/8 (1076)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (409)	7/8 (22)	6-1/2 (165)	19-7/8 (505)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
254T	16 (406)	42-1/4 (1073)	46-1/8 (1171)	14 (356)	14 (356)	32-1/4 (819)	16-1/8 (409)	7/8 (22)	6-1/2 (165)	20-7/8 (530)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
<b>"L" FRAME</b>														
286TS	16 (406)	51-3/4 (1314)	51-3/8 (1305)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/8 (105)	22 (559)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
324TS	16 (406)	51-3/4 (1314)	53-3/8 (1356)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/8 (105)	23-1/8 (587)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
326TS	16 (406)	51-3/4 (1314)	54-7/8 (1394)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/8 (105)	23-1/8 (587)	22 (559)	5 (127)	5-1/2 (140)	6-1/2 (165)
364TS	24 (610)	56 (1422)	56-5/8 (1438)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	4-3/4 (121)	26-3/4 (679)	24-1/2 (622)	6 (152)	5-1/2 (140)	6-1/2 (165)
365TS	24 (610)	56 (1422)	57-3/8 (1457)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	4-3/4 (121)	26-3/4 (679)	24-1/2 (622)	6 (152)	5-1/2 (140)	6-1/2 (165)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.  
8200 N. Austin Avenue  
Morton Grove, IL 60053  
Phone: (847)966-3700  
Fax: (847)965-8379  
www.gouldswatertechnology.com



Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license.  
© 2016 Xylem Inc.