


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO.: SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	--	--



5-11B

Marlow Series e-530SL

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____	HEAD _____
HP _____	RPM _____
VOLTS _____	
CYCLE _____	PHASE _____
ENCLOSURE _____	
APPROX. WEIGHT _____	
SPECIALS _____	

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling


TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



5-11B

Marlow Series e-530SL

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW		HEAD	
HP		RPM	
VOLTS			
CYCLE		PHASE	
ENCLOSURE			
APPROX. WEIGHT			
SPECIALS			

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) W.P.
- w/ 125# ANSI flange drilling

TYPE OF SEAL

- ☐ Standard Seal (Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling





FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	5" (127)	1-3/8" (35)	10-3/4" (273)
Suction	6" (152)	1-7/16" (37)	12-1/8" (308)

MAXIMUM WORKING PRESSURE 250 PSI

FLANGES ARE 125# ANSI - STANDARD
250# ANSI - AVAILABLE

DIMENSIONS - Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"L" FRAME														
254T	16 (406)	46-1/2 (1181)	46-3/4 (1187)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-7/16 (113)	21-7/8 (556)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
256T	16 (406)	46-1/2 (1181)	48-1/2 (1232)	15 (381)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-7/16 (113)	21-7/8 (556)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
284T	16 (406)	51-3/4 (1314)	49-1/4 (1251)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	23 (584)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
286T	16 (406)	51-3/4 (1314)	50-3/4 (1289)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	23 (584)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
324T	16 (406)	51-3/4 (1314)	53 (1346)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	24-1/8 (613)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"L" FRAME														
254T	16 (406)	51-3/4 (1314)	49-1/8 (1248)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	21-7/8 (555)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
256T	16 (406)	51-3/4 (1314)	50-7/8 (1292)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	21-7/8 (555)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
284T	16 (406)	51-3/4 (1314)	51-5/8 (1311)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	23 (584)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
286T	16 (406)	51-3/4 (1314)	53-1/8 (1349)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	23 (584)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)
324T	16 (406)	51-3/4 (1314)	55-3/8 (1407)	15 (381)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-7/16 (113)	24-1/8 (613)	25-1/2 (648)	5 (127)	5-35/64 (141)	7-15/16 (202)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.gouldswatertechnology.com

xylem
Let's Solve Water