

Flygt 2450 HT

60 Hz

NEW ULTRA HIGH HEAD DEWATERING PUMP

Denomination

Product code	2450.400
Installation	Portable
Discharge connection	100 mm
Impeller characteristics	High Head Wear Resistant Impellers, Two-Stage Hydraulics

Process Data

Liquid temperature	40°C (104°F)
Depth of immersion	50 m (164 ft)
Liquid density	1,100 kg/m ³
Strainer hole dimension	10 x 10 mm
pH of pumped liquid	pH 6-13

Motor data

Frequency	60 Hz
Insulation Class	H (180°C [360°F])
Voltage Variation	max +/- 10% - intermittent running
Voltage imbalance	max 2% between phases max 30 – no of starts/hour
Rating 60 Hz	160 kW /215 HP – 3,570 rpm
Rated current (460V)	229 A
Starting current (460V)	2,385 A

Materials

Impellers	Hard-Iron™
Wear Parts	Hard-Iron™
Stator housing	Cast Iron
Strainer	Galvanized Steel; Stainless Steel
Shaft	Stainless steel
O-rings	Nitrile rubber
Top diffuser	Cast Iron
Inner Mechanical Seal	WCCR Tungsten Carbide
Outer Mechanical Seal	WCCR Tungsten Carbide; RSiC Sil-Carbide

Weight & dimensions

Installation	Vertical, Horizontal
Weight (excl. cable)	~1,350 kg
Height	1,512 mm
Width	710 mm



FLYGT

xylem

Flygt 2450 HT

60 Hz

PERFORMANCE CURVE

