


JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



4-9D

Marlow Series e-531SC

Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION


☒ Stainless Steel Fitted

MAXIMUM WORKING PRESSURE


☒ 175 psi (12 bar) W.P.
 with 125# ANSI flange drilling

TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction
w/ Flushed Packing
(Graphite Impregnated Teflon)



JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



4-9D

Marlow Series e-531SC

Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION


☒ Stainless Steel Fitted

MAXIMUM WORKING PRESSURE

☒ 175 psi (12 bar) W.P.
 with 125# ANSI flange drilling



TYPE OF SEAL

- ☐ Standard Seal (Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated Teflon)



Marlow Series e-531SC 4-9D Centrifugal Pump Submittal

M-502.24



PUMP DIMENSIONS - INCHES (MM)						
X		Y		Z		
8.00 (203)		5.00 (127)		7.00 (178)		

FLANGE DIMENSIONS - INCHES (MM)						
125# ANSI FLAT FACE	NOMINAL PIPE SIZE	O.D.	THICKNESS	BOLT CIRCLE DIAMETER	NO. OF BOLTS	SIZE OF BOLTS
DISCHARGE	4	9.00 (229)	1.00 (25)	7.50 (191)	8	0.63 (16)
SUCTION	5	10.00 (254)	1.00 (25)	8.50 (216)	8	0.75 (19)

DIMENSIONS - INCHES (mm)

STANDARD SEAL


MOTOR FRAME	A	AB	HB	CP MAX	D	HF	G	G1	H	HH	HA	F2	2E	2HE	HF2 MAX	B	F	O	HG	DD
213JM	11.00 (279)	10.75 (273)	12.00 (305)	26.25 (667)	5.25 (133)	10.75 (273)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	5.88 (149)	6.00 (152)	4.38 (111)	11.13 (283)	4.75 (121)	10.00 (254)
215JM	11.00 (279)	10.75 (273)	12.00 (305)	27.75 (705)	5.25 (133)	10.75 (273)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	5.88 (149)	6.00 (152)	4.38 (111)	11.13 (283)	4.75 (121)	10.00 (254)
254JM	11.00 (279)	10.75 (273)	15.50 (394)	31.75 (807)	6.25 (159)	14.25 (362)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	7.13 (181)	6.00 (152)	4.38 (111)	13.13 (333)	3.75 (95)	10.00 (254)
256JM	11.00 (279)	10.75 (273)	15.50 (394)	33.50 (851)	6.25 (159)	14.25 (362)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	7.13 (181)	6.00 (152)	4.38 (111)	13.13 (333)	3.75 (95)	10.00 (254)

DIMENSIONS - INCHES (mm)

STANDARD SEAL

MOTOR FRAME	A	AB	HB	CP MAX	D	HF	G	G1	H	HH	HA	F2	2E	2HE	HF2 MAX	B	F	O	HG	DD
213JP	11.00 (279)	10.75 (273)	12.00 (305)	30.13 (765)	5.25 (133)	10.75 (273)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	9.75 (248)	6.00 (152)	4.38 (111)	11.13 (283)	4.75 (121)	10.00 (254)
215JP	11.00 (279)	10.75 (273)	12.00 (305)	31.63 (803)	5.25 (133)	10.75 (273)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	9.75 (248)	6.00 (152)	4.38 (111)	11.13 (283)	4.75 (121)	10.00 (254)
254JP	11.00 (279)	10.75 (273)	15.50 (394)	34.63 (879)	6.25 (159)	14.25 (362)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	10.00 (254)	6.00 (152)	4.38 (111)	13.13 (333)	3.75 (95)	10.00 (254)
256JP	11.00 (279)	10.75 (273)	15.50 (394)	36.38 (924)	6.25 (159)	14.25 (362)	0.75 (19)	0.18 (9)	0.63 (16)	0.50 (13)	13.63 (346)	1.88 (48)	9.13 (232)	12.50 (318)	10.00 (254)	6.00 (152)	4.38 (111)	13.13 (333)	3.75 (95)	10.00 (254)

Dimensions are subject to change. Not to be used for construction purposes unless certified.



PUMP DIMENSIONS - INCHES (MM)						
Y			Z			
5.00 (127)			7.00 (178)			
FLANGE DIMENSIONS - INCHES (MM)						
125# ANSI FLAT FACE	NOMINAL PIPE SIZE	O.D.	THICKNESS	BOLT CIRCLE DIAMETER	NO. OF BOLTS	SIZE OF BOLTS
DISCHARGE	4	9.00 (229)	1.00 (25)	7.50 (191)	8	0.63 (16)
SUCTION	5	10.00 (254)	1.00 (25)	8.50 (216)	8	0.75 (19)

DIMENSIONS - INCHES (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF1	HF2	HH	HL	HM MAX	HO	HP
213JM	14.63 (371)	31.00 (787)	26.25 (667)	12.75 (324)	12.88 (327)	25.00 (635)	-	0.75 (19)	4.00 (102)	18.63 (473)	20.75 (527)	3.00 (76)
215JM	14.63 (371)	31.00 (787)	27.75 (705)	12.75 (324)	12.88 (327)	25.00 (635)	-	0.75 (19)	4.00 (102)	18.63 (473)	20.75 (527)	3.00 (76)
254JM	14.63 (371)	39.38 (1000)	31.75 (807)	12.75 (324)	12.88 (327)	33.38 (847)	-	0.75 (19)	4.00 (102)	19.63 (498)	20.75 (527)	3.00 (76)
256JM	16.00 (406)	46.50 (1181)	33.50 (851)	14.00 (356)	14.00 (356)	36.50 (927)	18.25 (464)	0.88 (22)	5.13 (130)	20.88 (530)	22.00 (559)	5.00 (127)

DIMENSIONS - INCHES (mm)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF1	HF2	HH	HL	HM MAX	HO	HP
213JP	14.63 (371)	31.00 (787)	30.13 (765)	12.75 (324)	12.88 (327)	25.00 (635)	-	0.75 (19)	5.13 (130)	19.88 (505)	20.75 (527)	3.00 (76)
215JP	14.63 (371)	34.63 (880)	31.63 (803)	12.75 (324)	12.88 (327)	28.63 (727)	-	0.75 (19)	5.13 (130)	19.88 (505)	20.75 (527)	3.00 (76)
254JP	14.63 (371)	39.38 (1000)	34.63 (879)	12.75 (324)	12.88 (327)	33.38 (847)	-	0.75 (19)	5.13 (130)	20.88 (530)	20.75 (527)	3.00 (76)
256JP	16.00 (406)	46.50 (1181)	36.38 (924)	14.00 (356)	14.00 (356)	36.50 (927)	18.25 (464)	0.88 (22)	5.13 (130)	20.88 (530)	22.00 (559)	5.00 (127)

Dimensions are subject to change. Not to be used for construction purposes unless certified.