



U-22XD Water Quality Analyzer

Water quality monitoring system for 10 different parameters



- Handheld water quality monitoring system with water quality analyzer
- Rugged, fully submersible sensor
- Detachable and non-detachable versions
- Dry cell batteries
- Built in datalogger
- Ideal for multi-parameter water quality measurements without having a permanent installation

Description

Global Water's U-22XD water quality monitoring system brings laboratory accuracy and the ease of push-button operation to water quality measurement in the field. Years of water quality analyzer technology development have resulted in the form of a 47-mm diameter water quality analyzer probe: a compact water quality monitoring system offering high pressure tolerance, long-term continuous measurement capability and highly accurate, simultaneous analysis of 10 parameters. The water quality analyzer can simultaneously measure: pH, temperature, dissolved oxygen, conductivity, salinity, turbidity, total dissolved solids (TDS), water depth, oxidation reduction potential (ORP), and seawater specific gravity. Featuring a powerful water quality analyzer and state-of-the-art functions, the water quality analyzer makes it easy to get highly reliable water quality data simply and quickly just by submersing the sensor in the water. The water quality monitoring system is flexible enough to use for checking the quality of a broad range of water samples, from factory effluent to urban drainage, river water, lake and marsh water, aquatic culture tanks, agricultural water supplies, and seawater. The main unit is water resistant, so it can be used safely even in the rain.

Specifications

Range:

PH- 0-14 with 0.01 pH resolution and ± 0.1 pH accuracy
DO- 0-20 mg/L with 0.01 resolution and ± 0.2 mg/L accuracy
Conductivity-0-10 S/m with 0.1% FS res. and $\pm 3\%$ accuracy
Salinity- 0-4% with 0.01% resolution and $\pm 0.3\%$ accuracy
Temp- 0-55C with 0.01° C resolution and $\pm 1.0^\circ$ C accuracy
ORP- ± 1999 mV with 1mV resolution and ± 15 mV accuracy
Turbidity- 0-800 NTU with 0.1 NTU res. $\pm 5\%$ accuracy
Seawater Specific Gravity- 0-50 σ t with 0.1 σ t res. and $\pm 5\sigma$ t accuracy
TDS- 0-100 g/L with 0.1% resolution and ± 5 g/L accuracy
Water Depth- 0-100 m with 0.1 m res. and $\pm 5\%$ accuracy

Visit www.globalw.com for more specifications

Options and Accessories

U-22XD Water Quality Analyzer

Fixed 2m cable and able to go to depths of 60 meters

W-22XD Water Quality Analyzer

Detachable 2m cable and able to go to depths of 100 meters

Additional cable lengths available for U-22XD and W-22XD, please see our website, www.globalw.com.

U/W-22XD Flow Cell

In the U.S. call toll free
at 1-800-876-1172
International: 1-979-690-5560
Fax: 1-979-690-0440
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670



Global Water
a xylem brand

Contact
Global Water
for all your
instrumentation
needs:

Water Level

Water Flow

Water Samplers

Water Quality

Weather

Remote Monitoring

Control