


<b>JOB:</b>   <b>UNIT TAG:</b> <b>ENGINEER:</b> <b>CONTRACTOR:</b>	<b>REPRESENTATIVE:</b>   <b>ORDER NO.:</b> <b>SUBMITTED BY:</b> <b>APPROVED BY:</b>	<b>DATE:</b> <b>DATE:</b> <b>DATE:</b>
---	--	--



# 1.25-9C

## Marlow Series e-530SC

### Close-Coupled Centrifugal Pumps

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**


STAINLESS STEEL FITTED

**MAXIMUM WORKING PRESSURE**


175 psi (12 bar) W.P.

**TYPE OF SEAL**

- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated Teflon)



<b>JOB:</b>   <b>UNIT TAG:</b> <b>ENGINEER:</b> <b>CONTRACTOR:</b>	<b>REPRESENTATIVE:</b>   <b>ORDER NO.:</b> <b>SUBMITTED BY:</b> <b>APPROVED BY:</b>	<b>DATE:</b> <b>DATE:</b> <b>DATE:</b>
---	--	--



# 1.25-9C

## Marlow Series e-530SC

### Close-Coupled Centrifugal Pumps

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**


STAINLESS STEEL FITTED

**MAXIMUM WORKING PRESSURE**


175 psi (12 bar) W.P.

**TYPE OF SEAL**

- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated Teflon)



<b>JOB:</b>   <b>UNIT TAG:</b> <b>ENGINEER:</b> <b>CONTRACTOR:</b>	<b>REPRESENTATIVE:</b>   <b>ORDER NO.:</b> <b>SUBMITTED BY:</b> <b>APPROVED BY:</b>	<b>DATE:</b> <b>DATE:</b> <b>DATE:</b>
---	--	--



# 1.25-9C

## Marlow Series e-530SC

### Close-Coupled Centrifugal Pumps

**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**MATERIALS OF CONSTRUCTION**


STAINLESS STEEL FITTED

**MAXIMUM WORKING PRESSURE**

175 psi (12 bar) W.P.


**TYPE OF SEAL**

- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated Teflon)



**Marlow Series e-530SC 1.25-9C Centrifugal Pump Submittal**

**M-500.14**



SIZE OF PUMP AND DISCHARGE	SUCTION	PUMP DIMENSIONS IN INCHES (MM)			
		DD	X	Y	Z
1.25-9C(NPT)	1.5 NPT	6.125 (155)	8 (204)	3.25 (83)	5.5 (140)

**DIMENSIONS - Inches (mm)**

**STANDARD SEAL**

MOTOR FRAME	A (Max)	AB (Max)	B (Max)	CP (Max)	D	2E	F	H	L	O (Max)
145JM	7 (178)	7 (178)	6 (152)	19 (483)	3.5 (89)	5.5 (140)	5 (127)	0.344 (9)	10.75 (273)	7.25 (184)
182JM	9 (229)	8.5 (216)	6.5 (165)	21.875 (556)	4.5 (114)	7.5 (190)	4.5 (114)	0.406 (10)	11.5 (292)	9.375 (238)
184JM	9 (229)	8.5 (216)	7.5 (190)	21.875 (556)	4.5 (114)	7.5 (190)	5.5 (140)	0.406 (10)	11.5 (292)	9.375 (238)
213JM	10.5 (267)	10.75 (273)	7.5 (190)	24.125 (613)	5.25 (133)	8.5 (216)	5.5 (140)	0.406 (10)	12.375 (314)	11.125 (283)
215JM	10.5 (267)	10.75 (273)	9 (229)	25.625 (651)	5.25 (133)	8.5 (216)	7 (178)	0.406 (10)	12.375 (314)	11.125 (283)
254JM	12.5 (318)	10.75 (273)	10.75 (273)	29.5 (750)	6.25 (159)	10 (254)	8.25 (210)	0.531 (13)	13.875 (353)	13.125 (333)
256JM	12.5 (318)	10.75 (273)	12.5 (318)	31.25 (794)	6.25 (159)	10 (254)	10 (254)	0.531 (13)	13.875 (353)	13.125 (333)
284JM	14 (356)	12.625 (321)	12.5 (318)	30.75 (781)	7 (178)	11 (279)	9.5 (241)	0.531 (13)	13.875 (353)	15 (381)
286JM	14 (356)	12.625 (321)	14 (356)	32.25 (819)	7 (178)	11 (279)	11 (279)	0.531 (13)	13.875 (353)	15 (381)

**STUFFING BOX**

MOTOR FRAME	A (Max)	AB (Max)	B (Max)	CP (Max)	D	2E	F	H	L	O (Max)
145JP	7 (178)	7 (178)	6 (152)	22.125 (562)	3.5 (89)	5.5 (140)	5 (127)	0.344 (9)	13.875 (352)	7.25 (184)
182JP	9 (229)	8.5 (216)	6.5 (165)	25 (635)	4.5 (114)	7.5 (190)	4.5 (114)	0.406 (10)	14.625 (371)	9.375 (238)
184JP	9 (229)	8.5 (216)	7.5 (190)	25 (635)	4.5 (114)	7.5 (190)	5.5 (140)	0.406 (10)	14.625 (371)	9.375 (238)
213JP	10.5 (267)	10.75 (273)	7.5 (190)	28 (711)	5.25 (133)	8.5 (216)	5.5 (140)	0.406 (10)	16.25 (413)	11.125 (283)
215JP	10.5 (267)	10.75 (273)	9 (229)	29.5 (749)	5.25 (133)	8.5 (216)	7 (178)	0.406 (10)	16.25 (413)	11.125 (283)
254JP	12.5 (318)	10.75 (273)	10.75 (273)	32.375 (822)	6.25 (159)	10 (254)	8.25 (210)	0.531 (13)	16.75 (425)	13.125 (333)
256JP	12.5 (318)	10.75 (273)	12.5 (318)	34.125 (867)	6.25 (159)	10 (254)	10 (254)	0.531 (13)	16.75 (425)	13.125 (333)
284JP	14 (356)	12.625 (321)	12.5 (318)	33.625 (854)	7 (178)	11 (279)	9.5 (241)	0.531 (13)	16.75 (425)	15 (381)
286JP	14 (356)	12.625 (321)	14 (356)	35.125 (892)	7 (178)	11 (279)	11 (279)	0.531 (13)	16.75 (425)	15 (381)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.  
 8200 N. Austin Avenue  
 Morton Grove, IL 60053  
 Phone: (847)966-3700  
 Fax: (847)965-8379  
 www.gouldswatertechnology.com

