

JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



3-13SC

Marlow Series 530

Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION


☐ BRONZE FITTED

MAXIMUM WORKING PRESSURE


☐ 175 psi (12 bar) W.P.
with 125# ANSI flange drilling

TYPE OF SEAL

- ☐ 1531 Standard Seal
(Buna-Carbon/Ceramic)
- ☐ 1531 -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ 1531 -S Stuffing Box construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ 1531 -D Stuffing Box construction w/ Flushed
Double Mechanical Seal
(EPR-Carbon/Ceramic)
Requires external water source
- ☐ 1531 -PF Stuffing Box Construction
w/ Flushed Packing
(Graphite Impregnated Teflon)



JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



3-13SC

Marlow Series 530

Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION


☐ BRONZE FITTED



MAXIMUM WORKING PRESSURE

☐ 175 psi (12 bar) W.P.
 with 125# ANSI flange drilling

TYPE OF SEAL

- ☐ 1531 Standard Seal
(Buna-Carbon/Ceramic)
- ☐ 1531 -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ 1531 -S Stuffing Box construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ 1531 -D Stuffing Box construction w/ Flushed
Double Mechanical Seal
(EPR-Carbon/Ceramic)
Requires external water source
- ☐ 1531 -PF Stuffing Box Construction
w/ Flushed Packing
(Graphite Impregnated Teflon)





SIZE OF PUMP AND DISCHARGE	SUCTION	PUMP DIMENSIONS IN INCHES (MM)			
		DD	X	Y	Z
3-13SC	4	10 (254)	9.50 (241)	5.63 (143)	8 (203)

125# ANSI FLANGE DIMENSIONS - INCHES (MM)

PIPE SIZE OF FLANGE	O.D. OF FLANGE	DIA. OF BOLT CIRCLE	NO. OF BOLTS	SIZE OF BOLTS
3	8 (203)	6 (152)	4	5/8 (16)
4	9-1/2 (241)	7-1/2 (191)	8	5/8 (16)

DIMENSIONS – Inches (mm)

STANDARD SEAL

MOTOR FRAME	A	AB	HB	CP	D	HF	G	G1	H	HH	HA	F2	2E	2HE	HF2	B	F	O	HG
254JP	16 (406)	8 (203)	15.5 (394)	30.06 (763)	6.25 (159)	14.25 (362)	0.88 (22)	0.19 (5)	0.62 (16)	0.5 (13)	13.62 (346)	2.12 (54)	14 (356)	12.5 (317)	6.56 (167)	7 (178)	5 (127)	10.88 (276)	3.75 (95)
256JP	16 (406)	8.94 (227)	15.5 (394)	31.94 (811)	6.25 (159)	14.25 (362)	0.88 (22)	0.19 (5)	0.62 (16)	0.5 (13)	13.62 (346)	2.12 (54)	14 (356)	12.5 (317)	8.25 (209)	7 (178)	5 (127)	12.94 (329)	3.75 (95)
284JP	16 (406)	11.5 (292)	17 (432)	32.13 (816)	7 (178)	15.5 (394)	0.88 (22)	0.25 (6)	0.62 (16)	0.62 (16)	14 (356)	2.12 (54)	14 (356)	12.5 (317)	6.63 (168)	7 (178)	5 (127)	13.88 (352)	3 (76)
286JP	16 (406)	11.5 (292)	17 (432)	33.63 (854)	7 (178)	15.5 (394)	0.88 (22)	0.25 (6)	0.62 (16)	0.62 (16)	14 (356)	2.12 (54)	14 (356)	12.5 (317)	8.13 (206)	7 (178)	5 (127)	13.88 (352)	3 (76)
324JP	16 (406)	14.62 (371)	18 (457)	34.06 (865)	8 (203)	16.5 (419)	0.88 (22)	0.25 (6)	0.62 (16)	0.62 (16)	15.75 (400)	2.12 (54)	14 (356)	12.5 (317)	7.13 (181)	7 (178)	5 (127)	15.94 (405)	2 (51)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.gouldswatertechnology.com

xylem
Let's Solve Water

Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license.
© 2013 Xylem Inc.