


JOB: UNIT TAG: ENGINEER: CONTRACTOR:		REPRESENTATIVE: ORDER NO.: SUBMITTED BY: APPROVED BY:		DATE: DATE: DATE:	
---	--	--	--	--	--



4-9D

Marlow Series e-530SL

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____	HEAD _____		
HP _____	RPM _____		
VOLTS _____			
CYCLE _____	PHASE _____		
ENCLOSURE _____			
APPROX. WEIGHT _____			
SPECIALS _____			

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling


TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO.: SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	--	--



4-9D

Marlow Series e-530SL

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling


TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



JOB:		REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	



4-9D Marlow Series e-530SL Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL

- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling





DIMENSIONS – Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
213T	14-5/8 (371)	34-5/8 (879)	37-3/4 (959)	12-3/4 (324)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	4 (102)	18-5/8 (473)	20-3/4 (527)	3 (76)	5 (127)	7 (178)
215T	14-5/8 (371)	34-5/8 (879)	39-1/4 (997)	12-3/4 (324)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	4 (102)	18-5/8 (473)	20-3/4 (527)	3 (76)	5 (127)	7 (178)
254T	14-5/8 (371)	39-3/8 (1000)	43 (1092)	12-3/4 (324)	12-7/8 (327)	33-3/8 (848)	-	3/4 (19)	4 (102)	19-5/8 (498)	20-3/4 (527)	3 (76)	5 (127)	7 (178)
"L" FRAME														
256T	16 (406)	46-1/2 (1181)	49-1/8 (1248)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	20-7/8 (530)	22 (559)	5 (127)	5 (127)	7 (178)
284TS	16 (406)	46-1/2 (1181)	48-1/2 (1232)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	22 (559)	22 (559)	5 (127)	5 (127)	7 (178)
286TS	16 (406)	46-1/2 (1181)	50 (1270)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	22 (559)	22 (559)	5 (127)	5 (127)	7 (178)
324TS	16 (406)	51-3/4 (1314)	51-7/8 (1318)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	23-1/8 (587)	22 (559)	5 (127)	5 (127)	7 (178)
326TS	16 (406)	51-3/4 (1314)	53-5/8 (1362)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	23-1/8 (587)	22 (559)	5 (127)	5 (127)	7 (178)
364TS	24 (610)	56 (1422)	55-1/4 (1403)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	26-3/4 (679)	24-1/2 (622)	6 (152)	5 (127)	7 (178)
365TS	24 (610)	56 (1422)	55-7/8 (1419)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	26-3/4 (679)	24-1/2 (622)	6 (152)	5 (127)	7 (178)
404TS	24 (610)	56 (1422)	58-1/8 (1476)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	28-3/8 (721)	24-1/2 (622)	6 (152)	5 (127)	7 (178)
405TS	24 (610)	56 (1422)	58-7/8 (1496)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	30 (762)	24-1/2 (622)	6 (152)	5 (127)	7 (178)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"L" FRAME														
213T	16 (406)	46-1/2 (1181)	44-1/2 (1130)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	19-7/8 (505)	22 (559)	5 (127)	5 (127)	7 (178)
215T	16 (406)	46-1/2 (1181)	46 (1168)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	19-7/8 (505)	22 (559)	5 (127)	5 (127)	7 (178)
254T	16 (406)	51-3/4 (1314)	49-3/4 (1264)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	20-7/8 (530)	22 (559)	5 (127)	5 (127)	7 (178)
256T	16 (406)	51-3/4 (1314)	51-1/2 (1308)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	20-7/8 (530)	22 (559)	5 (127)	5 (127)	7 (178)

Dimensions are subject to change. Not to be used for construction purposes unless certified.
Box type pumps should not be operated at 3500 RPM.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.gouldswatertechnology.com

xylem
Let's Solve Water