



TECHNICAL BROCHURE

BCPCWK21 R6

CWK21/22/23

UNASSEMBLED ROLL TOP POLYETHYLENE BASIN KITS



FEATURES

Structural foam cover is strong and corrosion resistant.

Vent grommets for both 2" and 3" vent provided on A8SF18, 2" only on A8ST18. Adds system flexibility and reduces inventory.

Rubber grommets for positive seal and easy installation.

Vent, discharge, inlet and cord holes all pre-drilled.

Torque stop insert to stabilize the pump.

Swing type 2" check valve:

- A9-2PH rubber sleeve type
- A9-2P compression type

Schedule 40, 2" PVC discharge pipe with 1/8" bleed hole is factory installed.

APPLICATIONS

Specially designed for the following uses:

- Homes, rural water districts, parks and dewatering
- Sewage lift station
- Anywhere waste or drainage must be disposed of quickly, quietly and efficiently
- Waste drainage in new additions below sewer line.

SPECIFICATIONS

Basin:

- Roll top polyethylene
- Usable capacity: 14 gallons
- Dimensions: 18" w x 30" h
- Inlet: 4" inlet grommet
- Shipping weight: 33 lbs.

18" X 30" ROLL TOP POLY BASIN WITH STRUCTURAL FOAM OR STEEL COVER

Kit Order Number		Basin	Cover	Check Valve	Discharge Pipe	Torque Stop Insert
CWK21	Includes	Roll Top 18" dia. x 30" deep polyethylene basin with 4" pipe grommet inlet	18" structural foam cover with bolts, seal tape, cord grommet, and (2) 2" and (1) 3" vent and discharge grommets	2" rubber sleeve type model A9-2PH	Sch 40 PVC 2" dia. x 30" long discharge pipe	Basin torque stop insert
CWK22				2" compression type model A9-2P		
CWK23			18" epoxy coated steel cover with (2) 2" vent and discharge grommets	2" rubber sleeve type model A9-2PH		

BASIN KIT COMPONENTS

- Roll Top Polyethylene Basin 18" x 30".
- Structural Foam 18" Diameter Cover Assembly (includes bolts, seal tape, cord grommet and (1) 3" and (2) 2" grommets).

OR

- Steel 18" Diameter Cover with Epoxy Coating (includes bolts, seal tape, cord grommet and (2) 2" grommets).
- Swing Style Check Valve (2 choices)
 - 2" Compression Type
 - 2" Full Flow Rubber Sleeve Style
- Sch 40 PVC Discharge Pipe 2" D x 30" L.
- Roll Top Basin 18" Torque Stop Insert.
- Basin Inlet Grommet.
- Vent and Discharge Grommets*
 - (to purchase separately from cover assembly).
 - 2" (pipe) x 4" (cover hole) Grommet
 - 3" (pipe) x 4" (cover hole) Grommet (use only on SF Cover)

Replacement Part Order Number*

A7PE1830

A8SF18

A8ST18

A9-2P

A9-2PH

ADP2030


ATS18

A8-4U

*A8-24U

*A8-3U

* These order numbers should only be used to order replacement parts as it will be much less expensive to order the "kit" versus all components.



Xylem |'zīləm|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating advanced technology solutions to the world's water challenges. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. Our products and services move, treat, analyze, monitor and return water to the environment, in public utility, industrial, residential and commercial building services settings. Xylem also provides a leading portfolio of smart metering, network technologies and advanced analytics solutions for water, electric and gas utilities. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise with a strong focus on developing comprehensive, sustainable solutions.

For more information on how Xylem can help you, go to www.xylem.com



Xylem, Inc.
2881 East Bayard Street Ext., Suite A
Seneca Falls, NY 13148
Phone: (866) 325-4210
Fax: (888) 322-5877
www.xylem.com/goulds

Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.
© 2024 Xylem, Inc. BCPCWK21 R6 January 2024