



Guide and disconnect systems less rails

1¼" through 4" connections

Features


- Ductile iron construction
- Powder coated for corrosion resistance
- Compact design for greater space availability in the basin
- Designed for simple installation and removal on most pumps
- Innovative design allows for pump service without the need to disconnect plumbing or physically enter the basin
- Units include a SS chain kit – see descriptions
- Base units accept different size guide pipes (not supplied)
- Optional non-sparking bronze guide plate available for 3" and 4" flanged discharge models with HB suffix
- Upper guide bracket included in all packages
- Intermediate guide brackets available as an option


Conery base elbow rail system

Goulds order #	Connections	Description	Usable rail sizes	Weight (lbs.)	Use with	Maximum pump weight lbs (kgs)
CBE1220	1¼" x 2"	Kit includes: • (1) Ductile iron base elbow • (1) Ductile iron pull-out • (1) SS Pump adapter flange and mounting hardware • (1) SS Lower guide plate bracket and mounting hardware (Attached) • (2) BUNA-N O-rings • (1) SS Upper guide rail bracket • (1) SS 3/16" Lifting chain (7') • (1) SS 3/16" Lifting chain (3') • (3) SS ¼" SPA shackles • (1) SS ¼" Quick link • (1) SS Lifting eyebolt	¾", 1"	51 (23.1)	Grinder or effluent pumps with 1¼" discharge	200 (91.7)
CBE1520	1½" x 2"		¾", 1"	51 (23.1)	Sump and effluent pumps with 1½" discharge and stainless steel sewage pumps with 1½" discharge for 1⅜" solids	200 (91.7)
CBE2020	2" x 2"		¾", 1"	55 (25)	Sewage or effluent pumps with 2" discharge	200 (91.7)
CBE3030	3" x 3"		¾", 1", 1¼"	76 (34.4)	2" Solids handling sewage pumps and 3" NPT threaded vertical discharge (pumps equipped with A1-3, 3" flange)	400 (181.4)
CBE2020CP	2" x 2"		¾", 1"	76 (34.4)	2" Solids handling sewage pumps and 2" NPT threaded vertical discharge	200 (91.7)
CBE3030H	3" x 3"		¾", 1", 1¼"	66 (30)	2½" Solids handling pumps with 3" 125# ANSI flanged discharge	400 (181.4)
CBE3030HB	3" Flange x 3" NPT non-sparking		¾", 1", 1¼"	68 (31)	2½" Solids handling pumps with 3" 125# ANSI flanged discharge	400 (181.4)
CBE4040H	4" Flange		2"	157 (71.2)	3" Solids handling pumps with 4" 125# ANSI flanged discharge	2,000 (907.2)
CBE4040HB	4" Flange non-sparking		2"	163 (74)	3" Solids handling pumps with 4" 125# ANSI flanged discharge	2,000 (907.2)

* Note: 4" size do not include hardware

Conery base elbow rail system optional components

Goulds order #	Vendor part #	Pictures	Description
CBR075	IGB075		SS Intermediate guide bracket – use with ¾" pipe
CBR100	IGB100		SS Intermediate guide bracket – use with 1" pipe
CBR125	IGB0125		SS Intermediate guide bracket – use with 1¼" pipe
CPA12	PAF125		SS Pump adapter – for pumps with 1¼" NPT discharge
CPA20	PAF200		SS Pump adapter – for pumps with 2" NPT discharge
CUGBS	UGB-STNLS		SS Upper guide rail bracket: For use with ¾", 1" and 1¼" Guide Rails (stainless steel recommended)
UGB-0200	UGB-0200		SS Upper guide rail bracket: For use with 2" guiderails (stainless steel recommended)



Shackle



Quick link

1 1/4" Lift out dimensions CBE1220

Materials of construction:

Pump adapter: 304 SST

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron



Lower guide bracket: 304 SST

All fasteners are 304 series SST

Usable guide rail sizes: 3/4", 1"

Maximum weight allowance: 200 lbs (91.7 kgs)

Note: All dimensions are in inches



1½" Lift out dimensions CBE1520

Materials of construction:

Pump adapter: 304 SST

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron



Lower guide bracket: 304 SST

All fasteners are 304 series SST

Usable rail sizes: ¾" and 1"

Maximum weight allowance: 200 lbs (91.7 kgs)

Note: All dimensions are in inches



2" Lift out dimensions CBE2020

Materials of construction:

Pump adapter: 304 SST

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron




Lower guide bracket: 304 SST

All fasteners are 304 series SST

Usable rail sizes: $\frac{3}{4}$ " and 1"

Maximum weight allowance: 200 lbs (91.7 kgs)

Note: All dimensions are in inches



2" Lift out dimensions CBE2020CP

Materials of construction:

Pump adapter: 304 SST

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron




Lower guide bracket: 304 SST

All fasteners are 304 series SST

Usable rail sizes: $\frac{3}{4}$ " and 1"

Maximum weight allowance: 200 lbs (91.7 kgs)

Note: All dimensions are in inches



3" Lift out dimensions CBE3030

Materials of construction:

Pump adapter: 304 SST

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron

Lower guide bracket: 304 SST

All fasteners are 304 series SST



Usable guide rail sizes: $\frac{3}{4}$ ", 1", $1\frac{1}{4}$ "

Spherical solids size: 3" diameter

Maximum weight allowance: 400 lbs (181.4 kgs)

Note: All dimensions are in inches

Mounting dimensions



CBE3030H

Materials of construction:

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron

Lower guide bracket: 304 SST

All fasteners are 304 series SST





Usable guide rail sizes: $\frac{3}{4}$ ", 1", $1\frac{1}{4}$ "

Spherical solids size: 3" diameter

Maximum weight allowance: 400 lbs (181.4 kgs)

Note: All dimensions are in inches

Mounting dimensions



CBE3030HB

Materials of construction:

Base elbow: Cast ductile iron

Lift-out flange: Cast brass

Lower guide bracket: Cast brass

All fasteners are 304 series SST





Usable guide rail sizes: $\frac{3}{4}$ ", 1", $1\frac{1}{4}$ "

Spherical solids size: 3" diameter

Maximum weight allowance: 400 lbs (181.4 kgs)

Note: All dimensions are in inches

Mounting dimensions



4" Lift Out Dimensions CBE4040

Materials of construction:

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron with SST sealing ring

Lower guide bracket: Cast ductile iron

All fasteners are 304 series SST





Usable guide rail sizes: 2"

Spherical solids size: 4" diameter

Maximum weight allowance: 2000 lbs (907.2 kgs)

Note: All dimensions are in inches

Mounting dimensions



4" Lift out dimensions CBE4040HB

Materials of construction:

Base elbow: Cast ductile iron

Lift-out flange: Cast ductile iron with bronze sealing ring

Lower guide bracket: Bronze

All fasteners are 304 series SST





Usable guide rail sizes: 2"

Spherical solids size: 4" diameter



Maximum weight allowance: 2000 lbs (907.2 kgs)

Note: All dimensions are in inches

Mounting dimensions





Intermediate guide bracket 1" rails




Note: Surface of part must be free of porosity.
Part must be free of distortion due to casting process.

Intermediate guide bracket 1 1/4" rails



Note: Surface of part must be free of porosity.
Part must be free of distortion due to casting process.

Intermediate guide bracket 2" rails



Installation for 2" NPT discharge pumps




Figure 1




Figure 2




Figure 3

Figure 1 shows all the parts included with the pull-out flange assembly. This is the removable portion of the base elbow rail system assembly, and it is this assembly that will attach to the discharge of the pump (see figure 2). The threaded pump adapter flange will thread into the pump discharge as shown. The pump adapter flange is secured by tightening the two (2) long cap screws provided. This allows the pump to be oriented as

necessary before lowering into the basin or collection tank. After attaching the pull out flange assembly to the pump, the lifting chain or cable assembly should be attached (see figure 3). This should be adequately sized to handle the weight of the pump and the pull out flange assembly as well as be long enough to allow for easy access for pulling the pump.

Installation for 3" and 4" ANSI flange pumps





Figure 2

NOTE: Pictures are 3" flange. 4" flange (8 bolt holes) assembly is the same.

Figure 1 shows all the parts included with the pull-out flange assembly. This is the removable portion of the base elbow rail system assembly, and it is this assembly that will attach to the discharge of the pump (see figure 2). The pull out flange will bolt to the pump discharge as shown. A gasket flange should be placed between

the pull out flange and the pump discharge flange. After attaching the pull out flange assembly to the pump discharge flange, the lifting chain or cable assembly should be attached. This should be adequately sized to handle the weight of the pump and the pull out flange assembly as well as be long enough to allow for easy access for pulling the pump.

Notes

Notes

Xylem Inc.
2881 East Bayard Street Ext.,
Suite A
Seneca Falls, NY 13148

Phone: (866) 325-4210

Fax: (888) 322-5877

www.xylem.com/goulds

This information is subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2025 Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Xylem Inc. or one of its subsidiaries is under license. All other trademarks or registered trademarks are the property of their respective owners.

BCPGDS R8 11/2025

xylem
Let's Solve Water