


|                                                                                   |                                                                                                   |                                              |
|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>JOB:</b><br><br><br><b>UNIT TAG:</b><br><b>ENGINEER:</b><br><b>CONTRACTOR:</b> | <b>REPRESENTATIVE:</b><br><br><br><b>ORDER NO.</b><br><b>SUBMITTED BY:</b><br><b>APPROVED BY:</b> | <b>DATE:</b><br><b>DATE:</b><br><b>DATE:</b> |
|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|----------------------------------------------|



## 3x3x7C Marlow Series e-580 In-Line Mounted Centrifugal Pumps

### SPECIFICATIONS

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ INPUT PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

### MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

### MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) with 125# ANSI flange drilling  
☐ 250 psi (17 bar) with 250# ANSI flange drilling (requires e-580-S)

### MOUNTING


- ☐ In-Line Piping    ☐ Flange Supports

### TYPE OF SEAL

- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)  
☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)  
☐ -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated PTFE)



|                                                                                   |                                                                                                   |                                              |
|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|----------------------------------------------|
| <b>JOB:</b><br><br><br><b>UNIT TAG:</b><br><b>ENGINEER:</b><br><b>CONTRACTOR:</b> | <b>REPRESENTATIVE:</b><br><br><br><b>ORDER NO.</b><br><b>SUBMITTED BY:</b><br><b>APPROVED BY:</b> | <b>DATE:</b><br><b>DATE:</b><br><b>DATE:</b> |
|-----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|----------------------------------------------|



## 3x3x7C

# Marlow Series e-580

### In-Line Mounted Centrifugal Pumps

#### SPECIFICATIONS

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ INPUT \_\_\_\_\_  
 PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

#### MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

#### MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) with 125# ANSI flange drilling  
☐ 250 psi (17 bar) with 250# ANSI flange drilling (requires e-580-S)

#### MOUNTING


- ☐ In-Line Piping    ☐ Flange Supports

#### TYPE OF SEAL

- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)  
☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)  
☐ -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated PTFE)



|             |               |                 |  |
|-------------|---------------|-----------------|--|
| JOB:        |               | REPRESENTATIVE: |  |
| UNIT TAG:   | ORDER NO.     | DATE:           |  |
| ENGINEER:   | SUBMITTED BY: | DATE:           |  |
| CONTRACTOR: | APPROVED BY:  | DATE:           |  |



## 3x3x7C Marlow Series e-580 In-Line Mounted Centrifugal Pumps

### SPECIFICATIONS

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ INPUT PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

### MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

### MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) with 125# ANSI flange drilling  
☐ 250 psi (17 bar) with 250# ANSI flange drilling (requires e-580-S)


### MOUNTING

- ☐ In-Line Piping ☐ Flange Supports

### TYPE OF SEAL

- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)  
☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)  
☐ -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated PTFE)





# 3x3x7C

## Marlow Series e-580

### Centrifugal Pump Submittal - In-Line Piping

DIMENSIONS - Inches (mm)

STANDARD SEAL

| MOTOR FRAME | A             | B              | C             | D             | E (max)        | F             | G             | H (max)        | 125# ANSI     |   |              | 250# ANSI     |   |              | R              | S (Max)*      | V (min)       | Suct/Disch Gauge Taps (NPT) | Drain Tap (NPT) |
|-------------|---------------|----------------|---------------|---------------|----------------|---------------|---------------|----------------|---------------|---|--------------|---------------|---|--------------|----------------|---------------|---------------|-----------------------------|-----------------|
|             |               |                |               |               |                |               |               |                | J             | N | P            | J             | N | P            |                |               |               |                             |                 |
| 143JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 11.63<br>(295) | 4.88<br>(124) | 5.85<br>(149) | 22.35<br>(568) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 145JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 12.63<br>(321) | 4.88<br>(124) | 5.85<br>(149) | 23.35<br>(593) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 182JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 15.31<br>(389) | 4.88<br>(124) | 5.85<br>(149) | 26.04<br>(661) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 184JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 15.31<br>(389) | 4.88<br>(124) | 5.85<br>(149) | 26.04<br>(661) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 213JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 19.25<br>(489) | 4.88<br>(124) | 5.85<br>(149) | 29.98<br>(761) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 215JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 19.25<br>(489) | 4.88<br>(124) | 5.85<br>(149) | 29.98<br>(761) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 254JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 24.13<br>(613) | 5.88<br>(149) | 5.85<br>(149) | 35.85<br>(911) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 256JM       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 24.13<br>(613) | 5.88<br>(149) | 5.85<br>(149) | 35.85<br>(911) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 284JP       | 9.50<br>(241) | 19.00<br>(483) | 5.88<br>(149) | 6.25<br>(159) | 23.63<br>(600) | 8.56<br>(217) | 4.50<br>(114) | 36.75<br>(933) | 3.88<br>(98)  | 4 | 0.63<br>(16) | 4.50<br>(114) | 4 | 0.88<br>(22) | 16.13<br>(410) | 4.63<br>(117) | 4.00<br>(102) | 0.25                        | 0.25            |
| 286JP       | 9.50<br>(241) | 19.00<br>(483) | 5.88<br>(149) | 6.25<br>(159) | 25.13<br>(638) | 8.56<br>(217) | 4.50<br>(114) | 38.25<br>(972) | 3.88<br>(98)  | 4 | 0.63<br>(16) | 4.50<br>(114) | 4 | 0.88<br>(22) | 16.13<br>(410) | 4.63<br>(117) | 4.00<br>(102) | 0.25                        | 0.25            |

STUFFING BOX

| MOTOR FRAME | A             | B              | C             | D             | E (max)        | F             | G             | H (max)        | 125# ANSI     |   |              | 250# ANSI     |   |              | R              | S (Max)*      | V (min)       | Suct/Disch Gauge Taps (NPT) | Drain Tap (NPT) |
|-------------|---------------|----------------|---------------|---------------|----------------|---------------|---------------|----------------|---------------|---|--------------|---------------|---|--------------|----------------|---------------|---------------|-----------------------------|-----------------|
|             |               |                |               |               |                |               |               |                | J             | N | P            | J             | N | P            |                |               |               |                             |                 |
| 143JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 11.63<br>(295) | 8.00<br>(203) | 5.85<br>(149) | 25.48<br>(647) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 145JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 12.63<br>(321) | 8.00<br>(203) | 5.85<br>(149) | 26.48<br>(672) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 182JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 15.31<br>(389) | 8.00<br>(203) | 5.85<br>(149) | 29.16<br>(741) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 184JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 15.31<br>(389) | 8.00<br>(203) | 5.85<br>(149) | 29.16<br>(741) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25)  | 4.50<br>(114) | 0.25                        | 0.25            |
| 213JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 19.25<br>(489) | 8.75<br>(222) | 5.85<br>(149) | 33.85<br>(860) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 215JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 19.25<br>(489) | 8.38<br>(213) | 5.85<br>(149) | 33.48<br>(850) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 254JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 24.13<br>(613) | 8.75<br>(222) | 5.85<br>(149) | 38.73<br>(984) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 256JP       | 9.50<br>(241) | 19.00<br>(483) | 4.98<br>(126) | 6.25<br>(159) | 24.13<br>(613) | 8.75<br>(222) | 5.85<br>(149) | 38.73<br>(984) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -             | 4.50<br>(114) | 0.25                        | 0.25            |
| 284JP       | 9.50<br>(241) | 19.00<br>(483) | 5.88<br>(149) | 6.25<br>(159) | 23.63<br>(600) | 8.56<br>(217) | 4.50<br>(114) | 36.75<br>(933) | 3.88<br>(98)  | 4 | 0.63<br>(16) | 4.50<br>(114) | 4 | 0.88<br>(22) | 16.13<br>(410) | 4.63<br>(117) | 4.00<br>(102) | 0.25                        | 0.25            |
| 286JP       | 9.50<br>(241) | 19.00<br>(483) | 5.88<br>(149) | 6.25<br>(159) | 25.13<br>(638) | 8.56<br>(217) | 4.50<br>(114) | 38.13<br>(968) | 3.88<br>(98)  | 4 | 0.63<br>(16) | 4.50<br>(114) | 4 | 0.88<br>(22) | 16.13<br>(410) | 4.63<br>(117) | 4.00<br>(102) | 0.25                        | 0.25            |

Dimensions are subject to change. Not to be used for construction purposes unless certified.

NOTE: For Single phase Motors add 1" to dimensions E & H.


\*Dimensions are for ODP Motors. For TEFC add S dimension to dimensions E & H.

Xylem Inc.  
8200 N. Austin Avenue  
Morton Grove, IL 60053  
Phone: (847)966-3700 Fax: (847)965-8379  
www.bellgossett.com

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.

© 2016 Xylem Inc.

**xylem**  
Let's Solve Water



# 3x3x7C

## Marlow Series e-580

### Centrifugal Pump Submittal - Flange Support Mounting

## DIMENSIONS - Inches (mm)

## STANDARD SEAL

| MOTOR FRAME | A             | HF BOLTING     | HB             | 2HE BOLTING    | HA             | HH DIA       | E (max)        | F             | G             | H (max)        | 125# ANSI     |   |              | 250# ANSI     |   |              | R              | S (Max)*     | V (min)       | Suct/Disch Gauge Taps (NPT) | Drain Tap (NPT) |
|-------------|---------------|----------------|----------------|----------------|----------------|--------------|----------------|---------------|---------------|----------------|---------------|---|--------------|---------------|---|--------------|----------------|--------------|---------------|-----------------------------|-----------------|
|             |               |                |                |                |                |              |                |               |               |                | J             | N | P            | J             | N | P            |                |              |               |                             |                 |
| 143JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 11.63<br>(295) | 4.88<br>(124) | 7.75<br>(197) | 24.25<br>(616) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38) | 4.50<br>(114) | 0.25                        | 0.25            |
| 145JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 12.63<br>(321) | 4.88<br>(124) | 7.75<br>(197) | 25.25<br>(641) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38) | 4.50<br>(114) | 0.25                        | 0.25            |
| 182JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 15.31<br>(389) | 4.88<br>(124) | 7.75<br>(197) | 27.94<br>(710) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25) | 4.50<br>(114) | 0.25                        | 0.25            |
| 184JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 15.31<br>(389) | 4.88<br>(124) | 7.75<br>(197) | 27.94<br>(710) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25) | 4.50<br>(114) | 0.25                        | 0.25            |
| 213JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 19.25<br>(489) | 4.88<br>(124) | 7.75<br>(197) | 31.88<br>(810) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -            | 4.50<br>(114) | 0.25                        | 0.25            |
| 215JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 19.25<br>(489) | 4.88<br>(124) | 7.75<br>(197) | 31.88<br>(810) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -            | 4.50<br>(114) | 0.25                        | 0.25            |
| 254JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 24.13<br>(613) | 5.88<br>(149) | 7.75<br>(197) | 37.75<br>(959) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -            | 4.50<br>(114) | 0.25                        | 0.25            |
| 256JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 24.13<br>(613) | 5.88<br>(149) | 7.75<br>(197) | 37.75<br>(959) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -            | 4.50<br>(114) | 0.25                        | 0.25            |

## STUFFING BOX

| MOTOR FRAME | A             | HF BOLTING     | HB             | ZHE BOLTING    | HA             | HH DIA       | E (max)        | F             | G             | H (max)         | 125# ANSI     |   |              | 250# ANSI     |   |              | R              | S (Max)*     | V (min)       | Suct/Disch Gauge Taps (NPT) | Drain Tap (NPT) |
|-------------|---------------|----------------|----------------|----------------|----------------|--------------|----------------|---------------|---------------|-----------------|---------------|---|--------------|---------------|---|--------------|----------------|--------------|---------------|-----------------------------|-----------------|
|             |               |                |                |                |                |              |                |               |               |                 | J             | N | P            | J             | N | P            |                |              |               |                             |                 |
| 143JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 11.63<br>(295) | 8.00<br>(203) | 7.75<br>(197) | 27.38<br>(695)  | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38) | 4.50<br>(114) | 0.25                        | 0.25            |
| 145JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 12.63<br>(321) | 8.00<br>(203) | 7.75<br>(197) | 28.38<br>(721)  | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 9.75<br>(248)  | 1.50<br>(38) | 4.50<br>(114) | 0.25                        | 0.25            |
| 182JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 15.31<br>(389) | 8.00<br>(203) | 7.75<br>(197) | 31.06<br>(789)  | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25) | 4.50<br>(114) | 0.25                        | 0.25            |
| 184JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 15.31<br>(389) | 8.00<br>(203) | 7.75<br>(197) | 31.06<br>(789)  | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 11.75<br>(298) | 1.00<br>(25) | 4.50<br>(114) | 0.25                        | 0.25            |
| 213JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 19.25<br>(489) | 8.75<br>(222) | 7.75<br>(197) | 35.75<br>(908)  | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -            | 4.50<br>(114) | 0.25                        | 0.25            |
| 215JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 19.25<br>(489) | 8.38<br>(213) | 7.75<br>(197) | 35.38<br>(899)  | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 14.00<br>(356) | -            | 4.50<br>(114) | 0.25                        | 0.25            |
| 254JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 24.13<br>(613) | 8.75<br>(222) | 7.75<br>(197) | 40.63<br>(1032) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -            | 4.50<br>(114) | 0.25                        | 0.25            |
| 256JM       | 9.50<br>(241) | 20.95<br>(532) | 24.45<br>(621) | 21.50<br>(546) | 25.00<br>(635) | 0.88<br>(22) | 24.13<br>(613) | 8.75<br>(222) | 7.75<br>(197) | 40.63<br>(1032) | 6.00<br>(152) | 4 | 0.75<br>(19) | 6.63<br>(168) | 8 | 0.88<br>(22) | 17.00<br>(432) | -            | 4.50<br>(114) | 0.25                        | 0.25            |

Dimensions are subject to change. Not to be used for construction purposes unless certified.

NOTE: For Single phase Motors add 1" to dimensions E & H.

\*Dimensions are for ODP Motors. For TEFC add S dimension to dimensions E & H.