


JOB:		REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	



8x8x9.5B

Marlow Series e-580

In-Line Mounted Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ INPUT PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) with 125# ANSI flange drilling
- ☐ 250 psi (17 bar) with 250# ANSI flange drilling (requires e-580-S)

MOUNTING


- ☐ In-Line Piping ☐ Flange Supports

TYPE OF SEAL

- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated PTFE)



JOB:		REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	



8x8x9.5B

Marlow Series e-580

In-Line Mounted Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ INPUT PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

MAXIMUM WORKING PRESSURE


- ☐ 175 psi (12 bar) with 125# ANSI flange drilling
- ☐ 250 psi (17 bar) with 250# ANSI flange drilling (requires e-580-S)


MOUNTING

- ☐ In-Line Piping ☐ Flange Supports

TYPE OF SEAL

- ☐ -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated PTFE)





8x8x9.5B

Marlow Series e-580

Centrifugal Pump Submittal - In-Line Piping

DIMENSIONS - Inches (mm)

STANDARD SEAL

MOTOR FRAME	A	B	C	D	E (max)	F	G	H (max)	125# ANSI			250# ANSI			R	S (Max)*	V (min)	Suct/Disch Gauge Taps (NPT)	Drain Tap (NPT)
									J	N	P	J	N	P					
254JM	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	24.13 (613)	7.38 (187)	10.25 (260)	41.75 (1060)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
256JM	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	24.13 (613)	7.38 (187)	10.25 (260)	41.75 (1060)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
284JM	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	23.63 (600)	7.38 (187)	10.25 (260)	41.25 (1048)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
286JM	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	25.13 (638)	7.38 (187)	10.25 (260)	42.75 (1086)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
324JM	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	26.00 (660)	7.38 (187)	10.25 (260)	43.63 (1108)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25
326JM	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	26.00 (660)	7.38 (187)	10.25 (260)	43.63 (1108)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25


STUFFING BOX

MOTOR FRAME	A	B	C	D	E (max)	F	G	H (max)	125# ANSI			250# ANSI			R	S (Max)*	V (min)	Suct/Disch Gauge Taps (NPT)	Drain Tap (NPT)
									J	N	P	J	N	P					
254JP	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	24.13 (613)	10.25 (260)	10.25 (260)	44.63 (1133)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
256JP	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	24.13 (613)	10.25 (260)	10.25 (260)	44.63 (1133)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
284JP	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	23.63 (600)	10.25 (260)	10.25 (260)	44.13 (1121)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
286JP	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	25.13 (638)	10.25 (260)	10.25 (260)	45.63 (1159)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
324JP	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	26.00 (660)	10.25 (260)	10.25 (260)	46.50 (1181)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25
326JP	18.00 (457)	36.00 (914)	8.55 (217)	12.75 (324)	26.00 (660)	10.25 (260)	10.25 (260)	46.50 (1181)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25

Dimensions are subject to change. Not to be used for construction purposes unless certified.

NOTE: For Single phase Motors add 1" to dimensions E & H.

*Dimensions are for ODP Motors. For TEFC add S dimension to dimensions E & H.



8x8x9.5B

Marlow Series e-580

Centrifugal Pump Submittal - Flange Support Mounting

DIMENSIONS - Inches (mm)

STANDARD SEAL

MOTOR FRAME	A	HF BOLTING	HB	2HE BOLTING	HA	HH DIA	E (max)	F	G	H (max)	125# ANSI			250# ANSI			R	S (Max)*	V (min)	Suct/Disch Gauge Taps (NPT)	Drain Tap (NPT)
											J	N	P	J	N	P					
254JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	24.13 (613)	7.38 (187)	14.25 (362)	45.75 (1162)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
256JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	24.13 (613)	7.38 (187)	14.25 (362)	45.75 (1162)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
284JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	23.63 (600)	7.38 (187)	14.25 (362)	45.25 (1149)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
286JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	25.13 (638)	7.38 (187)	14.25 (362)	46.75 (1187)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
324JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	26.00 (660)	7.38 (187)	14.25 (362)	47.63 (1210)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25
326JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	26.00 (660)	7.38 (187)	14.25 (362)	47.63 (1210)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25

STUFFING BOX

MOTOR FRAME	A	HF BOLTING	HB	ZHE BOLTING	HA	HH DIA	E (max)	F	G	H (max)	125# ANSI			250# ANSI			R	S (Max)*	V (min)	Suct/Disch Gauge Taps (NPT)	Drain Tap (NPT)
											J	N	P	J	N	P					
254JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	24.13 (613)	10.25 (260)	14.25 (362)	48.63 (1235)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
256JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	24.13 (613)	10.25 (260)	14.25 (362)	48.63 (1235)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (432)	17.00 (432)	-	4.75 (121)	0.25	0.25
284JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	23.63 (600)	10.25 (260)	14.25 (362)	48.13 (1222)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
286JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	25.13 (638)	10.25 (260)	14.25 (362)	49.63 (1260)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (410)	16.13 (410)	4.63 (117)	4.75 (121)	0.25	0.25
324JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	26.00 (660)	10.25 (260)	14.25 (362)	50.50 (1283)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25
326JM	18.00 (457)	36.92 (938)	40.42 (1027)	28.50 (724)	32.00 (813)	1.13 (29)	26.00 (660)	10.25 (260)	14.25 (362)	50.50 (1283)	11.75 (298)	8 (22)	0.88 (22)	13.00 (330)	12 (25)	1.00 (476)	18.75 (476)	5.38 (137)	4.75 (121)	0.25	0.25

Dimensions are subject to change. Not to be used for construction purposes unless certified.

NOTE: For Single phase Motors add 1" to dimensions E & H.

*Dimensions are for ODP Motors. For TEFC add S dimension to dimensions E & H.