


JOB: _____ REPRESENTATIVE: _____

UNIT TAG: _____ ORDER NO. _____ DATE: _____
ENGINEER: _____ SUBMITTED BY: _____ DATE: _____
CONTRACTOR: _____ APPROVED BY: _____ DATE: _____



6-9SC

Marlow Series 530

Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
HP _____ RPM _____
VOLTS _____
CYCLE _____ PHASE _____
ENCLOSURE _____
APPROX. WEIGHT _____
SPECIALS _____

MATERIALS OF CONSTRUCTION


☐ BRONZE FITTED ☐ ALL IRON

MAXIMUM WORKING PRESSURE

☐ 175 psi (12 bar) W.P.
with 125# ANSI flange drilling


TYPE OF SEAL

- ☐ 530 Standard Seal
(Buna-Carbon/Ceramic)
- ☐ 530 -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ 530 -S Stuffing Box construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ 530 -D Stuffing Box construction w/ Flushed Double
Mechanical Seal
(EPR-Carbon/Ceramic)
Requires external water source
- ☐ 530 -PF Stuffing Box Construction
w/ Flushed Packing
(Graphite Impregnated Teflon)



JOB: _____ REPRESENTATIVE: _____

UNIT TAG: _____ ORDER NO. _____ DATE: _____
ENGINEER: _____ SUBMITTED BY: _____ DATE: _____
CONTRACTOR: _____ APPROVED BY: _____ DATE: _____



6-9SC

Marlow Series 530

Close-Coupled Centrifugal Pumps

SPECIFICATIONS

FLOW _____ HEAD _____
HP _____ RPM _____
VOLTS _____
CYCLE _____ PHASE _____
ENCLOSURE _____
APPROX. WEIGHT _____
SPECIALS _____

MATERIALS OF CONSTRUCTION


☐ BRONZE FITTED ☐ ALL IRON


MAXIMUM WORKING PRESSURE

☐ 175 psi (12 bar) W.P.
with 125# ANSI flange drilling

TYPE OF SEAL

- ☐ 530 Standard Seal (Buna-Carbon/Ceramic)
- ☐ 530 -F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- ☐ 530 -S Stuffing Box construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- ☐ 530 -D Stuffing Box construction w/ Flushed Double Mechanical Seal (EPR-Carbon/Ceramic) Requires external water source
- ☐ 530 -PF Stuffing Box Construction w/ Flushed Packing (Graphite Impregnated Teflon)





SIZE OF PUMP AND DISCHARGE	SUCTION	PUMP DIMENSIONS IN INCHES (MM)			
		DD	X	Y	Z
6-9SC	8	10-3/8 (264)	10-1/2 (267)	7 (178)	8-1/4 (210)

125# ANSI FLANGE DIMENSIONS - INCHES (MM)				
PIPE SIZE OF FLANGE	O.D. OF FLANGE	DIA. OF BOLT CIRCLE	NO. OF BOLTS	SIZE OF BOLTS
6	12-1/8 (308)	9-1/2 (241)	8	3/4 (19)
8	14-3/4 (375)	11-3/4 (298)	8	3/4 (19)

DIMENSIONS – Inches (mm)

STANDARD SEAL										
MOTOR FRAME	A (Max)	AB (Max)	B (Max)	CP (Max)	D	2E	F	H	L	O (Max)
254JP	12-1/2 (318)	10-3/4 (273)	10-3/4 (273)	37-7/8 (962)	6-1/4 (159)	10 (254)	8-1/4 (210)	17/32 (13)	22-1/4 (565)	13-1/8 (333)
256JP	12-1/2 (318)	10-3/4 (273)	12-1/2 (318)	39-5/8 (1006)	6-1/4 (159)	10 (254)	10 (254)	17/32 (13)	22-1/4 (565)	13-1/8 (333)
284JP	14 (356)	12-5/8 (321)	12-1/2 (318)	39 (991)	7 (178)	11 (279)	9-1/2 (241)	17/32 (13)	22-1/4 (565)	15 (381)
286JP	14 (356)	12-5/8 (321)	14 (356)	40-1/2 (1029)	7 (178)	11 (279)	11 (279)	17/32 (13)	22-1/4 (565)	15 (381)
324JP	16 (406)	15-1/8 (384)	14 (356)	42 (1067)	8 (203)	12-1/2 (318)	10-1/2 (267)	21/32 (17)	22-3/4 (578)	17 (432)
326JP	16 (406)	15-1/8 (384)	15-1/2 (394)	43-1/2 (1105)	8 (203)	12-1/2 (318)	12 (305)	21/32 (17)	22-3/4 (578)	17 (432)

STUFFING BOX										
MOTOR FRAME	A (Max)	AB (Max)	B (Max)	CP (Max)	D	2E	F	H	L	O (Max)
254JP	12-1/2 (318)	10-3/4 (273)	10-3/4 (273)	37-7/8 (962)	6-1/4 (159)	10 (254)	8-1/4 (210)	17/32 (13)	22-1/4 (565)	13-1/8 (333)
256JP	12-1/2 (318)	10-3/4 (273)	12-1/2 (318)	39-5/8 (1006)	6-1/4 (159)	10 (254)	10 (254)	17/32 (13)	22-1/4 (565)	13-1/8 (333)
284JP	14 (356)	12-5/8 (321)	12-1/2 (318)	39 (991)	7 (178)	11 (279)	9-1/2 (241)	17/32 (13)	22-1/4 (565)	15 (381)
286JP	14 (356)	12-5/8 (321)	14 (356)	40-1/2 (1029)	7 (178)	11 (279)	11 (279)	17/32 (13)	22-1/4 (565)	15 (381)
324JP	16 (406)	15-1/8 (384)	14 (356)	42 (1067)	8 (203)	12-1/2 (318)	10-1/2 (267)	21/32 (17)	22-3/4 (578)	17 (432)
326JP	16 (406)	15-1/8 (384)	15-1/2 (394)	43-1/2 (1105)	8 (203)	12-1/2 (318)	12 (305)	21/32 (17)	22-3/4 (578)	17 (432)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.gouldswatertechnology.com

