



4SD

SUBMERSIBLE SEWAGE PUMP

DUAL SEAL WITH SEAL SENSOR PROBE



FEATURES

Impeller: Cast iron, two vane semi-open, non-clog with pump-out vanes for mechanical seal protection. Balanced for smooth operation. Silicon bronze impeller available as an option.

Casing: Heavy duty cast iron, volute type for maximum efficiency. 4" flange conforms to 125 # ANSI standard. Connects to A10-40 or A10-60 guide rail system.

Dual Mechanical Seals: Silicon carbide vs. silicon carbide outer seal and ceramic vs. carbon inner seal, stainless steel metal parts, BUNA-N elastomers. Upper and lower shaft seals are positioned independently and are separated by an oil-filled chamber.

Seal Sensor Probe: Located in oil-filled chamber. If pumpage should begin to leak past lower seal it indicates to pump control panel a fault has occurred. **Requires optional Seal Fail Circuit in the control panel.**

Shaft: 300 series stainless steel keyed design.

Fasteners: 300 series stainless steel.

Capable of running dry without damage to components.

AGENCY LISTINGS



Tested to UL 778 and CSA 22.2 108 Standards
By Canadian Standards Association
File #LR38549

APPLICATIONS

Used in a variety of residential, commercial and industrial applications such as:

- Sewage systems
- Flood and pollution control
- Dewatering/Effluent
- Farms
- Hospitals
- Trailer courts
- Motels

SPECIFICATIONS

Pump:

- Maximum solid size: 3"
- Discharge size: 4", 125 # ANSI flange
- Maximum capacity: 620 GPM
- Maximum total head: 60 feet
- 300 Series stainless steel fasteners
- 20' Power cord
- Standard silicon carbide/silicon carbide outer seal

Motor:

- Maximum ambient temperature: 104° F (40° C) continuous duty, 140° F (60° C) intermittent duty
- Rated for continuous duty when fully submerged
- Insulation: Class F
- 60 Hertz
- Single row ball bearings
- 300 Series stainless steel keyed shaft

Single Phase:

- 1.5 - 5 HP
- 208 and 230 volts
- Built-in thermal overloads with automatic reset
- Built-in capacitors

Three Phase:

- 1.5 - 7.5 HP
- 200, 230, 460 and 575 volts
- Class 10 overload protection must be provided in control panel

MOTORS


- Fully submerged in oil-filled chamber. High grade turbine oil surrounds motor for more efficient heat dissipation, permanent lubrication of bearings and mechanical seal for complete protection against outside environment.
- **Class F insulation**
- **Designed for Continuous Operation:** Pump ratings are within the motor manufacturer's recommended working limits and can be operated continuously without damage when fully submerged.
- **Bearings:** Upper and lower heavy duty ball bearing construction for precision positioning of parts and to carry thrust loads.
- **Power and Control Cables:** Severe duty rated, oil and water resistant. Epoxy seal on motor end provides secondary moisture barrier in case of outer jacket damage and to prevent oil wicking. 20 foot standard with optional lengths available.
- **O-ring:** Assures positive sealing against contaminants and oil leakage.

MODEL AND MOTOR INFORMATION

Order Number	HP	Phase	Volts	RPM	Impeller		Maximum Amps	Locked Rotor Amps	KVA Code	Power Cable	F.L. Motor Efficiency %	Resistance		Weight (lbs.)
					Dia. (In.)	Code						Start	Line-Line	
4SD52F8EA	1.5	1	208	1750	5.63	E	17.2	50.8	B	14/3	80	1.1	0.9	195
4SD52F1EA			230				14.7	29.5	E		70	1.4	1.8	
4SD52F2EA		3	200				11.5	40.9	H	14/4	81	NA	1.7	
4SD52F3EA			230				10.0	40.0	F		83		2.3	
4SD52F4EA			460				5.0	20.0	F		83		9.3	
4SD52F5EA			575				4.0	14.4	H		74		14.8	
4SD52F8DA	1.5	1	208		6.25	D	17.2	50.8	B	14/3	80	1.1	0.9	195
4SD52F1DA			230				14.7	29.5	E		70	1.4	1.8	
4SD52F2DA		3	200				11.5	40.9	H	14/4	81	NA	1.7	
4SD52F3DA			230				10.0	40.0	F		83		2.3	
4SD52F4DA			460				5.0	20.0	F		83		9.3	
4SD52F5DA			575				4.0	14.4	H		74		14.8	
4SD52G8CA	2	1	208		6.63	C	20.3	50.8	B	14/3	80	1.1	0.9	200
4SD52G1CA			230				17.3	36.9	D		75	1.4	1.5	
4SD52G2CA		3	200				13.3	40.9	H	14/4	81	NA	1.7	
4SD52G3CA			230				11.6	40.0	F		83		2.3	
4SD52G4CA			460				5.8	20.0	F		83		9.3	
4SD52G5CA			575				4.6	14.4	H		74		14.8	
4SD52H8BA	3	1	208		7.00	B	25.5	50.8	B	10/3	80	1.1	0.9	208
4SD52H1BA			230				21.5	46.4	C		79	1.0	1.0	
4SD52H2BA		3	200				16.6	53.8	G	10/4	85	NA	1.3	205
4SD52H3BA			230				14.4	49.5	H		83		1.9	
4SD52H4BA			460				7.2	24.8	H		83		7.5	
4SD52H5BA			575				5.8	17.3	G		78		11.6	
4SD52J1AA	5	1	230		7.25	A	26.5	57.7	A	10/3	80	1.0	0.8	213
4SD52J2AA		3	200				19.1	73.9	F	10/4	84	NA	0.9	210
4SD52J3AA			230				16.6	63.6	E		85		1.2	
4SD52J4AA			460				8.3	31.8	E		85		4.8	
4SD52J5AA			575				6.6	22.8	E	14/4	80		7.4	
4SD52K3FA	7.5	3	230		7.69	F	23.0	105.0	G	10/4	83	NA	0.7	225
4SD52K4FA			460				11.5	52.5	G		83		2.8	
4SD52K5FA			575				9.2	42.0	E		84		4.4	

DIMENSIONS

(All dimensions are in inches. Do not use for construction purposes.)



APPLICATION DATA

Maximum Solid Size	3"
Minimum Casing Thickness	5/16"
Casing Corrosion Allowance	1/8"
Maximum Working Pressure	30 PSI
Maximum Submergence	50 feet
Minimum Submergence	Fully submerged for continuous operation
	6" below top of motor for intermittent operation
Maximum Environmental Temperature	40°C (104°F) continuous operation
	60°C (140°F) intermittent operation

CONSTRUCTION DETAILS

Power Cable - Type	14/3, type SJTOW: single phase, ½ and 2 HP
	14/4, type STOW: single phase, 1½ - 3 HP and 5 HP, 460 V
	10/4, type STOW: single phase, 3 and 5 HP, three phase 5 HP, 230 V and 7½ HP
Sensor Cable - Type	16/2, type SJTOW: seal sensor only
	18/4, type SJTOW: seal/heat sensor
Motor Cover	Gray Cast Iron - ASTM A48 Class 30
Bearing Housing	Gray Cast Iron - ASTM A48 Class 30
Seal Housing	Gray Cast Iron - ASTM A48 Class 30
Casing	Gray Cast Iron - ASTM A48 Class 30
Impeller	Gray Cast Iron - ASTM A48 or Cast Bronze - ASTM B584 C87600
Motor Shaft	AISI 300 Series Stainless Steel
Motor Design	NEMA 56 Frame, oil filled with Class F Insulation
Motor Overload Protection	Single Phase: on winding thermal overload protection
	Three Phase: require ambient compensated Class 10, quick trip overloads in the control panel.
Motor Seal Fail (Moisture) Detection	Seal fail sensor in an oil-filled seal chamber. Connect to an optional relay in control panel.
Optional Motor Thermal Protection	Normally closed on-winding thermostats open at 275° F (135 °C) and close at 112° F (78° C). Require terminal connection in the control panel.
External Hardware	300 Series Stainless Steel
Impeller Type	Semi-open with pump out vanes on back shroud
Oil Capacity - Seal Chamber	1.75 quarts
Oil Capacity - Motor Chamber	1½-5 HP single and three phase: 7 quarts
	7½ HP three phase: 6.5 quarts

STANDARD PARTS

Ball Bearing	Upper	1½ - 5 HP single and three phase: single row ball- SKF™ 6204-2Z
		7½ HP three phase: single row ball - SKF™ 6204-2Z
	Lower	1½ - 5 HP single and three phase: single row ball - SKF™ 5206-2Z
		7½ HP three phase: double row ball - SKF™ 5206-2Z
Mechanical Seals - Standard	Upper	Carbon/Ceramic; Type 21
	Lower	Silicon Carbon/Silicon Carbon; Type 31
Mechanical Seals - Optional Lower		Silicon Carbide/Tungsten Carbide: Type 21
O-Ring - Stuffing Box		BUNA-N, AS 568A-265
O-Ring - Motor Cover		BUNA-N, AS 568A-374

NOMENCLATURE DESCRIPTION

1st, 2nd and 3rd Character - Discharge Size and Type

4SD = 4" discharge, 3" solids handling, dual seal with seal fail probe in pump.

4th Character - Mechanical Seals

5 = Silicon carbide/silicon carbide/BUNA - lower seal and carbon/ceramic/BUNA - upper seal (standard)

3 = Silicon carbide/tungsten carbide/BUNA - lower seal and carbon/ceramic/BUNA - upper seal (optional)

5th Character - Cycle/RPM

2 = 60 Hz/1750 RPM 6 = 50 Hz/1450 RPM

6th Character - Horsepower

F = 1½ HP H = 3 HP K = 7½ HP

G = 2 HP J = 5 HP

7th Character - Phase/Voltage

1 = single phase, 230 V 4 = three phase, 460 V

2 = three phase, 200 V* 5 = three phase, 575 V

3 = three phase, 230 V 8 = single phase, 208 V

* Not available on 7½ HP.

8th Character - Impeller Diameter

A = 7.25", 5 HP D = 6.25", 1½ HP

B = 7.00", 3 HP E = 5.63", 1½ HP

C = 6.63", 2 HP F = 7.69", 7½ HP

9th Character - Cord Length (Power and Sensor)

A = 20' (standard) F = 50'

D = 30' J = 100'

10th Character - Options

B = Bronze impeller

E = Epoxy paint


F = Both epoxy paint and bronze impeller

11th Character - Option

H = Pilot duty thermal sensors (3 phase only)

MATERIALS OF CONSTRUCTION

Item No.	Part Name		Material			
			Standard		Optional	
1	Impeller, non-clog		1003		1179	
2	Castings		1003			
3	Shaft-Keyed		300 Series SS			
4	Fasteners		300 Series SS			
5	Ball bearings		Steel			
6	Power cable		STOW, 20 feet		Additional lengths	
	Seal sensor cable					
7	O-ring		BUNA-N			
8	Outer Mech. Seal	Service	Rotary	Stationary	Elasto- mers	Metal Parts
	OPT	Heavy duty	Silicon Carbide	Tungsten Carbide	BUNA-N	300 Series SS
	STD	Mild abrasives	Silicon Carbide		BUNA-N	300 Series SS
Material Code			Engineering Standard			
1003			Cast iron – ASTM A48 Class 30			
1179			Silicon bronze – ASTM C87600			



STANDARD PANEL OPTIONS

Order Number	HP	Phase	Volts	SF Amps	Simplex Panel Part Number	Duplex Panel Part Number
4SD52F8EA	1.5	1	208	17.2	SDS11522	SDD11522
4SD52F1EA			230	14.7	SDS17015	SDD17015
4SD52F2EA		3	200	11.5	SDS39014	SDD39014
4SD52F3EA			230	10	SDS39014	SDD39014
4SD52F4EA			460	5	SDS34063	SDD34063
4SD52F5EA			575	4.0	Consult factory for custom quote.	Consult factory for custom quote.
4SD52F8DA		1	208	17.2	SDS11522	SDD11522
4SD52F1DA			230	14.7	SDS17015	SDD17015
4SD52F2DA		3	200	11.5	SDS39014	SDD39014
4SD52F3DA			230	10	SDS39014	SDD39014
4SD52F4DA			460	5	SDS34063	SDD34063
4SD52F5DA			575	4	Consult factory for custom quote.	Consult factory for custom quote.
4SD52G8CA	2	1	208	20.3	SDS11522	SDD11522
4SD52G1CA			230	17.3	SDS11522	SDD11522
4SD52G2CA		3	200	13.3	SDS31318	SDD31318
4SD52G3CA			230	11.6	SDS39014	SDD39014
4SD52G4CA			460	5.8	SDS34063	SDD34063
4SD52G5CA			575	4.6	Consult factory for custom quote.	Consult factory for custom quote.
4SD52H8BA	3	1	208	25.5	SDS12228	SDD12228
4SD52H1BA			230	21.5	SDS12228	SDD12228
4SD52H2BA		3	200	16.6	SDS31318	SDD31318
4SD52H3BA			230	14.4	SDS31318	SDD31318
4SD52H4BA			460	7.2	SDS36010	SDD36010
4SD52H5BA			575	5.8	Consult factory for custom quote.	Consult factory for custom quote.
4SD52J1AA	5	1	230	26.5	SDS12228	SDD12228
4SD52J2AA		3	200	19.1	SDS31723	SDD31723
4SD52J3AA			230	16.6	SDS31318	SDD31318
4SD52J4AA			460	8.3	SDS36010	SDD36010
4SD52J5AA			575	6.6	Consult factory for custom quote.	Consult factory for custom quote.
4SD52K3FA	7.5	3	230	23	SDS32025	SDD32025
4SD52K4FA			460	11.5	SDS39014	SDD39014
4SD52K5FA			575	9.2	Consult factory for custom quote.	Consult factory for custom quote.

NOTES

Xylem |'zīləm|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating advanced technology solutions to the world's water challenges. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. Our products and services move, treat, analyze, monitor and return water to the environment, in public utility, industrial, residential and commercial building services settings. Xylem also provides a leading portfolio of smart metering, network technologies and advanced analytics solutions for water, electric and gas utilities. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise with a strong focus on developing comprehensive, sustainable solutions.

For more information on how Xylem can help you, go to www.xylem.com



Xylem Inc.
2881 East Bayard Street Ext., Suite A
Seneca Falls, NY 13148
Phone: (866) 325-4210
Fax: (888) 322-5877
www.xylem.com/goulds

Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.
© 2023 Xylem Inc. B4SD R4 September 2023