



# Full Circle®

## All Stainless Steel, Fabricated Lugs, Double Band

# 262

### IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)

[Sales Terms & Conditions](#)

[Freight Policy](#)

[Returns Policy](#)

[Corrosion & Product Selection Notice](#)



**THIS PRODUCT DOES NOT RESTRAIN PIPE MOVEMENT.** Proper anchoring is required to prevent pipe pullout. Failure to anchor or improper anchoring can result in dangerous pipe content escape, property damage, serious injury, or death. Read the product installation instructions prior to installing this product.

**Description:** A double-band clamp designed to provide 360° pressure and complete leak repair

**Application:** Works on Cast Iron, Ductile Iron, Steel, Asbestos cement, Copper, Aluminum, PVC, HDPE and Fiberglass.

### Key Features:

- Designed with "hot" soils in mind
- Standard widths 7.5" through 30"
- Can be used to repair pipe or join pipe ends
- Can be manufactured to odd size pipe O.D.'s
- All 304 Stainless Steel construction for corrosion resistance
- A 360° Gasket seal provides maximum support and reinforcement
- Keeper bar helps pull clamp around the pipe and closes the clamp during installation
- Range up to .40"
- Larger clamps have a greater range to help reduce inventory

### Materials Specifications (subject to change):

BAND: Stainless Steel Type 304

LUGS: Stainless Steel Type 304)

KEEPER BARS: Stainless Steel Type 304)

GASKET: Nitrile (Buna N) to produce superior storage and performance characteristics while resisting water, acids, alkalis, most aliphatic hydrocarbon and other chemicals.

Temperature Range: -20°F to +180°F

BRIDGE PLATE: 304 Stainless Steel recessed flush and bonded to gasket

STUD BOLTS: Type 304 Stainless Steel Epoxy coated

NUTS: fluoropolymer coated to prevent galling

*Also in metric sizes. HDPE applications require clamps with spring washers*

**Working Pressure:** Up to 150 PSI

**Pipe Applications:** Cast Iron, Asbestos Cement, PVC, HDPE, Steel, Copper, Fiberglass and other types of pipes

**Sizes (in inches):** 2, 2¼-2½, 3, 4, 4-5, 6, 8, 10, 12



# Full Circle<sup>®</sup>

## All Stainless Steel, Fabricated Lugs, Double Band

262

STANDARD				CATALOG NUMBER	METRIC			
NOM. SIZE INCHES	O.D. RANGE INCHES	WIDTH INCHES	WT. EACH LBS.		NOM. SIZE MM	O.D. RANGE MM	WIDTH MM	WT. EACH KG.
3	3.49-4.29	7.5	8	262-00035007-000	80	88-110	190	4.1
	3.49-4.29	10	12	262-00035010-000		88-110	254	5.4
	3.49-4.29	12.5	15	262-00035012-000		88-110	317	6.8
	3.49-4.29	15	18	262-00035015-000		88-110	381	8.2
	3.49-4.29	20	24	262-00035020-000		88-110	508	10.9
4	4.44-5.24	7.5	9	262-00045007-000	100	113-133	190	4.3
	4.44-5.24	10	13	262-00045010-000		113-133	254	5.7
	4.44-5.24	12.5	16	262-00045012-000		113-133	317	7.1
	4.44-5.24	15	19	262-00045015-000		113-133	381	8.5
	4.44-5.24	20	25	262-00045020-000		113-133	508	11.4
4	4.74-5.57	7.5	10	262-00048007-000	100	121-141	190	4.5
	4.74-5.57	10	13	262-00048010-000		121-141	254	5.9
	4.74-5.57	12.5	16	262-00048012-000		121-141	317	7.4
	4.74-5.57	15	20	262-00048015-000		121-141	381	8.9
	4.74-5.57	20	26	262-00048020-000		121-141	508	11.8
6	6.62-7.42	7.5	10	262-00066307-000	150	168-189	190	4.9
	6.62-7.42	10	14	262-00066310-000		168-189	254	6.5
	6.62-7.42	12.5	18	262-00066312-000		168-189	317	8.2
	6.62-7.42	15	22	262-00066315-000		168-189	381	9.8
	6.62-7.42	20	29	262-00066320-000		168-189	508	13.1
6	6.84-7.64	7.5	10	262-00069007-000	150	174-194	190	4.9
	6.84-7.64	10	15	262-00069010-000		174-194	254	6.6
	6.84-7.64	12.5	18	262-00069012-000		174-194	317	8.3
	6.84-7.64	15	22	262-00069015-000		174-194	381	9.9
	6.84-7.64	20	29	262-00069020-000		174-194	508	13.2
8	8.62-9.42	7.5	13	262-00086307-000	200	219-239	190	5.7
	8.62-9.42	10	17	262-00086310-000		219-239	254	7.6
	8.62-9.42	12.5	21	262-00086312-000		219-239	317	9.4
	8.62-9.42	15	25	262-00086315-000		219-239	381	11.3
	8.62-9.42	20	34	262-00086320-000		219-239	508	15.1
8	8.99-9.79	7.5	13	262-00090507-000	200	229-248	190	5.9
	8.99-9.79	10	16	262-00090510-000		229-248	254	7.9
	8.99-9.79	12.5	22	262-00090512-000		229-248	317	9.9
	8.99-9.79	15	26	262-00090515-000		229-248	381	11.8
	8.99-9.79	20	35	262-00090520-000		229-248	508	15.8
10	10.75-11.55	10	21	262-00107510-000	250	273-293	254	9.4
	10.75-11.55	15	31	262-00107515-000		273-293	381	14.1
	10.75-11.55	20	41	262-00107520-000		273-293	508	18.8

STANDARD				CATALOG NUMBER	METRIC			
NOM. SIZE INCHES	O.D. RANGE INCHES	WIDTH INCHES	WT. EACH LBS.		NOM. SIZE MM	O.D. RANGE MM	WIDTH MM	WT. EACH KG.
10	11.10-11.90	10	21	262-00111010-000	250	282-302	254	9.5
	11.10-11.90	15	31	262-00111015-000		282-302	381	14.2
	11.10-11.90	20	42	262-00111020-000		282-302	508	19.0
10	11.60-12.40	10	21	262-00116010-000	250	295-315	254	9.6
	11.60-12.40	15	32	262-00116015-000		295-315	381	14.4
	11.60-12.40	20	42	262-00116020-000		295-315	508	19.2
12	12.75-13.55	10	23	262-00127510-000	300	325-344	254	10.4
	12.75-13.55	15	35	262-00127515-000		325-344	381	15.7
	12.75-13.55	20	46	262-00127520-000		325-344	508	20.9
12	13.20-14.00	10	23	262-00132010-000	300	335-355	254	10.5
	13.20-14.00	15	35	262-00132015-000		335-355	381	15.8
	13.20-14.00	20	46	262-00132020-000		335-355	508	21.1
12	13.65-14.45	10	24	262-00136510-000	300	347-367	254	10.7
	13.65-14.45	15	35	262-00136515-000		347-367	381	16.0
	13.65-14.45	20	47	262-00136520-000		347-367	508	21.3
12	14.00-14.80	10	25	262-00140010-000	300	357-376	254	11.4
	14.00-14.80	15	38	262-00140015-000		357-376	381	17.1
	14.00-14.80	20	50	262-00140020-000		357-376	508	22.8

## Bolt Numbers

BAND WIDTH INCHES	NUMBER OF STUDS	STUD SIZES
7.5	4	5/8" X 7" or 16mm x 178mm
10	6	
12.5	6	
15	8	
20	10	