



Service Saddle

For PVC or Steel Pipe

357

IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)

[Sales Terms & Conditions](#)

[Freight Policy](#)

[Returns Policy](#)

[Corrosion & Product Selection Notice](#)



Description: Double strap saddle with large tapped outlet.

Application: For distribution or new pipeline installations. (Not for use on Ductile Iron pipe)

Key Features:

- Meets applicable AWWA C800 Standards
- The wide saddle body provides stability on the pipe
- Designed with PVC pipe in mind
- The gasket fully bonded to the cavity to hold it in place
- NPT, CC and other threaded outlets available in 3" and 4"
- Wide bands spread the load over larger area to prevent damage to the pipe when tightening the straps
- A closed lug on one side, combined with the straps, acts as a hinge for easier installation

Materials Specifications (subject to change):

BODIES: Ductile Iron per ASTM A536

BANDS: Type 304 Stainless Steel

GASKET: Nitrile (Buna N) NSF 61 compounded to resist oil, acids, alkalies, most (aliphatic) hydrocarbon fluids, water and other chemicals

Temperature Range: -20°F to 180°F

FINISH: Flexi-Coat® Fusion-Bonded Epoxy Finish

STUD: Type 304 Stainless Steel

NUTS & WASHERS: Type 304 Stainless Steel

Working Pressure: Up to 150 PSI, depending on size and application

Pipe Applications: Steel and PVC

Taps: 3" and 4" NPT taps

Sizes (in inches): 6, 8, 10, 12



357

Service Saddle

For PVC or Steel Pipe

3" and 4" NPT Taps

STANDARD				CATALOG NUMBER	METRIC		
NOM. SIZES INCHES	O.D. RANGE INCHES	WT. EACH LBS.	TAP SIZE INCHES		NOM. SIZE MM	O.D. RANGE MM	WT. EACH KG.
6	6.63-6.90	12 12	3 4	357-00069017-000 357-00069018-000	150	168-175	6 6
8	8.63-9.05	13 13	3 4	357-00090517-000 357-00090518-000	200	219-230	6 6
10	10.75-11.10	14 14	3 4	357-00111017-000 357-00111018-000	250	273-282	6 6
12	12.75-13.20	14 14	3 4	357-00132017-000 357-00132018-000	300	323-335	6 6