

Quick Startup Guide



DOC Series

DOC., DOC..VX., DOC..SG., DOC.. GW







 $0 \div 40^{\circ}\text{C}$ ($32 \div 104^{\circ}\text{F}$)




Pump unit					
Cod.		t _{max}	°C		
Q	l/min	P2	kW		
H	m	H _{min}	m		
Motor	~		Hz		
	V		A		
P1	kW	Duty	CI	IP	
C	uF/	V		∇	m
Date	No				

∇, m	d, m (ft)	L, m (ft)
2	≤ 2 (6.5)	5 (16.4)
5	≤ 5 (16.4)	≥ 10 (32.8)



 , mm (in)	
≤ 10 (0,4)	DOC
≤ 20 (0,8)	DOC VX


i




1




2





3




i




	A, mm (in)	B, mm (in)	C, mm (in)	D, mm (in)
DOC3..	330 (13)	50 (2)	310 (12.2)	≥ 330 (13)
DOC7..	370 (14.5)	90 (3.5)	350 (13.7)	≥ 370 (14.6)
DOC7VX..	395 (15.6)	115 (4.5)	378 (14.8)	≥ 395 (15.6)




	A, mm (in)	B, mm (in)	C, mm (in)	D, mm (in)
DOC3..GW	≤ 131 (5.2)	≥ 56 (2.2)	95 (3.7)	≥ 330 (13)
DOC7..GW	≤ 171 (6.7)	≥ 96 (3.8)	115 (4.5)	≥ 370 (14.6)
DOC7VX..GW	≤ 196 (7.7)	≥ 121 (4.8)	140 (5.5)	




4



1~



3~





xylem
Let's Solve Water

Xylem Service Italia S.r.l.
Via Vittorio Lombardi 14
36075 - Montecchio Maggiore (VI) - Italy

Visit our Web site for the latest version of this document
and more information

© 2019 Xylem Inc
Cod. 001082044 rev.B ed.12/2024