



Smith-Blair, Inc.
Inside Sales Department
 30 Globe Avenue
 Texarkana, AR 71854

Phone: 870-773-5127 or 800-643-9705
 Fax: 870-773-5212 or 800-648-6792
 www.smith-blair.com
 insidesales@smith-blair.com

625 Typical Data Sheet

Style Required: <input type="checkbox"/> 2 Flange (Typical for 4"-12" Outlets) <input type="checkbox"/> 3 Flange (Typical for 14" and larger Outlets)	
Customer Name:	By Date:
Address:	
<i>Street</i>	<i>City</i>
<i>State</i>	<i>Zip Code</i>
Customer Contact:	Smith-Blair Rep:
Customer Phone:	Customer Fax:
Project Title:	
Operating Pressure:	Test Pressure:
Line Contents:	Submittal Drawing Required: <input type="checkbox"/> No (standard) <input type="checkbox"/> Yes (optional)
Pipe Type:	Nominal Pipe Size:
Concrete Outside Diameter:	Steel Cylinder Diameter:
Outlet Size:	Valve Lip Outside Diameter:
Cutter Outside Diameter:	Cutter Support Bearing Required: <input type="checkbox"/> No (standard) <input type="checkbox"/> Yes (optional)
Valve Flange: <input type="checkbox"/> AWWA C207 Class 'D' (standard) <input type="checkbox"/> Other (please specify) _____ _____	Valve Lip Recess Required: <input type="checkbox"/> No (standard 14" valves and larger) <input type="checkbox"/> Yes (standard 12" valves and smaller) - Valve Lip Outside Diameter: _____ - Valve Lip Height: _____
Test Port Required: <input type="checkbox"/> No (standard) <input type="checkbox"/> Yes (optional) Test port size if not standard: _____	Fasteners: <input type="checkbox"/> High Strength Corrosion Resistant Alloy Steel <input type="checkbox"/> 304 Stainless Steel <input type="checkbox"/> Other (please specify)
Special Requirements:	

