



Flexible Meter Coupling

926

IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)

[Sales Terms & Conditions](#)

[Freight Policy](#)

[Returns Policy](#)

[Corrosion & Product Selection Notice](#)



NSF/ANSI 61
NSF/ANSI 372

Description: Meter coupling

Application: For joining plain-end pipe to oval flanged water meters and joining plain-end pipe to flanged valves and fittings

Key Features:

- Simple, quick installation of 1½" and 2" flanged meters
- Meter coupling eliminates pipe threading and need of precise cutting or alignment of pipe

Materials Specifications (subject to change):

FLANGED BODY AND FOLLOWER: Ductile Iron ASTM A536

GASKET: Nitrile (Buna N)

O-RING: Nitrile (Buna N)

BOLTS & NUTS: High strength low alloy bolts.

FINISH: Flexi-Coat® Fusion-Bonded Epoxy Coat Finish per AWWA C213

Working Pressure: Up to 150 PSI.

Pipe Applications: PVC, Copper, Steel

Sizes (in inches): 1½, 2



926

Flexible Meter Coupling

FLANGED METER OUTLET SIZE INCHES	SERVICE SIZE (INCHES)		CATALOG NUMBER	WEIGHT EACH LBS.	LENGTH FLANGE	OD FLANGE	BODY THICKNESS	LENGTH	BOLTS	
	NOM. SIZE (INCHES)	PIPE O.D. INCHES							QTY.	SIZE
1 1/2	1 1/2 I.P.	1.90	926-000190-000	5	3 1/2	3 3/4	7/16	1 3/4	2	5/8 x 5
2	2 CO P.T. or Steel	2.13	926-000213-000	6	3 1/2	4 1/4	7/16	1 3/4	2	5/8 x 5
2	2 I.P. 2 C.I.	2.37- 2.50	926-000250-000	6	3 1/2	4 1/4	7/16	1 3/4	2	5/8 x5