




Wedeco LBX Series

THE IDEAL UV SOLUTION WHEN WASTEWATER IS UNDER PRESSURE



WEDECO
a xylem brand

Certified to meet industry and national standards. Customized to meet yours.


The Wedeco LBX Series is a thousand times proven, energy efficient solution for the disinfection of pressurized wastewater, surface water, process water, and other low UV transmittance liquids.

Validated performance for applications from water to water reuse

LBX systems have been extensively tested to meet the U.S. Environmental Protection Agency's UV Disinfection Guidance Manual (USEPA's UVDGM 2006) and the National Water Research Institute (NWRI) guidelines, including the most stringent California Title-22 Water Reuse standards. The extensive validation envelope allows for proven disinfection performance over a wide range of UV transmittance (UVT) and a variety of target organisms including Adenovirus.

Highest efficiency and adaptability for various municipal and industrial treatment schemes

For improved economy and maximum sustainability LBX units employ Wedeco's low-pressure, high-output (LoHi) amalgam Ecoray® UV lamps. With numerous sizes for a wide range of flow rates and extensive options including alternative flange connectors and reactor shapes, cabinet types, various control modes, chemical free wiping system, and SCADA communications, the LBX Series is easily customizable to match specific site requirements.



Reduce Costs

The automatic wiping system maintains maximum sleeve transmittance resulting in peak efficiency. By keeping the sleeves clean, the system uses less energy and lowers operational costs.


Save Energy

UV sensor-based OptiDose™ closed-loop UV control allows energy savings up to 20% by adjusting the output to match water quality and flow in real-time. This avoids over dosage and reduces overall operating cost without compromising disinfection performance.



Simplify Operation

The unique EcoTouch controller unifies all sensor signals, alarms, SCADA connectivity, and OptiDose closed loop control to maximize operator usability.



Improve Performance

Exclusive Ecoray Technology perfectly matches UV lamps and ballasts to deliver the highest efficiency, longer lamp life, shorter warm-up time and excellent dimming mode properties to do the job. More stable and sustainable by reduced mercury content, Ecoray lamps are an environmentally friendly choice that can help reduce your carbon footprint.



Maximize Flexibility

Alternative shapes and flanges maximize the flexibility to fit in site-specific arrangements. L shape units also feature the patented OptiCone flow diverter that optimizes hydraulics no matter of inlet piping conditions.

WEDECO LBX Series FLEXIBLE SOLUTIONS TO FIT YOUR SPECIFIC NEEDS

LBX Series - System Specification												
Model #	10	20	33	90e	120e	200e	400e	550e	850e	1000e	1500e	
Standards	CE			CE, UL, cUL								
UV Transmittance	20 - 98											
Flow Rate (m³/h / GPM)**	10.2 / 45	21.7 / 96	29.3 / 129	83 / 365	127 / 559	216 / 951	347 / 1528	536 / 2360	717 / 3157	911 / 4011	1346 / 5926	
Bioassay Tested	N/A			Yes *	N/A		Yes *	N/A	Yes *			
UV Lamps and Monitoring System												
Power Per Lamp (W) Approx.	80			315								
Number of UV Lamps	3	6	8	4	6	10	16	24	32	40	60	
Lamp Certification	N/A			3 rd Party on Aging and UV-C Output								
UV Intensity Monitoring	Germicidal, ÖNORM Compliant											
Dose Pacing (Variable Power)	N/A			Optional								
Individual Lamp Monitoring	Yes											
UV Reactor												
Protection Class	IP 65			IP 65 / NEMA 4X								
Automatic Wiping System	Optional											
Reactor Material	Stainless Steel 1.4404 / 1.4435 (ASTM 316L)											
Flange Sizes	DN 50	DN 80		DN 150 / ANSI 6"		DN 200 / ANSI 8"	DN 250 / ANSI 10"	DN 300 / ANSI 12"	DN 400 / ANSI 16"		DN 500/ ANSI 20"	
Reactor Shape				U or Z						L	U or Z	L
Reactor Length (MM / Inch) Approx.	930 / 37			1530 / 60		1540 / 61			2400 / 95			
Operating Pressure (Bar/PSI), Max.	16 / 232			16 / 232	10 / 145							
UV System Contol Cabinet												
Controller	Microprocessor			EcoTouch or PLC								
Common Outputs	System Status, Lamp Status, Alarm Messages, Process Values											
Bus Communication	N/A			Yes								
Protection Class	IP 54			IP 54 / cUL Type 12 (4X Optional)								
Supply Voltage (V / V / Hz)	230 V / 50 - 60 Hz (TN-S-net, TN-C-net)			CE: 400/230 +/- 10%, 50 Hz (TN-S Net) cUL: 480/277 +/- 10%, 60 Hz (5 Wire WYE; L1,L2,L3,N,GND)								
Power Consumption (kW) Approx.	0.34	0.6	0.76	1.72	2.38	3.7	5.69	8.33	11.19	13.84	20.57	

* Compliant with NWRI and UVDGM protocol

** UV Dose according to the "point source summation" method: 40 mJ/cm²; UVT = 65% per 1 cm at the end of the lamp lifetime.



Regional Head Office
 Xylem Water Solutions Singapore Pte Ltd
 6 Wan Lee Road, Singapore 627937
 Email asia@xylem.com
 Tel. +65 6507 6999
 Fax +65 6507 6992
asia.xylem.com

Wedeco is a brand of Xylem, whose 12,000 employees are addressing the most complex issues in the global water market.

© 2014 Xylem, Inc. All rights reserved. Wedeco is a trademark of Xylem Inc. or one of its subsidiaries.