


SPECIFICATION

AWWA M11

HARNESS ASSEMBLY



APPLICATIONS

- **Typical Uses**
 - Restraining steel pipe joints
- **Standard Pipe Sizes**
 - 6" – 144"
- **Type of Pipe**
 - Steel
- **Design Pressure**
 - 50, 100, 150, 200, and 250 psi. Higher pressure design available upon request.

MATERIALS

- **M11 Harness**
 - Carbon Steel per ASTM A36 or equivalent
 - Flexi-Coat® fusion bonded epoxy finish, if part of a fabricated assembly
 - Shop Coat Primer for field welding or bare upon request, if loose
- **Rod**
 - High Strength Low Alloy (HSLA) Steel per ASTM A193 GR B7
 - Threaded stud size and quantity specified by threaded stud material and pressure
 - Rolled threads for improved physical characteristics, greater thread accuracy, and smooth surface finish
- **Nut**
 - HSLA Steel per ASTM A194 GR 2H
 - Heavy Hex Semi-Finished

LISTINGS/STANDARDS

- Designed and fabricated per latest edition of AWWA M11 manual
- Flexi-Coat® Fusion-Bonded Epoxy Coating meets requirements of AWWA C213

OPTIONS

- Other materials of construction (e.g. 304SS, 316SS, etc.)
- Type 304 Stainless Steel hardware per ASTM A193 GR B8 and A194 GR 8
- Type 316 Stainless Steel hardware per ASTM A193 GR B8M and A194 GR 8M
- Custom rod lengths



SPECIFICATION

AWWA M11

HARNESS ASSEMBLY

NOTES

- Flexi-Coat® is a registered trademark of Smith-Blair
- These product specifications were correct at the time of publication and are subject to change without notice
- See the Smith-Blair® website for part numbers and ordering information
- See the Smith-Blair® website for warranty information
- See the Smith-Blair® website for corrosion warnings

30 Globe Ave, Texarkana, AR 71854
Ph: 870-773-5127 • Fax: 870-773-5212
Toll-Free Numbers: Ph: 800-643-9705 • Fax: 800-648-6792

