

BrazePak BPDC425


DUAL CIRCUIT BRAZED PLATE HEAT EXCHANGER



BrazePak BPDC425 dual circuit braze plate exchangers offer true two independent refrigerant circuit performance. An engineered plate configuration allows for two separate refrigerant circuits to operate with one common process circuit while maintaining performance during part load operation.

FEATURES

- **True dual circuit construction** for operation with two independent refrigerant circuits.
- **Facilitates operation at partial load** with only one compressor running maximizing performance.
- **Engineered plate technology** uniformly distributes fluid across the heat transfer surface area optimizing performance and minimizing flow maldistribution.
- **Customized distribution device** based on refrigerant to ensure proper distribution of flow.
- **Suitable for use with all modern refrigerants**



Standard **Xchange**
a xylem brand

BrazePak BPDC425 Dual circuit brazed plate heat exchanger

Standard Design Data

Maximum design pressure	435, 650 psig options
Maximum design temperature	450F
Minimum number of plates	10
Maximum number of plates	200
Maximum tonnage	60 tons
Flow arrangement	Parallel

Options


Mounting	Studs or tabs
Connections	NPT/sweat/SAE
Connection location	Front and back

Standard Material

Plates	Stainless Steel 316
Braze alloy	Copper
Connections	Stainless Steel 316
Cover plates	Stainless Steel 316

Codes

UL	Standard
CRN	Standard
ASME code	Optional
EU PED	Optional



NOTE:

1. Dimensions shown in inches (in.)



Xylem Inc.
 175 Standard Parkway
 Cheektowaga, NY 14227
 Phone: (800) 447-7700
 FAX: (716) 862-4176
www.xylem.com/standardxchange

Xylem and Standard Xchange are trademarks or registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.

© 2023 Xylem Inc. SX-BZPDC27-SS-120056 R1 August 2023