

70E/70M Pressure Booster Systems

TECHNOLOGIC CONSTANT SPEED PUMP CONTROL PANEL FOR PRESSURE BOOSTING APPLICATIONS

STANDARD FEATURES


- Exclusive Microprocessor Design
- Internal Diagnostics
- Log Menu
- On-Screen Help Function
- Integral, Fused 24 Volt Power Supply
- Exclusive Analog Inputs with overvoltage protection
- Remote Alarm Indication
- NEMA 1 Enclosure
- UL Listed
- cUL or CSA Certified
- No Flow Shut Down
- Visual Alarm Messages
 - High and Low Suction Pressure Alarms
 - High and Low System Pressure Alarms
 - High Temperature Alarm
 - Overload Failure Alarm
- Automatic or Manual Operation
- User Selectable Pump Staging by:
 - kW (True Power)
 - Amps (RMS)
 - Flow (GPM) (flow sensor reqd.)
 - Pressure (PSI)
- kW and Amp Transducer with On-Board Calibration
- Elapsed Time Meters
- Virtual H-O-A Switches
- Control Power Transformer
- Ambient Environmental Ratings:
 - Temperature: 0°C to 50°C
 - Humidity: 10% to 90%, non-condensing
- IEC Magnetic Starters with Integral Overload Protection
- Short Circuit Protection for Each Pump
- Remote Pump Run Indication
- Remote Start/Stop
- Manual and Automatic Pump Alternation
- "EZ" Start through Quick Setup
- Real Time Clock
- Scheduled Start/Stop of System
- Pump Exercise
- Parameter Backup through Save and Load Menu
- Serial Communication with RS-485 Port Allows BACnet MS/TP, Johnson Controls Metasys N2, or Modicon Modbus Protocols. LonWorks shall be provided through RS-232 port.



OPTIONAL FEATURES

- NEMA 12 Rated Enclosure
- NEMA 4 Rated Enclosure
- Low Water Level Cutout with Alarm
- High Water Level Cutout with Alarm
- Differential Pressure Switches (for pump failure indication)
- NEMA Starters
- Flow Meter (for staging to flow or for display)
- Phase Monitoring
- 4-6 Pump System

DIMENSIONAL DATA



TECHNOLOGIC	
H	36"
W	30"
D	9"
WT.	180 lbs. Maximum

Consult factory for systems larger than 3 pumps and above 140 total amps.

Pump Logic Controller

The Technologic microprocessor, programmable, constant speed pump logic controller shall be provided by Xylem Bell & Gossett. The controller shall be specifically designed for constant speed pressure boosting applications.

The controller shall function to a proven program that safeguards against potentially damaging electrical and hydraulic conditions including:

- motor overload
- low and high suction pressure
- low and high system pressure
- pump failure
- low suction water level
- no flow
- high system temperature

The entire pump logic controller assembly shall be listed and bear the label of a nationally recognized test lab. The pump logic controller shall be listed and shall bear the label of Underwriters Laboratories (UL), cUL or CSA.

The pump logic controller shall be microcomputer based and hold its software in non-volatile memory. On-line field modified data entries, such as stage point, or method of staging, shall be stored in flash memory with capability to prevent accidental loss of data due to voltage surge or spike. In the event of a complete power outage, all factory preset data values remain stored and available for recall by the operator.

The pump logic controller shall be powered by 115V AC power from a control power transformer within the control enclosure. The control panel shall be equipped with an integral, regulated 24VDC power supply to power analog input signals. The Pump Logic Controller shall be capable of receiving four 4-20 mA analog input signals and two RTD signals.

The staging of pumps shall be user-selectable based on kilowatts (kW), current (Amps), flow (GPM) or pressure (PSI).

kW shall be true power derived from a B&G transducer. Amps shall be RMS from the kW transducer. Both kW and Amps shall be micro-controller calibrated with calibration held in non-volatile memory. PSI shall be derived from a B&G supplied pressure transducer with a 4-20 mA analog input. Optional flow shall be derived from a B&G supplied and calibrated transducer with a 4-20 mA analog input.

The control enclosure shall conform to NEMA 1 requirements and it shall include motor starters, overloads, control power transformer and microprocessor with NEMA 4 rated operator interface.

The pump logic controller shall alternate the pumps automatically based on a user defined time period, scheduled, manually from the operator interface, or via serial interface.

The Technologic controller shall have off line and on line diagnostic software. Off line diagnostics shall consist of CPU, non-volatile and RAM memory test. The controller shall have digital input diagnostics, display test, and all analog and digital I/O user-tests. Fault information may be accessed by interrogating the pump logic controller through its HELP key.

The pump logic controller shall be powered by 115V/1Ph/60Hz or 50Hz power. The incoming power and I/O circuitry shall reject electromagnetic (EMI) and radio frequency interference (RFI). All digital outputs shall be externally isolated.

The pump controller shall be capable of operation in ambient conditions of 0°C to 50°C and a humidity range of 10% to 90%, non-condensing.

All external sensors/transmitters and switches shall be powered by the pump logic controller through its integral 24VDC power supply. Over-voltage and short circuit protection shall be on-board. All analog inputs shall be provided with current limit circuitry to provide short circuit protection and safeguard against incorrect wiring of sensors.

The pump logic controller shall operate the pump(s) in a pre-determined manner as indicated in the Sequence of Operation.

The controller's user interface shall contain a 4 line x 20 character liquid crystal display with 1/4" characters.

The pump logic controller shall be capable of operating in automatic, manual or off-line diagnostic modes. One level of password and software security shall be provided for protection of field modifiable data.

A data-logging feature provides historical information of key events with date and time stamps. Log information includes alarms, pump run timers, system on/off timers and pump cycle counters. The data log displays the minimum, maximum and average values of temperature, pressure and flow. It is also capable of displaying kilowatt-hours.

The pump controller shall be capable of communicating with the Building Automation System (BAS) by both hardwired and serial communications. The following communication features shall be provided to the BAS in hardwired form via digital outputs:

- Remote system start/stop
- System alarm output
- Pump on/off status indication
- Auto/manual status indication

The following communication features shall be provided to the Building Automation System via an RS-485 port utilizing BACnet MS/TP, Johnson Controls Metasys N2, or Modicon Modbus protocols. LonWorks shall be provided through RS-232 port.

1. Individual analog inputs
2. Individual pump failure
3. Individual pump on/off status
4. Start/Stop command and status
5. System flow when optional flow sensor is provided
6. Pressure, Temperature, Power measurement
7. General alarm indication
8. No flow shutdown status
9. Pump alternation

The pump logic controller shall provide the following standard user-selectable features:

- low suction pressure alarm and cut out
- high suction pressure alarm and cut out
- low system pressure alarm
- high system pressure alarm and cut out
- visual alarm messages
- no-flow shut down
- pump failure alarm
- high temperature alarm and cut out
- low level alarm and cut out
- overload failure alarm
- automatic and manual alternation



Xylem Inc.
8200 N. Austin Avenue
Morton Grove, Illinois 60053
Phone: (847) 966-3700
Fax: (847) 965-8379
www.xyleminc.com/brands/bellgossett

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2012 Xylem Inc. D-216B Marxh 2008