


<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



# Model VSH 18x20x22B Double Suction Split Case Pump



**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**STANDARD MATERIALS OF CONSTRUCTION**

- Cast Ductile Iron, Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling (Less Than 1500 HP)


- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance

**OPTIONAL MATERIALS OF CONSTRUCTION**


- Galvanized Drip Pan
- Spacer Coupling

**TYPE OF SEAL AND WORKING PRESSURE**

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Balanced mechanical seal, EPR/Graphite loaded Silicon on Graphite loaded Silicon, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)



<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



# Model VSH 18x20x22B Double Suction Split Case Pump



**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**STANDARD MATERIALS OF CONSTRUCTION**


- Cast Ductile Iron, Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling (Less Than 1500 HP)
- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance

**OPTIONAL MATERIALS OF CONSTRUCTION**


- Galvanized Drip Pan
- Spacer Coupling

**TYPE OF SEAL AND WORKING PRESSURE**

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Balanced mechanical seal, EPR/Graphite loaded Silicon on Graphite loaded Silicon, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)



<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



# Model VSH

## 18x20x22B

### Double Suction Split Case Pump



**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_

HP \_\_\_\_\_ RPM \_\_\_\_\_

VOLTS \_\_\_\_\_

CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_

ENCLOSURE \_\_\_\_\_

APPROX. WEIGHT \_\_\_\_\_

SPECIALS \_\_\_\_\_

**STANDARD MATERIALS OF CONSTRUCTION**

- Cast Ductile Iron, Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling (Less Than 1500 HP)


- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance

**OPTIONAL MATERIALS OF CONSTRUCTION**


- Galvanized Drip Pan
- Spacer Coupling

**TYPE OF SEAL AND WORKING PRESSURE**

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Balanced mechanical seal, EPR/Graphite loaded Silicon on Graphite loaded Silicon, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)



<b>JOB:</b>	<b>REPRESENTATIVE:</b>	
<b>UNIT TAG:</b>	<b>ORDER NO.</b>	<b>DATE:</b>
<b>ENGINEER:</b>	<b>SUBMITTED BY:</b>	<b>DATE:</b>
<b>CONTRACTOR:</b>	<b>APPROVED BY:</b>	<b>DATE:</b>



# Model VSH

## 18x20x22B

### Double Suction Split Case Pump



**SPECIFICATIONS**

FLOW \_\_\_\_\_ HEAD \_\_\_\_\_  
 HP \_\_\_\_\_ RPM \_\_\_\_\_  
 VOLTS \_\_\_\_\_  
 CYCLE \_\_\_\_\_ PHASE \_\_\_\_\_  
 ENCLOSURE \_\_\_\_\_  
 APPROX. WEIGHT \_\_\_\_\_  
 SPECIALS \_\_\_\_\_

**STANDARD MATERIALS OF CONSTRUCTION**

- Cast Ductile Iron, Bronze Fitted
- Heavy Duty Maintenance Free Bearings
- Alignment Friendly Coupling (Less Than 1500 HP)


- Heavy Duty Groutless Baseplate
- ANSI/OSHA Coupling Guard
- ISO 1940-1:2003 Impeller Balance


**OPTIONAL MATERIALS OF CONSTRUCTION**

- Galvanized Drip Pan
- Spacer Coupling

**TYPE OF SEAL AND WORKING PRESSURE**

- Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Balanced mechanical seal, EPR/Graphite loaded Silicon on Graphite loaded Silicon, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)





FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	18"	2.57 (65)	27.5 (699)
Suction	20"	2.69 (68)	30 (762)

FLANGES ARE 125# ANSI - STANDARD  
250# ANSI - AVAILABLE

DIMENSIONS IN INCHES (MM)		
S	X	Z
17 (432)	34 (864)	17 (432)

Removal clearance from end  
of bracket: 47 Inches (1194 mm)

**STANDARD COUPLER**

**Motors weighing over 5,000 lbs. will be shipped separate and unmounted.**

\*Motor dimensions are approximate and vary by manufacturer and motor type.

\*\*\*Distance to the next available hole.

For all customers supplied motors above 449 NEMA frame, a certified motor drawing must be supplied by the customer at time of order entry. Submittal dimensions for motor frames above 449 NEMA are specific to ODP U.S. Electric Motors only.


MOTOR FRAME	DIMENSIONS - INCHES (mm) FOR STANDARD COUPLER															
	CP	HA	HB	HC*	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub> ***	HG	HH	HM*	HO	HP	HQ	HR	W
447T/TS	66.95 (1701)	53 (1346)	107.5 (2731)	119.81 (3043)	42.13 (1070)	50 (1270)	97.5 (2477)	24.375 (619)	9.38 (238)	1.375 (35)	56.01 (1423)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
449T/TS	66.95 (1701)	53 (1346)	107.5 (2731)	120.51 (3061)	42.13 (1070)	50 (1270)	97.5 (2477)	24.375 (619)	9.38 (238)	1.375 (35)	56.01 (1423)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
449TM**	66.95 (1701)	53 (1346)	107.5 (2731)	120.51 (3061)	42.13 (1070)	50 (1270)	97.5 (2477)	24.375 (619)	9.38 (238)	1.375 (35)	56.01 (1423)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
5010S**	66.95 (1701)	53 (1346)	123.5 (3137)	123.83 (3145)	42.13 (1070)	50 (1270)	113.5 (2883)	28.375 (721)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
5010MS**	66.95 (1701)	53 (1346)	123.5 (3137)	122.83 (3120)	42.13 (1070)	50 (1270)	113.5 (2883)	28.375 (721)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
5012S**	66.95 (1701)	53 (1346)	123.5 (3137)	131.83 (3348)	42.13 (1070)	50 (1270)	113.5 (2883)	28.375 (721)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
5012MS**	66.95 (1701)	53 (1346)	123.5 (3137)	130.83 (3323)	42.13 (1070)	50 (1270)	113.5 (2883)	28.375 (721)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
5810M**	66.95 (1701)	55 (1397)	137 (3480)	131.83 (3349)	44.13 (1121)	52 (1321)	127 (3226)	25.4 (645)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5811M**	66.95 (1701)	55 (1397)	137 (3480)	135.83 (3450)	44.13 (1121)	52 (1321)	127 (3226)	25.4 (645)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5812M**	66.95 (1701)	55 (1397)	137 (3480)	140.83 (3577)	44.13 (1121)	52 (1321)	127 (3226)	25.4 (645)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5813M**	66.95 (1701)	55 (1397)	137 (3480)	145.83 (3704)	44.13 (1121)	52 (1321)	127 (3226)	25.4 (645)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
6811S**	66.95 (1701)	55 (1397)	136 (3454)	148.33 (3768)	44.13 (1121)	52 (1321)	126 (3200)	25.2 (640)	11.38 (289)	1.375 (35)	61.26 (1556)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
6811MS**	66.95 (1701)	55 (1397)	136 (3454)	148.33 (3768)	44.13 (1121)	52 (1321)	126 (3200)	25.2 (640)	11.38 (289)	1.375 (35)	61.26 (1556)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
8009S**	66.95 (1700.53)	55 (1397)	148 (3759)	155.33 (3945)	44.13 (1121)	52 (1321)	138 (3505)	27.6 (701)	11.38 (289)	1.375 (35)	99.51 (2528)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
8010S**	66.95 (1701)	55 (1397)	148 (3759)	161.33 (4098)	44.13 (1121)	52 (1321)	138 (3505)	27.6 (701)	11.38 (289)	1.375 (35)	99.51 (2528)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5807S**	66.95 (1700.53)	53 (1346.2)	124 (3149.6)	126.45 (3212)	42.13 (1070)	50 (1270)	114 (2896)	28.5 (724)	9.38 (238.252)	1.375 (34.925)	57.69 (1465)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.19 (944.626)
5809S**	66.95 (1700.53)	53 (1346.2)	124 (3149.6)	133.45 (3390)	42.13 (1070)	50 (1270)	114 (2896)	28.5 (724)	9.38 (238.252)	1.375 (34.925)	57.69 (1465)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.19 (944.626)
5811S**	66.95 (1700.53)	53 (1346.2)	124 (3149.6)	141.45 (3593)	42.13 (1070)	50 (1270)	114 (2896)	28.5 (724)	9.38 (238.252)	1.375 (34.925)	57.69 (1465)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.19 (944.626)
5811+M**	66.95 (1700.53)	55 (1397)	137 (3479.8)	153.39 (3896)	44.13 (1121)	52 (1320.8)	127 (3226)	25.4 (645)	11.38 (289.052)	1.375 (34.925)	112.26 (2851)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)
5812+M**	66.95 (1700.53)	55 (1397)	137 (3479.8)	158.39 (4023)	44.13 (1121)	52 (1320.8)	127 (3226)	25.4 (645)	11.38 (289.052)	1.375 (34.925)	112.26 (2851)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.375)
5813+M**	66.95 (1700.53)	55 (1397)	137 (3479.8)	163.39 (4150)	44.13 (1121)	52 (1320.8)	127 (3226)	25.4 (645)	11.38 (289.052)	1.375 (34.925)	112.26 (2851)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)
8008S+**	66.95 (1700.53)	55 (1397)	148 (3759.2)	171.14 (4347)	44.13 (1121)	52 (1320.8)	138 (3505)	27.6 (701)	11.38 (289.052)	1.375 (34.925)	121.01 (3074)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)
8009S+**	66.95 (1700.53)	55 (1397)	148 (3759.2)	176.14 (4474)	44.13 (1121)	52 (1320.8)	138 (3505)	27.6 (701)	11.38 (289.052)	1.375 (34.925)	121.01 (3074)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)

\*\*US Electric Motors Only

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Units may be built where foot/feet overhang the motor mounting platform. If overhang is unacceptable, consult factory for a custom submittal, quotation and/or lead time. A certified motor drawing will be required.





FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	18"	2.57 (65)	27.5 (699)
Suction	20"	2.69 (68)	30 (762)

FLANGES ARE 125# ANSI - STANDARD  
250# ANSI - AVAILABLE

DIMENSIONS IN INCHES (MM)		
S	X	Z
17 (432)	34 (864)	17 (432)

Removal clearance from end of bracket: 47 Inches (1194 mm)

**SPACER COUPLER**

**Motors weighing over 5,000 lbs. will be shipped separate and unmounted.**

\* Motor dimensions are approximate and vary by manufacturer and motor type.

\*\*\* Distance to the next available hole.

For all customers supplied motors above 449 NEMA frame, a certified motor drawing must be supplied by the customer at time of order entry. Submittal dimensions for motor frames above 449 NEMA are specific to ODP U.S. Electric Motors only.

MOTOR FRAME	DIMENSIONS - INCHES (mm) FOR SPACER COUPLER****															
	CP	HA	HB	HC*	HD	2HE	HF <sub>1</sub>	HF <sub>2</sub> ***	HG	HH	HM*	HO	HP	HQ	HR	W
447T/TS	66.95 (1701)	53 (1346)	122.5 (3112)	134.81 (3424)	42.13 (1070)	50 (1270)	112.5 (2858)	28.125 (714)	9.38 (238)	1.375 (35)	56.01 (1423)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
449T/TS	66.95 (1701)	53 (1346)	122.5 (3112)	135.51 (3442)	42.13 (1070)	50 (1270)	112.5 (2858)	28.125 (714)	9.38 (238)	1.375 (35)	56.01 (1423)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
449TM**	66.95 (1701)	53 (1346)	122.5 (3112)	135.51 (3442)	42.13 (1070)	50 (1270)	112.5 (2856)	28.125 (714)	9.38 (238)	1.375 (35)	56.01 (1423)	62.38 (1584)	5 (127)	5 (508)	20 (508)	37.18 (944)
5010S**	66.95 (1701)	53 (1346)	138.5 (3518)	139.33 (3539)	42.13 (1070)	50 (1270)	128.5 (3264)	25.7 (653)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.18 (944)
5010MS**	66.95 (1701)	53 (1346)	138.5 (3518)	138.33 (3514)	42.13 (1070)	50 (1270)	128.5 (3264)	25.7 (653)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.18 (944)
5012S**	66.95 (1701)	53 (1346)	138.5 (3518)	147.33 (3742)	42.13 (1070)	50 (1270)	128.5 (3264)	25.7 (653)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.18 (944)
5012MS**	66.95 (1701)	53 (1346)	138.5 (3518)	146.33 (3717)	42.13 (1070)	50 (1270)	128.5 (3264)	25.7 (653)	9.38 (238)	1.375 (35)	56.63 (1438)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.18 (944)
5810M**	66.95 (1701)	55 (1397)	152 (3861)	146.83 (3730)	44.13 (1121)	52 (1321)	142 (3607)	28.4 (721)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5811M**	66.95 (1701)	55 (1397)	152 (3861)	150.83 (3831)	44.13 (1121)	52 (1321)	142 (3607)	28.4 (721)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5812M**	66.95 (1701)	55 (1397)	152 (3861)	155.83 (3958)	44.13 (1121)	52 (1321)	142 (3607)	28.4 (721)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
5813M**	66.95 (1701)	55 (1397)	152 (3861)	160.83 (4085)	44.13 (1121)	52 (1321)	142 (3607)	28.4 (721)	11.38 (289)	1.375 (35)	60.69 (1542)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944)
6811S**	66.95 (1701)	55 (1397)	151 (3835)	163.33 (4149)	44.13 (1121)	52 (1321)	141 (3581)	23.5 (597)	11.38 (289)	1.375 (35)	61.26 (1556)	64.38 (1635)	5 (127)	7 (508)	20 (508)	37.18 (944)
6811MS**	66.95 (1701)	55 (1397)	151 (3835)	163.33 (4149)	44.13 (1121)	52 (1321)	141 (3581)	23.5 (597)	11.38 (289)	1.375 (35)	61.26 (1556)	64.38 (1635)	5 (127)	7 (508)	20 (508)	37.18 (944)
8009S**	66.95 (1701)	55 (1397)	163 (4140)	170.33 (4326)	44.13 (1121)	52 (1321)	153 (3886)	25.5 (648)	11.38 (289)	1.375 (35)	99.51 (2528)	64.38 (1635)	5 (127)	7 (508)	20 (508)	37.18 (944)
8010S**	66.95 (1701)	55 (1397)	163 (4140)	176.33 (4479)	44.13 (1121)	52 (1321)	153 (3886)	25.5 (648)	11.38 (289)	1.375 (35)	99.51 (2528)	64.38 (1635)	5 (127)	7 (508)	20 (508)	37.18 (944)
5807S**	66.95 (1700.53)	53 (1346.2)	139 (3530.6)	141.45 (3593)	42.13 (1070)	50 (1270)	129 (3277)	25.8 (655)	9.38 (238.252)	1.375 (34.925)	57.69 (1465)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.19 (944.626)
5809S**	66.95 (1700.53)	53 (1346.2)	139 (3530.6)	148.45 (3771)	42.13 (1070)	50 (1270)	129 (3277)	25.8 (655)	9.38 (238.252)	1.375 (34.925)	57.69 (1465)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.19 (944.626)
5811S**	66.95 (1700.53)	53 (1346.2)	139 (3530.6)	156.45 (3974)	42.13 (1070)	50 (1270)	129 (3277)	25.8 (655)	9.38 (238.252)	1.375 (34.925)	57.69 (1465)	62.38 (1584)	5 (127)	6 (508)	20 (508)	37.19 (944.626)
5811+M**	66.95 (1700.53)	55 (1397)	152 (3860.8)	168.39 (4277)	44.13 (1121)	52 (1320.8)	142 (3607)	28.4 (721)	11.38 (289.052)	1.375 (34.925)	112.26 (2851)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)
5812+M**	66.95 (1700.53)	55 (1397)	152 (3860.8)	173.39 (4404)	44.13 (1121)	52 (1320.8)	142 (3607)	28.4 (721)	11.38 (289.052)	1.375 (34.925)	112.26 (2851)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)
5813+M**	66.95 (1700.53)	55 (1397)	152 (3860.8)	178.39 (4531)	44.13 (1121)	52 (1320.8)	142 (3607)	28.4 (721)	11.38 (289.052)	1.375 (34.925)	112.26 (2851)	64.38 (1635)	5 (127)	6 (508)	20 (508)	37.18 (944.372)
8008S**	66.95 (1700.53)	55 (1397)	163 (4140.2)	186.14 (4728)	44.13 (1121)	52 (1320.8)	153 (3886)	25.50 (648)	11.38 (289.052)	1.375 (34.925)	121.01 (3074)	64.38 (1635)	5 (127)	7 (508)	20 (508)	37.18 (944.372)
8009S**	66.95 (1700.53)	55 (1397)	163 (4140.2)	191.14 (4855)	44.13 (1121)	52 (1320.8)	153 (3886)	25.50 (648)	11.38 (289.052)	1.375 (34.925)	121.01 (3074)	64.38 (1635)	5 (127)	7 (508)	20 (508)	37.18 (944.372)

\*\* US Electric Motors Only

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Units may be built where foot/feet overhang the motor mounting platform. If overhang is unacceptable, consult factory for a custom submittal, quotation and/or lead time. A certified motor drawing will be required.

\*\*\*\* These dimensions are valid when using the Woods Duraflex (up to 1000HP @ 1780 RPM), or Dodge Paraflex (up to 700HP at 1780 RPM) spacer coupling option. For dimensions on Falk SteelFlex coupling options, consult factory for a special submittal drawing.

