

JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



Model VSC 4x6x13¹/₂A Double Suction Split Case Pump



SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

STANDARD MATERIALS OF CONSTRUCTION


- ☒ Cast Iron Bronze Fitted
- ☒ Heavy Duty Maintenance Free Bearings
- ☒ Alignment Friendly Coupling
- ☒ Heavy Duty Groutless Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ ISO 1940-1:2003 Impeller Balance

OPTIONAL MATERIALS OF CONSTRUCTION

- ☐ Galvanized Drip Pan
- ☐ Spacer Coupling

TYPE OF SEAL AND WORKING PRESSURE

- ☐ **Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- ☐ **Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 200 PSIG (13.7 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- ☐ **Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)



JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



Model VSC 4x6x13¹/₂A Double Suction Split Case Pump



SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

STANDARD MATERIALS OF CONSTRUCTION


- ☒ Cast Iron Bronze Fitted
- ☒ Heavy Duty Maintenance Free Bearings
- ☒ Alignment Friendly Coupling
- ☒ Heavy Duty Groutless Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ ISO 1940-1:2003 Impeller Balance

OPTIONAL MATERIALS OF CONSTRUCTION

- ☐ Galvanized Drip Pan
- ☐ Spacer Coupling

TYPE OF SEAL AND WORKING PRESSURE

- ☐ **Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- ☐ **Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 200 PSIG (13.7 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- ☐ **Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)



JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



Model VSC 4x6x13¹/₂A Double Suction Split Case Pump



SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

STANDARD MATERIALS OF CONSTRUCTION


- ☒ Cast Iron Bronze Fitted
- ☒ Heavy Duty Maintenance Free Bearings
- ☒ Alignment Friendly Coupling
- ☒ Heavy Duty Groutless Baseplate
- ☒ ANSI/OSHA Coupling Guard
- ☒ ISO 1940-1:2003 Impeller Balance


OPTIONAL MATERIALS OF CONSTRUCTION

- ☐ Galvanized Drip Pan
- ☐ Spacer Coupling

TYPE OF SEAL AND WORKING PRESSURE

- ☐ **Standard:** 175 PSIG (12 BAR) max. working pressure, flat face flanges, 125# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 175 PSIG (12 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- ☐ **Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, Unitized mechanical seal, EPR/Carbon/Silicon Carbide, 200 PSIG (13.7 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)
- ☐ **Optional:** 300 PSIG (20 BAR) max. working pressure, flat face flanges, 250# ANSI flange drilling, balanced mechanical seal, EPR/Graphite loaded Silicon Carbide on Graphite loaded Silicon Carbide, 300 PSIG (20 BAR) max. suction pressure, 0 to 300°F (-18 to 149°C)






FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	4"	1.50 (38)	10 (254)
Suction	6"	1.69 (43)	12.13 (308)

FLANGES ARE 125# ANSI - STANDARD
250# ANSI - AVAILABLE

DIMENSIONS IN INCHES (MM)		
S	X	Z
9.5 (241)	16 (406)	9.5 (241)

Removal clearance from end
of bracket: 19 Inches (483 mm)

STANDARD COUPLER



*Motor dimensions are approximate and vary by manufacturer and motor type.

**Distance to the next available hole.

MOTOR FRAME	DIMENSIONS - INCHES (mm) FOR STANDARD COUPLER															
	CP	HA	HB	HC*	HD	2HE	HF ₁	HF ₂ **	HG	HH	HM*	HO	HP	HQ	HR	W
215T	34.48 (876)	25.4 (645)	61 (1549)	55.925 (1420)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	29.97 (761)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
254T	34.48 (876)	25.4 (645)	61 (1549)	58.495 (1486)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
256T	34.48 (876)	25.4 (645)	61 (1549)	60.245 (1530)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
284T/TS	34.48 (876)	25.4 (645)	61 (1549)	61.408 (1560)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
286T/TS	34.48 (876)	25.4 (645)	61 (1549)	62.904 (1598)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
324T/TS	34.48 (876)	25.4 (645)	61 (1549)	65.725 (1669)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	30.57 (776)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
326T/TS	34.48 (876)	25.4 (645)	61 (1549)	66.845 (1698)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	31.1 (790)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
364T/TS	34.48 (876)	25.4 (645)	61 (1549)	68.684 (1745)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	31.95 (812)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)
365T/TS	34.48 (876)	25.4 (645)	61 (1549)	68.684 (1745)	22 (559)	23.52 (597)	51 (1295)	17 (432)	5.25 (133)	0.88 (22)	31.95 (812)	38 (965)	5 (127)	4	7.63 (194)	18.925 (481)


Dimensions are subject to change. Not to be used for construction purposes unless certified.

Units may be built where foot/feet overhang the motor mounting platform. If overhang is unacceptable, consult factory for a custom submittal, quotation and/or lead time. A certified motor drawing will be required.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.bellgossett.com

xylem
Let's Solve Water

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2013 Xylem Inc.




FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	4"	1.50 (38)	10 (254)
Suction	6"	1.69 (43)	12.13 (308)

FLANGES ARE 125# ANSI - STANDARD
250# ANSI - AVAILABLE

DIMENSIONS IN INCHES (MM)		
S	X	Z
9.5 (241)	16 (406)	9.5 (241)

Removal clearance from end
of bracket: 19 Inches (483 mm)

SPACER COUPLER



*Motor dimensions are approximate and vary by manufacturer and motor type.

**Distance to the next available hole.

MOTOR FRAME	DIMENSIONS - INCHES (mm) FOR SPACER COUPLER															
	CP	HA	HB	HC*	HD	2HE	HF ₁	HF ₂ **	HG	HH	HM*	HO	HP	HQ	HR	W
215T	34.48 (876)	25.4 (645)	70 (1778)	65.175 (1655)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	29.97 (761)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
254T	34.48 (876)	25.4 (645)	70 (1778)	67.745 (1721)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
256T	34.48 (876)	25.4 (645)	70 (1778)	69.495 (1765)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
284T/TS	34.48 (876)	25.4 (645)	70 (1778)	70.658 (1795)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
286T/TS	34.48 (876)	25.4 (645)	70 (1778)	72.154 (1833)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	29.82 (757)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
324T/TS	34.48 (876)	25.4 (645)	70 (1778)	74.975 (1904)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	30.57 (776)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
326T/TS	34.48 (876)	25.4 (645)	70 (1778)	76.095 (1933)	22 (559)	23.52 (597)	60 (1524)	15 (381)	5.25 (133)	0.88 (22)	31.1 (790)	38 (965)	5 (127)	5	7.62 (194)	18.925 (481)
364T/TS	34.48 (876)	25.4 (645)	80 (2032)	77.934 (1980)	22 (559)	23.52 (597)	72 (1829)	18 (457)	5.25 (133)	0.88 (22)	31.95 (812)	38 (965)	4 (102)	5	8.63 (219)	18.925 (481)
365T/TS	34.48 (876)	25.4 (645)	80 (2032)	77.934 (1980)	22 (559)	23.52 (597)	72 (1829)	18 (457)	5.25 (133)	0.88 (22)	31.95 (812)	38 (965)	4 (102)	5	8.63 (219)	18.925 (481)

Dimensions are subject to change. Not to be used for construction purposes unless certified.

Units may be built where foot/feet overhang the motor mounting platform. If overhang is unacceptable, consult factory for a custom submittal, quotation and/or lead time. A certified motor drawing will be required.

These dimensions are valid when using the Woods DuraFlex spacer coupling option. For dimensions on Falk SteelFlex coupling options, consult factory for a special submittal drawing.

Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847)966-3700
Fax: (847)965-8379
www.bellgossett.com

xylem
Let's Solve Water

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2013 Xylem Inc.