



Bell & Gossett
a xylem brand

SUBMITTAL
B-880.8C

JOB:

REPRESENTATIVE:

UNIT TAG:

ORDER NO.

DATE:

ENGINEER:


SUBMITTED BY:

DATE:

CONTRACTOR:

APPROVED BY:

DATE:



3AD Series e-1510 Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
HP _____ RPM _____
VOLTS _____
CYCLE _____ PHASE _____
ENCLOSURE _____
APPROX. WEIGHT _____
SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

☒ ANSI/OSHA Coupling Guard
☒ Center Drop Out Spacer Coupling
☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL

☐ Standard Seal
(Buna-Carbon/Ceramic)
☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling






Bell & Gossett
a xylem brand

SUBMITTAL

B-880.8C

JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



3AD Series e-1510 Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

☒ ANSI/OSHA Coupling Guard
☒ Center Drop Out Spacer Coupling
☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

☐ 175 psi (12 bar) W.P.
 w/ 125# ANSI flange drilling

TYPE OF SEAL

☐ Standard Seal
 (Buna-Carbon/Ceramic)
☐ -F Standard Seal w/ Flush Line
 (Buna-Carbon/Ceramic)
☐ -S Stuffing Box Construction w/ Flushed
 Mechanical Single Seal
 (EPR-Tungsten Carbide/Carbon)
☐ -PF Stuffing Box Construction w/ Packing
 (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling






Bell & Gossett
a xylem brand

SUBMITTAL
B-880.8C

JOB: UNIT TAG: ENGINEER: CONTRACTOR:	REPRESENTATIVE: ORDER NO. SUBMITTED BY: APPROVED BY:	DATE: DATE: DATE:
---	---	--



3AD

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

☒ Stainless Steel Fitted

FEATURES

- ☒ ANSI/OSHA Coupling Guard
- ☒ Center Drop Out Spacer Coupling
- ☒ Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

- ☐ 175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL


- ☐ Standard Seal
(Buna-Carbon/Ceramic)
- ☐ -F Standard Seal w/ Flush Line
(Buna-Carbon/Ceramic)
- ☐ -S Stuffing Box Construction w/ Flushed
Mechanical Single Seal
(EPR-Tungsten Carbide/Carbon)
- ☐ -PF Stuffing Box Construction w/ Packing
(Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



Series e-1510 3AD Centrifugal Pump Submittal

B-880.8C



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	3"	3/4" (19)	7-1/2" (191)
Suction	4"	15/16" (24)	9" (229)

FLANGES ARE 125# ANSI - STANDARD

DIMENSIONS – Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
56	12 (305)	28-3/4 (730)	29-1/2 (749)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	-	3/4 (19)	4-5/16 (110)	13-3/8 (340)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
143T	12 (305)	28-3/4 (730)	29-5/8 (752)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	-	3/4 (19)	4-5/16 (110)	13-1/2 (343)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
145T	12 (305)	28-3/4 (730)	30-5/8 (778)	9-3/4 (248)	10-1/4 (260)	22-1/2 (572)	-	3/4 (19)	4-5/16 (110)	13-1/2 (343)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
182T	14-5/8 (371)	31 (787)	33-3/8 (848)	9-3/4 (248)	12-7/8 (327)	25 (635)	-	3/4 (19)	4-5/16 (110)	15 (381)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
184T	14-5/8 (371)	31 (787)	34-1/8 (867)	9-3/4 (248)	12-7/8 (327)	25 (635)	-	3/4 (19)	2-15/16 (75)	15 (381)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
"L" FRAME														
215T	14-5/8 (371)	39-3/8 (1000)	42-5/8 (1083)	9-3/4 (248)	12-7/8 (327)	33-5/8 (848)	-	3/4 (19)	2-15/16 (75)	15-3/8 (397)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
254T	16 (406)	46-1/2 (1181)	46-3/8 (1178)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/16 (103)	18-7/8 (479)	18 (457)	5 (127)	4-1/8 (105)	5 (127)
256T	16 (406)	46-1/2 (1181)	48-1/8 (1222)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/16 (103)	18-7/8 (479)	18 (457)	5 (127)	4-1/8 (105)	5 (127)
284TS	16 (406)	46-1/2 (1181)	47-3/8 (1203)	13 (330)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/16 (103)	21 (533)	19 (483)	5 (127)	4-1/8 (105)	5 (127)
286TS	16 (406)	46-1/2 (1181)	48-7/8 (1203)	13 (330)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/16 (103)	21 (533)	19 (483)	5 (127)	4-1/8 (105)	5 (127)
324TS	16 (406)	46-1/2 (1181)	50-7/8 (1292)	12 (305)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/16 (103)	21 (533)	18 (457)	5 (127)	4-1/8 (105)	5 (127)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
56	14-5/8 (371)	34-5/8 (879)	33-1/8 (841)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-15/16 (75)	13-3/8 (340)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
143T	14-5/8 (371)	34-5/8 (879)	33-1/4 (845)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-15/16 (75)	13-1/2 (343)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
145T	14-5/8 (371)	34-5/8 (879)	34-1/4 (870)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-15/16 (75)	13-1/2 (343)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
182T	14-5/8 (371)	34-5/8 (879)	37 (940)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-15/16 (75)	15 (381)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
184T	14-5/8 (371)	34-5/8 (879)	37-3/4 (959)	9-3/4 (248)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	2-15/16 (75)	15 (381)	15-3/4 (400)	3 (76)	4-1/8 (105)	5 (127)
"L" FRAME														
215T	16 (406)	46-1/2 (1181)	45 (1143)	11 (279)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	4-1/16 (103)	16-7/8 (429)	17 (432)	5 (127)	4-1/8 (105)	5 (127)
254T	16 (406)	51-3/4 (1314)	48-3/4 (1238)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/16 (103)	18-7/8 (479)	18 (457)	5 (127)	4-1/8 (105)	5 (127)
256T	16 (406)	51-3/4 (1314)	50-1/2 (1283)	12 (305)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/16 (103)	18-7/8 (479)	18 (457)	5 (127)	4-1/8 (105)	5 (127)
284TS	16 (406)	51-3/4 (1314)	49-3/4 (1264)	13 (330)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/16 (103)	21 (533)	19 (483)	5 (127)	4-1/8 (105)	5 (127)
286TS	16 (406)	51-3/4 (1314)	51-1/4 (1302)	13 (330)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	4-1/16 (103)	21 (533)	19 (483)	5 (127)	4-1/8 (105)	5 (127)

Dimensions are subject to change. Not to be used for construction purposes unless certified.



Xylem Inc.
 8200 N. Austin Avenue, Morton Grove, IL 60053
 Phone: (847)966-3700 Fax: (847)965-8379
www.bellgossett.com
 Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
 © 2016 Xylem Inc.