



2WC

SUBMERSIBLE SEWAGE PUMP



Bell & Gossett

a xylem brand

FEATURES

- Corrosion resistant construction
- Cast iron body
- Thermoplastic impeller and cover
- Upper sleeve and lower heavy duty ball bearing construction.
- Motor is permanently lubricated for extended service life.
- Powered for continuous operation.
- All ratings are within the working limits of the motor.

APPLICATIONS

Specially designed for the following uses:

- Residential Sewage Systems
- Heavy-Duty Sump/Dewatering
- Water Transfer

SPECIFICATIONS

Pump - General:

- Discharge: 2" NPT
- Temperature: 104°F (40°C) maximum, continuous when fully submerged.
- Solids handling: 2" maximum sphere.
- Automatic models include a float switch.
- Manual models available.

2WC04 Pump:

- Maximum capacity: 110 GPM
- Maximum head: 23' TDH

2WC05 Pump:

- Maximum capacity: 130 GPM
- Maximum head: 27' TDH

- Quick disconnect power cord, 10' and 20' standard lengths, heavy duty 16/3 SJTW with NEMA three prong, 115 or 230 volt grounding plug.
- Complete unit is heavy duty, portable and compact.
- Mechanical seal is carbon, ceramic, BUNA and stainless steel.
- Stainless steel fasteners

AGENCY LISTINGS



Tested to UL 778 and CSA 22.2 108 Standards
By Canadian Standards Association
File #218526

MOTOR

General:

- Single phase
- 60 Hertz
- 115 and 230 volt
- Built-in thermal overload protection with automatic reset
- Class B insulation
- Oil-filled design
- High strength carbon steel shaft

2WC04 Motor:

- .40 HP, 3400 RPM
- PSC design

2WC05 Motor:

- .50 HP, 3400 RPM
- PSC design

MODEL INFORMATION

Order No.	HP	Volts	Amps	Minimum Circuit Breaker	Phase	Float Switch Style	Cord Length	Discharge Connection	Minimum Basin Diameter	Maximum Solids Size	Shipping Weight lbs/kg
2WC042F	0.4	230	5	15	1	Manual / No Switch	20'	2"	18"	2"	40 / 18.1
2WC042AF						Piggyback Float Switch					
2WC051	0.5	115	13.0	20		Manual / No Switch	10'				
2WC051AF						Piggyback Float Switch	20'				
2WC052F		230	6.5	15		Manual / No Switch					

PERFORMANCE CHARTS


These charts show actual system performance with friction loss factored in for various discharge pipe lengths. Calculations and performance based on a system with 2" PVC, schedule 40 plastic pipe (C150), (4) 90° elbows, (1) check valve and (1) shut-off valve. Wastewater requires a minimum scouring velocity of 21gpm for 2" pipe. Shaded areas do not provide minimum scouring velocity - use only for gray water with no solids.

2WC04

Pipe Length	GPM									
	Vertical Head (Feet)									
	2	4	6	8	10	12	14	16	18	20
25	96	88	82	74	65	54	43	33	24	14
50	83	77	70	63	56	47	38	30	22	13
75	74	68	62	56	49	42	35	28	21	13
100	67	62	57	51	45	39	33	26	19	12
150	57	53	48	44	39	34	29	23	17	11
200	51	47	43	39	35	31	26	22	16	10
250	46	43	39	36	33	28	24	21	16	10
300	43	39	37	34	30	27	23	19	15	9


2WC05

	4	6	8	10	12	14	16	18	20	22
25	105	99	91	84	75	65	55	45	35	25
50	90	85	78	71	63	56	48	40	32	24
75	80	74	69	62	57	50	44	37	30	22
100	72	67	62	57	52	46	40	34	28	21
150	61	58	54	49	45	40	35	31	25	18
200	54	51	48	44	40	36	32	28	23	17
250	50	47	44	40	37	34	30	26	21	16
300	46	43	40	37	34	31	28	24	20	15



DIMENSIONS

(All dimensions are in inches. Do not use for construction purposes.)



TYPICAL SPECIFICATIONS

The contractor shall furnish and install quantity _____, Model 2WC _____ submersible wastewater pump(s) as illustrated on the plans and in accordance with the following specifications.

The submersible wastewater solids handling pump(s) shall be single-phase, 115 or 230V. The 10' or 20' power cord shall be 16/3 SJTW with a NEMA three prong grounding plug. The 4/10 and ½ HP motors shall be PSC designs.

The oil-filled, motor shall have Class B insulation, automatic reset on-winding overload protection, a carbon steel shaft, upper sleeve and lower ball bearings and be protected from water intrusion by a carbon/ceramic/BUNA/SS mechanical shaft seal. Maximum fluid temperature is 104° F (40° C) for continuous operation when pump is fully submerged.

Automatic models will be equipped with a piggyback wide angle float switch. Manual models are also available.

Pump(s) shall be designed to pass 2" maximum spheres and are suitable for residential sewage systems, heavy duty sump, dewatering and water transfer applications

Materials of Construction are ASTM A48, Class 30 grey cast iron and glass-filled engineered thermoplastics.



Xylem, Inc.
2881 East Bayard Street Ext., Suite A
Seneca Falls, NY 13148
Phone: (866) 325-4210
Fax: (888) 322-5877
www.xylem.com/bellgossett

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
© 2022 Xylem Inc. B2WC R7 February 2022