


Tech 5500 and Integrated Parallel Pumping System

CROSSOVER REFERENCE CHART

D-615



		Tech 5500	PPS
Control Strategy	Sensored Zone Control	•	•
	Sensorless Curve Control		•
	Sensored Curve Control		•
	Constant Flow	•	•
	Variable Primary Control	•	
Drive/Hardware	Automatic Bypass	•	
	Expandable I/O	•	
	Technologic IPC Only		•
	Compatible with All Drives	•	
	Max Pumps	4 (expandable to 12)	8
	Max Sensors (Zones)	4 (expandable to 24)	2 per pump (up to 16)
Features	Custom Programability	•	
	Color Touch Screen		•
	Best Efficiency Staging		•
	Pump Protections	•	•
	Pump Failure DP Switch	•	
	Low/High Suction	•	
	No Flow Shutdown	•	
BMS	Bacnet MS/TP	•	•
	Bacnet IP	•	•
	Modbus RTU	•	•
	Modbus TCP		•



Xylem Inc.
8200 N. Austin Avenue
Morton Grove, IL 60053
Phone: (847) 966-3710
www.xyleminc.com/bellgossett

Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries. © 2020 Xylem Inc. D-615 May 2020



Bell & Gossett
a xylem brand