



SpectroFlex Portable Spectrophotometers

Portable spectrophotometers for measuring a wide variety of samplers in the lab or field.



- Wavelengths from 190 - 1100 nm
- Innovative optics
- Intuitive operating
- Extensive analytical quality assurance (AQA)

Description

The spectroFlex series portable spectrophotometers for the VIS and UV/VIS range offer the unique combination of systematic and spectral analytics with analytical quality assurance (AQA) and the convenience provided by a filter photometer. Thanks to state-of-the-art technology all spectroFlex models have optimized operation handling. The spectrophotometers offer menu navigation through all applications and a large backlit graphic display for concise operation with the structured menu and graphical evaluation. The instruments also offer selection tables for convenient method selection and searchable fields for data, parameters and methods.

The portable spectrophotometer's regular operation place is the laboratory, although it can be quite practical at some times, when an instrument can also be operated on-site at a measuring station. The light-weight and easy to handle spectroFlex models enable this mobile operation. The most important factors to ensure that your spectrophotometers measure correctly is careful transportation, a protected measuring venue, and a good measuring preparation procedure especially with regard to the heating period and zeroing after transportation! Besides the transportation case, the meter accessories include a 12 V adapter cable for a common car storage battery.

Specifications

Instrument Type: Single beam with AutoCheck

Lamp:

spectroFlex 6100: Tungsten

spectroFlex 6600: Xenon Flashlamp

Wavelength Range:

spectroFlex 6100: 350-1100 nm

spectroFlex 6600: 190-1100 nm

Wavelength Accuracy: ± 1 nm

Wavelength Resolution: 1 nm

Wavelength Bandwidth: 4 nm

Scan Speed:

spectroFlex 6100: Approx. 334 nm/min resp. 5.6 nm/sec

spectroFlex 6600: Approx. 455 nm/min resp. 7.6 nm/sec

Test Recognition: Automatic test recognition via barcode for all cuvette types with automatic measurement start

Absorbance Range: -3.3 to 3.3 Abs

Photometric Resolution: 0.5% of measurement value or 0.005 Abs at Extinction 2

Photometric Reproducibility: ± 0.002 E @ 1 E (or better)

Photometric Accuracy: 0.003 E for E < 0.600 E, 0.5% or value or 0.600 E - 2.000 E

Photometric Linearity: <1% up to 2.000 A at 340 - 900 nm

Stray Light: <0.1% at 340 and 408 nm

Cuvette Recognition: Automatically for all cuvette types: round 16mm 10, 20, 50 mm w/o adapter

Measurement Modes: Concentration, absorbance, transmission, kinetics and spectra with absorbance, % transmission, multi-wavelength measurement

Storage: 1000 measurement values; spectra and kinetics approx. 4 Mb => 100 spectra (300-900 nm) and 400 kinetics with 150 values

Methods and Profiles: More than 200 methods, 100 user defined methods, 20 profiles each for kinetics and absorption spectra

Interface: 1 USB-A for USB stick, printer, barcode reader, 1 USB-B for PC, 1 RS-232 for serial connection of printer/PC

Power Supply: Universal plug

Protection Class: IP 30 and protecting rinse for optical slot

Approvals: CE and UL

Dimensions (WxHxD): 15.9x7.8x12.4 inches (404x197x314 mm)

Weight: 9.9 lbs (4.5 kg without plug-in power supply)

Options and Accessories

spectroFlex 6100 (VIS) – Portable Spectrophotometer
Includes meter, case & 12V car adapter cable.

spectroFlex 6600 (UV/VIS) – Portable Spectrophotometer
Includes meter, case & 12V car adapter cable.

Contact
Global Water
for all your
instrumentation
needs:

Water Level

Water Flow

Water Samplers

Water Quality

Weather

Remote Monitoring

Control



Global Water
The Leader in Water Instrumentation

In the U.S. call toll free
at 1-800-876-1172
International: 916-638-3429
Fax: 916-638-3270
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670