




WL700 Ultrasonic Level Sensor

Non-Contact Water Level Measurement



- Non-Contact Measurement
- Rugged and Fully Encapsulated
- 4-20 ma Transmitter
- Easy Installation/No Programming
- Cost Effective
- Great for Wastewater
- Great for Flumes and Weirs
- Temperature Compensated
- Four Ranges: 1', 3', 6' and 35'
- For Monitoring Water Level and Open Channel Flow

Description

The WL700 uses the latest ultrasonic distance measuring technology for accurate non-contact water level monitoring. The fully encapsulated sensor/transmitter is temperature compensated and provides an industry standard 4-20 MA output. There are three ranges available including 1', 3' and 6' to meet a wide variety of applications. The unique 1' range sensor is ideal for measuring flow in small flumes and weirs. The 3' and 6' ranges are best for measuring river, lake and tank levels and for measuring open channel flow in larger flumes. Installation is simple and requires no programming or calibration. No maintenance is required.

The WL700 Ultrasonic Level Sensor is rugged, reliable and completely weatherproof. It is ideal for sewer or wastewater applications. The sensor is easy to mount, comes with a 10' cable and complete instructions. It is easy to interface to all PLC's, SCADA and telemetry systems with its simple 3-wire 4-20 MA output. The WL700 is compatible and provided optionally with the Global Water FC200 Open Channel Flow Monitor and the PC300 Process Controller (for water level control).

Specifications

Ranges: 0.2' to 1'; 0.4' to 3'; 0.8' to 6'; and 1.5' to 35'

Input: 18 to 30 VDC

Current Draw: 100 ma

Output: 4-20 ma (4 ma is minimum water level and 20 ma is maximum water level)

Averaging: 15 second running average (to smooth out water turbulence).

Warm Up Time: 15 seconds

Resolution: Continuous Analog

Operating Temperature Range: -40° to 185°F (-40° to 85°C) (1, 3, and 6 ft range); -40° to +145°F (-40° to 62°C) (35 ft range only)

Temperature Compensated Range: -20°F to 120°F

Accuracy: ±1.0% of Range, ±2.0% of 35 ft Range

Dimensions:

1x2x4 inches (2.5 x 5.1 x 10.2 cm) rectangular (1 ft range)

1 inch id pipe thread x 4 inches long (2.5 cm ID x 10.2 cm long) (3 ft and 6 ft range)

2-1/2 inches id pipe thread x 4 inches long (6.3 cm ID x 10.2 cm long) (35 ft range)

Material: Extruded Aluminum (1' range), PVC (3', 6' and 35' range)

Weight: 1.5 Lbs

Options and Accessories

WL700 Ultrasonic Water Level Sensor

Includes 10' cable. Specify Water Level Range: 1', 3', 6'.

WL700-035 35' Ultrasonic Water Level Sensor

Includes 10' cable.

WEXC Extra Cable

Up to 500'



Global Water
a xylem brand

In the U.S. call toll free
at 1-800-876-1172
International: 1-979-690-5560
Fax: 1-979-690-0440
Email: globalw@globalw.com

Visit our online catalog at:
www.globalw.com
Our Address:
11390 Amalgam Way
Gold River, CA 95670

Contact
Global Water
for all your
instrumentation
needs:

Water Level

Water Flow

Water Samplers

Water Quality

Weather

Remote Monitoring

Control