


NS Duplex NSD33750

Control Panel Schematic and Layout

CONTROL PANEL SCHEMATIC

FRAME: NSD33750

REVDATE: 0423




CONTROL PANEL SCHEMATIC

GWTNSD33750 R1

FNAME: NSD33750

REVDATE: 0423



MULTI-TAP TRANSFORMER:

CONNECT FACTORY TAGGED WIRES TO APPROPRIATE TRANSFORMER VOLTAGE TAP. SEE BELOW FOR CONNECTIONS:

FOR 208V OPERATION, CONNECT TO FUSE INPUT HF & TO TRANSFORMER TAP H2.

FOR 240V OPERATION, CONNECT TO FUSE INPUT HF & TO TRANSFORMER TAP H3.

FOR 480V OPERATION, CONNECT TO FUSE INPUT HF & TO TRANSFORMER TAP H4.

DASHED LINE INDICATES FIELD WIRING.

USE COPPER CONDUCTORS ONLY.

TEMPERATURE RATING OF CONDUCTORS IS TO BE: 60°C (140°F) FOR UNDER 100A. 75°C (167°F) FOR OVER 100A.

BRANCH CIRCUIT PROTECTION SHALL BE PROVIDED BY THE INSTALLER. MUST BE SIZED ACCORDING TO PUMPMOTOR MANUFACTURING SPECIFICATIONS.

VERIFY CORRECT OPERATION OF CONTROL PANEL AFTER INSTALLATION IS COMPLETE.

FIELD WIRING TORQUE SPECS.

TERMINAL BLOCK UT 2.5	5 IN-LB
TERMINAL BLOCK UT 4	7 IN-LB
TERMINAL BLOCK UT 6	15 IN-LB
TERMINAL BLOCK UT 10	15 IN-LB
TERMINAL BLOCK UT 16	25 IN-LB
TERMINAL BLOCK UT 35	30 IN-LB
TS1, TS2, J2 & J3 PCB	5 IN-LB
TRANSFORMER H1F, H2F & H3F	15 IN-LB
TRANSFORMER H1, H2 & H3	10 IN-LB
DS1 VLS3P16-63 R1	16 IN-LB
DS1 VLS3P63-125 R2	45 IN-LB
DS1 LKAJU3CN 100A	36 IN-LB
DS1 LKAMU3N 200A	200 IN-LB

DRAWN BY:

AL

DATE:

04/10/23

APPROVED BY:

DO

DATE:

04/11/23


THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.



TITLE: NSD33750 CONTROL PANEL SCHEMATIC			
SIZE B	DWG NO. 4226	PART NO. NSD33750	REV
SCALE NONE	SHEET 2 OF 2		

FNAME: NSD33750

REVDATE: 0423



CONTROL PANEL LAYOUT



FNAME: NSD33750



REVDATE: 0423

QTY	MANUFACTURER	DESCRIPTION	PART NUMBER	REF.
1	Integra	P.C. Nema 4X Enclosure 18X16X10	H181610HCLL	E1
1	All-Spec	Dead Front	622P	DF1
1	All-Spec	Back Panel	625	BP1
1	Integra	Hinge Kit	US0PK-P909	N/A
1	Ingram	Beacon	R10-SM	BE1
1	Ingram	Buzzer	PB-024-AD	B1
1	See Water	Display Board	GBJ5	GBJ5
5	LEDTRONICS	White Lense	LENS-LCD780-CWF	N/A
2	See Water	Flat Cable Assembly	IDC-25MB	N/A
2	Molex	4 Pin Connector	09-50-3041	N/A
1	Molex	6 Pin Connector	09-50-3061	N/A
1	See Water	Power Circuit Board	WWD	PCB1
2	Carling	H0A Toggle Switch	6FC57-73	TG1-2
1	Schneider	Multitap Transformer 50VA	9070TF50D20	XF1
2	Mersen	ATQR 3/10A Fuse	ATQR-3/10A	XF1
1	Mersen	TRM 6/10A Fuse	TRM-6/10A	XF1
2	Schneider	Motor Protector	GV3P50	MP1-2

QTY	MANUFACTURER	DESCRIPTION	PART NUMBER	REF.
2	Schneider	Side Mount Auxiliary	GVAN11	OL1-2
2	Schneider	Contactora	LC1D50AG7	M1-2
1	Schneider	GV3 BusBar	GV3G264	N/A
1	Schneider	Circuit Breaker	B1E1C3	CB1
1	Macromatics	Door Mount Dual Seal Fail	SFF120C100	SFR1
2	Schneider	Mini Plug In Relay Holder	RSZE1S35M	CR1-2
2	Schneider	Mini Plug In Relay Clamp	RSZR215	CR1-2
2	Schneider	Mini Plug In Relay 12VDC	RSB1A120JD	CR1-2
2	Trumeter	Elapsed Time Meter	6320-2500-0000	ETM1-2
2	Trumeter	Cycle Counter	6300-2500-0000	CC1-2
3	Phoenix Contact	Terminal Block UT-35	3044225	TB1
1	Phoenix Contact	Terminal Block UT-35-PE	3044241	G1
5	Phoenix Contact	End Stop	3022218	N/A
2	Burndy	Ground	S250	G2-3
2	Altech	Angled Mounting Bracket	CA603	N/A
4	See Water	N.O. Narrow Angle Floats 50'	FPC0N50	N/A
1	UL	508A UL Label	N/A	N/A



Xylem Inc.
2881 East Bayard Street Ext.
Seneca Falls, NY 13148
Phone: (800) 453-6777
Fax: (888) 322-5877
www.xylem.com/goulds

Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are property of their respective owners.
© 2023 Xylem Inc. GWTNSD33750 R1 July 2023

DRAWN BY:	AL	DATE:	04/10/23		
APPROVED BY:	DO	DATE:	04/11/23		
THIS DRAWING CONTAINS PROPRIETARY INFORMATION AND SHALL NOT BE USED OR DISCLOSED WITHOUT PRIOR WRITTEN AUTHORIZATION.				TITLE:	
				NSD33750 CONTROL PANEL LAYOUT	
				SIZE B	DWG NO. 4227
SCALE		NONE	SHEET		2 OF 2