



AQUAVAR[®] IPC

Variable Speed Drive

AQUAVAR IPC

The AQUAVAR IPC variable speed drive (VFD) brings the latest in pump drive technology and programming. The drive and interface are designed to give you advanced capabilities that help you effectively and efficiently operate your system.

Optimized for pumps

- Wide range of standard and permanent magnet motors with power up to 90 kw / 450 hp
- Developed by pump experts and optimized for controlling pumps
- Submersible and above ground applications

Quick set-up and ease-of-use

- Easier start-up and programming with Start-Up Genie
- Two wire multi-pump connection for faster installation
- Hand On, Off, and Auto On buttons available for easy pump operation at the keypad. No toggling between local and remote operation

Helping to Improve Your Performance

- Multi-pump configuration for up to four (4) pumps
– no need for PLC
- System redundancy with multi-master control in case of drive failure

Standard for every drive


- Wide range of voltage and enclosure options
- True 208V coverage
- Dedicated single phase input
- Remote commissioning and monitoring with USB Connectivity and software
- In-panel or handheld keypad with backlit display
- Alarm Log for last 5 alarms and maintenance events
- EMC/RFI filters and Dual DC-link reactors to reduce drive noise emissions and interference
- I/O expansion cards, factory installed or field configured

TRANSDUCER


Includes: 4-20mA, 300psi transducer and 16' cable

Used for: Pressure transducer for constant pressure applications. Transducer will be delivered with your drive when you use the "1" Transducer character.

NOTE: 9K712 - Repair part number for the transducer
9K755 - Repair part number for the transducer and 16' cable



KEYPAD LAYOUT



NOMENCLATURE**Example Product Code**

AV	A	2	0015	D	0	F	0	D	0	X	1	
											Transducer	
											1 = Transducer 2 = No Transducer	
											Motor Mounting Options*	
											X = No Accessories	
											Coating / EMC Filter Options**	
											0 = Standard Protection w/ H2 EMC Filter (Standard EMC Filter)	
											1 = Standard Protection w/ H3 EMC Filter	
											2 = Standard Protection w/ H1 EMC Filter	
											3 = 3C3 Board Coating w/ H2 EMC Filter (Standard EMC Filter)	
											4 = 3C3 Board Coating w/ H3 EMC Filter	
											5 = 3C3 Board Coating w/ H1 EMC Filter	
											Disconnect Options	
											X = No Accessories	
											S = Standard Disconnect (Single Phase Only)	
											D = Fused Disconnect	
											Backup Options	
											0 = No Backup	
											4 = 24VDC Backup (Requires External Power)	
											Input/Output Options	
											X = No Additional I/O	C = PTC Thermistor Card
											A = Analog I/O and Real-time Clock	D = PT100 Sensor Input
											B = General Purpose I/O	E = Relay Card
												F = Co-Processor
											Communications Options	
											0 = Standard Communication	4 = LonWorks
											1 = MODBUS TCP	5 = Profinet
											2 = Profibus	6 = Ethernet IP
											3 = DeviceNet	7 = Co-Processor
											Enclosure	
											A = TYPE 1 (IP21)	D = TYPE 4X (IP66)
											B = TYPE 12 (IP55)	E = IP20 (Chassis)
											C = TYPE 3R	
											Nominal HP	
											0015 0075 0250 0600	
											0020 0100 0300 0750	
											0030 0150 0400 1000	
											0050 0200 0500 1250	
											Phase/Voltage	
											1 = 1/230 3 = 1/460*** 5 = 3/575	
											2 = 3/230 4 = 3/380-460	
											Type - A = Advanced B = Basic Drive	
											Model - AV	

* Motor mounted units are not available in the initial launch. Product news will be issued when this configuration is available.

** 575V and single phase 10, 20, and 30HP are not available with EMC filter. These are sold without filter as standard.

*** Single phase 460V are not available.

NOMENCLATURE**Example Product Code**

AV	A	2	2500	A	0	F	0	D	3	X	1	
												Transducer
												1=Transducer 2=No Transducer
												Motor Mounting Options
												X = No Accessories
												Coating Options
												3 = 3C3 Board Coating with H2 EMC Filter (Standard RFI Filter)
												4 = 3C3 Board Coating with H3 EMC Filter
												5 = 3C3 Board Coating with H1 EMC Filter
												Disconnect Options
												X = No Disconnect (Open Chassis and TYPE 3R Only)
												D = Fused Disconnect (TYPE 1 and TYPE 12 Only)
												Backup Options
												0 = No Backup
												4 = 24VDC Backup (Requires External Power)
												Input/Output Options
												X = No Additional I/O
												A = Analog I/O and Real-time Clock
												B = General Purpose I/O
												C = PTC Thermistor Card
												D = PT100 Sensor Input
												E = Relay Card
												F = Co-Processor
												Communications Options
												0 = Standard Communication
												1 = MODBUS® TCP
												2 = Profibus
												3 = DeviceNet
												4 = LonWorks
												5 = Profinet
												6 = Ethernet IP
												7 = Co-Processor
												Enclosure
												A = TYPE 1 (IP21)
												B = TYPE 12 (IP55)
												C = TYPE 3R (IP54 drive - Separate 3R Cover Required)
												E = IP20 / IP00 (Chassis)
												Nominal HP
												1500 2500 3500 4500 5500**
												2000 3000 4000* 5000 6000
												Phase/Voltage
												4 = 3/460 5 = 3/575
												Type - A= Advanced
												Model - AV

* Available on 575V only.

** Available on 460V only.

PRODUCT CHART - IP20 CHASSIS

Input Voltage	Input Phase	IP20 Chassis Base Model	Continuous Output Amps @ 45°C Ambient	Continuous Output Amps @ 50°C Ambient	Nominal Surface Motor HP*	Nominal Sub. Motor HP* 4" / 6" & Up	Frame Size
208-230	3	AVA20015E0FOX0X2	6.6	5.9	1.5	1.5	A2
		AVA20020E0FOX0X2	7.5	6.8	2	2	
		AVA20030E0FOX0X2	10.6	9.5	3	3	
		AVA20050E0FOX0X2	16.7	15.0	5		A3
		AVA20075E0FOX0X2	24.2	21.8	7.5	5	B3
		AVA20100E0FOX0X2	30.8	27.7	10	7.5	
		AVA20150E0FOX0X2	46.2	41.6	15	10 / 15	
		AVA20200E0FOX0X2	59.4	53.5	20	15	B4
		AVA20250E0FOX0X2	74.8	67.3	25	20	
		AVA20300E0FOX0X2	88	79.2	30	25	C3
		AVA20400E0FOX0X2	115	103.5	40	30	
		AVA20500E0FOX0X2	143	128.7	50		C4
		AVA20600E0FOX0X2	170	153.0	60		
380-460	3	AVA40015E0FOX0X2	2.7	2.4	1.5	1	A2
		AVA40020E0FOX0X2	3.4	3.1	2	1.5	
		AVA40030E0FOX0X2	4.8	4.3	3	2	
		AVA40050E0FOX0X2	8.2	7.4	5	3	
		AVA40075E0FOX0X2	11	9.9	7.5	5	A3
		AVA40100E0FOX0X2	14.5	13.1	10	7.5	
		AVA40150E0FOX0X2	21	18.9	15	10	
		AVA40200E0FOX0X2	27	24.3	20	15	B3
		AVA40250E0FOX0X2	34	30.6	25	20	
		AVA40300E0FOX0X2	40	36.0	30	25	
		AVA40400E0FOX0X2	52	46.8	40	30	B4
		AVA40500E0FOX0X2	65	58.5	50	40	
		AVA40600E0FOX0X2	80	72.0	60	50	
		AVA40750E0FOX0X2	105	94.5	75	60	C3
		AVA41000E0FOX0X2	130	117.0	100	75	
		AVA41250E0FOX0X2	160	144.0	125	100	C4
575	3	AVA50015E0FOX0X2	2.4	2.2	1.5	1.5	A3
		AVA50020E0FOX0X2	2.7	2.4	2		
		AVA50030E0FOX0X2	3.9	3.5	3	2	
		AVA50050E0FOX0X2	6.1	5.5	5	3	
		AVA50075E0FOX0X2	9	8.1	7.5	5	
		AVA50100E0FOX0X2	11	9.9	10	7.5	
		AVA50150E0FOX0X2	18	16.2	15		B3
		AVA50200E0FOX0X2	22	19.8	20		
		AVA50250E0FOX0X2	27	24.3	25		
		AVA50300E0FOX0X2	34	30.6	30		B4
		AVA50400E0FOX0X2	41	36.9	40		
		AVA50500E0FOX0X2	52	46.8	50		
		AVA50600E0FOX0X2	62	55.8	60		C3
		AVA50750E0FOX0X2	83	74.7	75		
		AVA51000E0FOX0X2	100	90.0	100		
		AVA51250E0FOX0X2	131	117.9	125		C4

* Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

AQUAVAR IPC

PRODUCT CHART - IP20/IP00 CHASSIS

Input Voltage	Input Phase	IP20 Chassis Base Model	Continuous Output Amps* @ 45°C (113°F) Ambient	Continuous Output Amps* @ 50°C (122°F) Ambient	Nominal Surface Motor HP**	Frame Size
460	3	AVA41500E0F0X3X2	190	175	150	D3
		AVA42000E0F0X3X2	240	221	200	
		AVA42500E0F0X3X2	302	278	250	
		AVA43000E0F0X3X2	361	332	300	D4
		AVA43500E0F0X3X2	443	408	350	
		AVA44500E0F0X3X2	535	492	450	
575		AVA51500E0F0X3X2	155	143	150	D3
		AVA52000E0F0X3X2	192	177	200	
		AVA52500E0F0X3X2	242	223	250	D4
		AVA53000E0F0X3X2	290	267	300	
		AVA53500E0F0X3X2	344	316	350	
		AVA54000E0F0X3X2	400	368	400	

* With Switching Frequency (Parameter 14-10) set to 2 kHz.

** Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

PRODUCT CHART - TYPE 1

Input Voltage	Input Phase	TYPE 1 Base Model	Continuous Output Amps* @ 45°C (113°F) Ambient	Continuous Output Amps* @ 50°C (122°F) Ambient	Nominal Surface Motor HP**	Frame Size
460	3	AVA41500A0F0D3X1	190	175	150	D5
		AVA42000A0F0D3X1	240	221	200	
		AVA42500A0F0D3X1	302	278	250	
		AVA43000A0F0D3X1	361	332	300	D7
		AVA43500A0F0D3X1	443	408	350	
		AVA44500A0F0D3X1	535	492	450	
575		AVA51500A0F0D3X1	155	143	150	D5
		AVA52000A0F0D3X1	192	177	200	
		AVA52500A0F0D3X1	242	223	250	D7
		AVA53000A0F0D3X1	290	267	300	
		AVA53500A0F0D3X1	344	316	350	
		AVA54000A0F0D3X1	400	368	400	

* With Switching Frequency (Parameter 14-10) set to 2 kHz.

** Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

PRODUCT CHART - TYPE 1

Input Voltage	Input Phase	TYPE 1 Base Model	Continuous Output Amps @ 45°C Ambient	Continuous Output Amps @ 50°C Ambient	Nominal Surface Motor Hp*	Nominal Sub. Motor HP* 4" / 6" & Up	Frame Size
208-230	1	AVA10020A0F0X0X1	7.5	6.8	2	2	B1
		AVA10030A0F0X0X1	10.6	9.5	3	3	
		AVA10050A0F0X0X1	16.7	15.0	5		
		AVA10075A0F0X0X1	24.2	21.8	7.5	5	
		AVA10100A0F0X0X1	30.8	27.7	10	7.5 / 5	B2
		AVA10200A0F0X0X1	59.4	53.5	20	10	C1
		AVA10300A0F0X0X1	88	79.2	30	15 & 20	C2
208-230	3	AVA20015A0F0X0X1	6.6	5.9	1.5	1.5	A2
		AVA20020A0F0X0X1	7.5	6.8	2	2	
		AVA20030A0F0X0X1	10.6	9.5	3	3	
		AVA20050A0F0X0X1	16.7	15.0	5		A3
		AVA20075A0F0X0X1	24.2	21.8	7.5	5	B1
		AVA20100A0F0X0X1	30.8	27.7	10	7.5	
		AVA20150A0F0X0X1	46.2	41.6	15	10 / 15	B2
		AVA20200A0F0X0X1	59.4	53.5	20	15	
		AVA20250A0F0X0X1	74.8	67.3	25	20	C1
		AVA20300A0F0X0X1	88	79.2	30	25	
		AVA20400A0F0X0X1	115	103.5	40	30	C2
		AVA20500A0F0X0X1	143	128.7	50		
		AVA20600A0F0X0X1	170	153.0	60		
380-460	3	AVA40015A0F0X0X1	2.7	2.4	1.5	1	A2
		AVA40020A0F0X0X1	3.4	3.1	2	1.5	
		AVA40030A0F0X0X1	4.8	4.3	3	2	
		AVA40050A0F0X0X1	8.2	7.4	5	3	
		AVA40075A0F0X0X1	11	9.9	7.5	5	A3
		AVA40100A0F0X0X1	14.5	13.1	10	7.5	
		AVA40150A0F0X0X1	21	18.9	15	10	B1
		AVA40200A0F0X0X1	27	24.3	20	15	
		AVA40250A0F0X0X1	34	30.6	25	20	B2
		AVA40300A0F0X0X1	40	36.0	30	25	
		AVA40400A0F0X0X1	52	46.8	40	30	C1
		AVA40500A0F0X0X1	65	58.5	50	40	
		AVA40600A0F0X0X1	80	72.0	60	50	C2
		AVA40750A0F0X0X1	105	94.5	75	60	
		AVA41000A0F0X0X1	130	117.0	100	75	
		AVA41250A0F0X0X1	160	144.0	125	100	
575	3	AVA50015A0F0X0X1	2.4	2.2	1.5	1.5	A3
		AVA50020A0F0X0X1	2.7	2.4	2		
		AVA50030A0F0X0X1	3.9	3.5	3	2	
		AVA50050A0F0X0X1	6.1	5.5	5	3	
		AVA50075A0F0X0X1	9	8.1	7.5	5	
		AVA50100A0F0X0X1	11	9.9	10	7.5	
		AVA50150A0F0X0X1	18	16.2	15		B1
		AVA50200A0F0X0X1	22	19.8	20		
		AVA50250A0F0X0X1	27	24.3	25		B2
		AVA50300A0F0X0X1	34	30.6	30		
		AVA50400A0F0X0X1	41	36.9	40		C1
		AVA50500A0F0X0X1	52	46.8	50		
		AVA50600A0F0X0X1	62	55.8	60		C2
		AVA50750A0F0X0X1	83	74.7	75		
		AVA51000A0F0X0X1	100	90.0	100		
		AVA51250A0F0X0X1	131	117.9	125		

* Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

PRODUCT CHART - TYPE 12 & TYPE 3R

Input Voltage	Input Phase	TYPE 12 Base Model	TYPE 3R Base Model	Cont. Output Amps @ 45°C Ambient	Cont. Output Amps @ 50°C Ambient	Nominal Surface Motor HP*	Nominal Sub. Motor HP* 4" / 6" & Up	Frame Size	DV / DT Load Filter TYPE 3R**
208-230	1	AVA10015B0F0X0X1	AVA10015C0F0X0X1	6.6	5.9	1.5	1.5	A5	V1K8A03
		AVA10020B0F0X0X1	AVA10020C0F0X0X1	7.5	6.8	2	2	B1	V1K8A03
		AVA10030B0F0X0X1	AVA10030C0F0X0X1	10.6	9.5	3	3		V1K12A03
		AVA10050B0F0X0X1	AVA10050C0F0X0X1	16.7	15.0	5			V1K18A03
		AVA10075B0F0X0X1	AVA10075C0F0X0X1	24.2	21.8	7.5	5		V1K25A03
		AVA10100B0F0X0X1	AVA10100C0F0X0X1	30.8	27.7	10	7.5 / 5	B2	V1K35A03
		AVA10200B0F0X0X1	AVA10200C0F0X0X1	59.4	53.5	20	10	C1	V1K80A03
		AVA10300B0F0X0X1	AVA10300C0F0X0X1	88	79.2	30	20 / 15	C2	V1K110A03
	3	AVA20015B0F0X0X1	AVA20015C0F0X0X1	6.6	5.9	1.5	1.5	A5	V1K8A03
		AVA20020B0F0X0X1	AVA20020C0F0X0X1	7.5	6.8	2	2		V1K8A03
		AVA20030B0F0X0X1	AVA20030C0F0X0X1	10.6	9.5	3	3		V1K12A03
		AVA20050B0F0X0X1	AVA20050C0F0X0X1	16.7	15.0	5			V1K18A03
		AVA20075B0F0X0X1	AVA20075C0F0X0X1	24.2	21.8	7.5	5	B1	V1K25A03
		AVA20100B0F0X0X1	AVA20100C0F0X0X1	30.8	27.7	10	7.5		V1K35A03
		AVA20150B0F0X0X1	AVA20150C0F0X0X1	46.2	41.6	15	10 / 15		V1K55A03
		AVA20200B0F0X0X1	AVA20200C0F0X0X1	59.4	53.5	20	15	B2	V1K80A03
		AVA20250B0F0X0X1	AVA20250C0F0X0X1	74.8	67.3	25	20	C1	V1K80A03
		AVA20300B0F0X0X1	AVA20300C0F0X0X1	88	79.2	30	25		V1K110A03
		AVA20400B0F0X0X1	AVA20400C0F0X0X1	115	103.5	40	30		V1K130A03
		AVA20500B0F0X0X1	AVA20500C0F0X0X1	143	128.7	50		C2	V1K160A03
		AVA20600B0F0X0X1	AVA20600C0F0X0X1	170	153.0	60			V1K200A03
380-460	3	AVA40015B0F0X0X1	AVA40015C0F0X0X1	2.7	2.4	1.5	1	A5	V1K8A03
		AVA40020B0F0X0X1	AVA40020C0F0X0X1	3.4	3.1	2	1.5		V1K8A03
		AVA40030B0F0X0X1	AVA40030C0F0X0X1	4.8	4.3	3	2		V1K8A03
		AVA40050B0F0X0X1	AVA40050C0F0X0X1	8.2	7.4	5	3		V1K12A03
		AVA40075B0F0X0X1	AVA40075C0F0X0X1	11	9.9	7.5	5		V1K12A03
		AVA40100B0F0X0X1	AVA40100C0F0X0X1	14.5	13.1	10	7.5	B1	V1K18A03
		AVA40150B0F0X0X1	AVA40150C0F0X0X1	21	18.9	15	10		V1K25A03
		AVA40200B0F0X0X1	AVA40200C0F0X0X1	27	24.3	20	15		V1K35A03
		AVA40250B0F0X0X1	AVA40250C0F0X0X1	34	30.6	25	20		V1K35A03
		AVA40300B0F0X0X1	AVA40300C0F0X0X1	40	36.0	30	25	B2	V1K55A03
		AVA40400B0F0X0X1	AVA40400C0F0X0X1	52	46.8	40	30		V1K55A03
		AVA40500B0F0X0X1	AVA40500C0F0X0X1	65	58.5	50	40	C1	V1K80A03
		AVA40600B0F0X0X1	AVA40600C0F0X0X1	80	72.0	60	50		V1K80A03
		AVA40750B0F0X0X1	AVA40750C0F0X0X1	105	94.5	75	60		V1K110A03
		AVA41000B0F0X0X1	AVA41000C0F0X0X1	130	117.0	100	75	C2	V1K130A03
		AVA41250B0F0X0X1	AVA41250C0F0X0X1	160	144.0	125	100		V1K160A03
575	3	AVA50015B0F0X0X1	AVA50015C0F0X0X1	2.4	2.2	1.5	1.5	A5	V1K8A03
		AVA50020B0F0X0X1	AVA50020C0F0X0X1	2.7	2.4	2			V1K8A03
		AVA50030B0F0X0X1	AVA50030C0F0X0X1	3.9	3.5	3	2		V1K8A03
		AVA50050B0F0X0X1	AVA50050C0F0X0X1	6.1	5.5	5	3		V1K8A03
		AVA50075B0F0X0X1	AVA50075C0F0X0X1	9	8.1	7.5	5		V1K12A03
		AVA50100B0F0X0X1	AVA50100C0F0X0X1	11	9.9	10	7.5	B1	V1K12A03
		AVA50150B0F0X0X1	AVA50150C0F0X0X1	18	16.2	15			V1K18A03
		AVA50200B0F0X0X1	AVA50200C0F0X0X1	22	19.8	20			V1K25A03
		AVA50250B0F0X0X1	AVA50250C0F0X0X1	27	24.3	25			V1K35A03
		AVA50300B0F0X0X1	AVA50300C0F0X0X1	34	30.6	30		B2	V1K35A03
		AVA50400B0F0X0X1	AVA50400C0F0X0X1	41	36.9	40			V1K55A03
		AVA50500B0F0X0X1	AVA50500C0F0X0X1	52	46.8	50			V1K55A03
		AVA50600B0F0X0X1	AVA50600C0F0X0X1	62	55.8	60		C1	V1K80A03
		AVA50750B0F0X0X1	AVA50750C0F0X0X1	83	74.7	75			V1K110A03
		AVA51000B0F0X0X1	AVA51000C0F0X0X1	100	90.0	100			V1K110A03
		AVA51250B0F0X0X1	AVA51250C0F0X0X1	131	117.9	125		C2	V1K160A03

* Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

** dv/dt filter recommended for applications with motor leads longer than 50'. It is recommended to use the dv/dt filter with all submersible applications. dv/dt filter is supplied with all AQUAVAR ordered with Accessories code "F".

AQUAVAR IPC

PRODUCT CHART - TYPE 12

Input Voltage	Input Phase	TYPE 12 Base Model	Continuous Output Amps* @ 45°C (113°F) Ambient	Continuous Output Amps* @ 50°C (122°F) Ambient	Nominal Surface Motor HP**	Frame Size
460	3	AVA41500B0F0D3X1	190	175	150	D5
		AVA42000B0F0D3X1	240	221	200	
		AVA42500B0F0D3X1	302	278	250	
		AVA43000B0F0D3X1	361	332	300	D7
		AVA43500B0F0D3X1	443	408	350	
		AVA44500B0F0D3X1	535	492	450	
575		AVA51500B0F0D3X1	155	143	150	D5
		AVA52000B0F0D3X1	192	177	200	
		AVA52500B0F0D3X1	242	223	250	
		AVA53000B0F0D3X1	290	267	300	
		AVA53500B0F0D3X1	344	316	350	
		AVA54000B0F0D3X1	400	368	400	

* With Switching Frequency (Parameter 14-10) set to 2 kHz.

** Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

PRODUCT CHART - TYPE 3R

Input Voltage	Input Phase	TYPE 3R Base Model	Continuous Output Amps* @ 45°C (113°F) Ambient	Continuous Output Amps* @ 50°C (122°F) Ambient	Nominal Surface Motor HP**	Frame Size	TYPE 3R Cover Kit Part Number***	DV / DT Load Filter TYPE 3R****
460	3	AVA41500C0F0X3X1	167	143	150	D1	9K715	V1K200A03
		AVA42000C0F0X3X1	211	180	200			V1K250A03
		AVA42500C0F0X3X1	266	227	250			V1K305A03
		AVA43000C0F0X3X1	318	271	300	D2	9K716	V1K362A03
		AVA43500C0F0X3X1	390	332	350			V1K420A03
		AVA44500C0F0X3X1	475	405	450			V1K480A03
575		AVA51500C0F0X3X1	136	116	150	D1	9K715	V1K160A03
		AVA52000C0F0X3X1	169	144	200			V1K200A03
		AVA52500C0F0X3X1	213	182	250	D2	9K716	V1K250A03
		AVA53000C0F0X3X1	255	218	300			V1K305A03
		AVA53500C0F0X3X1	303	258	350			
		AVA54000C0F0X3X1	352	300	400			V1K362A03

* With Switching Frequency (Parameter 14-10) set to 4 kHz.

** Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

*** TYPE 3R Cover Kit is required to be used with the base model number for TYPE 3R outdoor protection.

**** dv/dt filter recommended for applications with motor leads longer than 50'.

PRODUCT CHART - TYPE 4X


Input Voltage	Input Phase	TYPE 4X Base Model	Continuous Output Amps @ 45°C Ambient	Continuous Output Amps @ 50°C Ambient	Nominal Surface Motor HP*	Nominal Submersible Motor HP* 4" / 6" & Up	Frame Size	DV / DT Load Filter TYPE 3R**
208-230	1	AVA10015D0F0X0X1	6.6	5.9	1.5	1.5	A5	V1K8A03
		AVA10020D0F0X0X1	7.5	6.8	2	2	B1	V1K12A03
		AVA10030D0F0X0X1	10.6	9.5	3	3		V1K18A03
		AVA10050D0F0X0X1	16.7	15.0	5	5		V1K25A03
		AVA10075D0F0X0X1	24.2	21.8	7.5	7.5 / 5	B2	V1K35A03
		AVA10100D0F0X0X1	30.8	27.7	10	10	C3	V1K80A03
		AVA10200D0F0X0X1	59.4	53.5	20	15 & 20	C4	V1K110A03
		AVA10300D0F0X0X1	88	79.2	30			
208-230	3	AVA20015D0F0X0X1	6.6	5.9	1.5	1.5	A5	V1K8A03
		AVA20020D0F0X0X1	7.5	6.8	2	2		V1K12A03
		AVA20030D0F0X0X1	10.6	9.5	3	3		V1K18A03
		AVA20050D0F0X0X1	16.7	15.0	5	5		V1K25A03
		AVA20075D0F0X0X1	24.2	21.8	7.5	7.5	B1	V1K35A03
		AVA20100D0F0X0X1	30.8	27.7	10	10 / 15		V1K55A03
		AVA20150D0F0X0X1	46.2	41.6	15	15		V1K80A03
		AVA20200D0F0X0X1	59.4	53.5	20	20		V1K110A03
		AVA20250D0F0X0X1	74.8	67.3	25	25	C1	V1K130A03
		AVA20300D0F0X0X1	88	79.2	30	30		V1K160A03
		AVA20400D0F0X0X1	115	103.5	40			V1K200A03
		AVA20500D0F0X0X1	143	128.7	50			
		AVA20600D0F0X0X1	170	153.0	60			
380-460	3	AVA40015D0F0X0X1	2.7	2.4	1.5	1	A5	V1K8A03
		AVA40020D0F0X0X1	3.4	3.1	2	1.5		V1K12A03
		AVA40030D0F0X0X1	4.8	4.3	3	2		V1K18A03
		AVA40050D0F0X0X1	8.2	7.4	5	3		V1K25A03
		AVA40075D0F0X0X1	11	9.9	7.5	5		V1K35A03
		AVA40100D0F0X0X1	14.5	13.1	10	7.5		V1K55A03
		AVA40150D0F0X0X1	21	18.9	15	10	B1	V1K80A03
		AVA40200D0F0X0X1	27	24.3	20	15		V1K110A03
		AVA40250D0F0X0X1	34	30.6	25	20		V1K130A03
		AVA40300D0F0X0X1	40	36.0	30	25		V1K160A03
		AVA40400D0F0X0X1	52	46.8	40	30	B2	
		AVA40500D0F0X0X1	65	58.5	50	40		
		AVA40600D0F0X0X1	80	72.0	60	50		
		AVA40750D0F0X0X1	105	94.5	75	60		
		AVA41000D0F0X0X1	130	117.0	100	75	C1	
		AVA41250D0F0X0X1	160	144.0	125	100		
575	3	AVA50015D0F0X0X1	2.4	2.2	1.5	1.5	A5	V1K8A03
		AVA50020D0F0X0X1	2.7	2.4	2	2		V1K12A03
		AVA50030D0F0X0X1	3.9	3.5	3	2		V1K18A03
		AVA50050D0F0X0X1	6.1	5.5	5	3		V1K25A03
		AVA50075D0F0X0X1	9	8.1	7.5	5		V1K35A03
		AVA50100D0F0X0X1	11	9.9	10	7.5		V1K55A03
		AVA50150D0F0X0X1	18	16.2	15		B1	V1K80A03
		AVA50200D0F0X0X1	22	19.8	20			V1K110A03
		AVA50250D0F0X0X1	27	24.3	25			V1K130A03
		AVA50300D0F0X0X1	34	30.6	30			V1K160A03
		AVA50400D0F0X0X1	41	36.9	40		B2	
		AVA50500D0F0X0X1	52	46.8	50			
		AVA50600D0F0X0X1	62	55.8	60			
		AVA50750D0F0X0X1	83	74.7	75			
		AVA51000D0F0X0X1	100	90.0	100		C1	
		AVA51250D0F0X0X1	131	117.9	125			

* Nominal HP values are for reference only. Size AQUAVAR by maximum output amps of the motor.

** dv/dt filter recommended for applications with motor leads longer than 50'. It is recommended to use the dv/dt filter with all submersible applications.

SPECIFICATIONS**Ratings and Enclosures**

- IP20 Open, TYPE 1, TYPE 12, TYPE 3R, TYPE 4X
- 1.5 - 125 HP (frame A - C), 150 - 450 HP (frame D), wall or motor mounted
- Relative humidity lower than 95% without condensation.
- Ambient temperature 14° F - 113° F (-10°C - 45°C). Higher temperatures can be achieved by derating the output amperage of the drive 10% for up to 122° F (50°C).
- At altitudes from 0 to 3300 feet (0 to 1000 meters) rated current is available. For altitudes above 3300 feet (1000 meters) use table listed below. Maximum 9900 feet (3000 meters). (Consult factory above 9900 feet (3000 meters)). See chart below for derate in % of output current.

**Electrical Characteristics**

- INPUT POWER**
- 3 phase 380 V to 480 V $\pm 10\%$
 - 1 phase 200 V to 240 V $\pm 10\%$
 - 3 phase 200 V to 240 V $\pm 10\%$
 - 3 phase 525 V to 600 V $\pm 10\%$
 - Frequency 50 or 60 Hz, $\pm 2\text{Hz}$

- OUTPUT POWER**
- 3 phase from 0 to V_{supply}
 - 0 to 120 Hz frequency

BUILT-IN CONTROL CONNECTIONS

Analog input	1 current (0/4-20mA); 1 current/voltage (0/4-20mA/0-10vdc)
Programmable digital inputs	6, 2 can be used as digital outputs
Analog output	1, 0/4-20 mA
Programmable relay outputs	2, standard Form C, 240 VAC, 2 A
Auxiliary voltage	+24 V DC, maximum 200 mA

PUMP AND MOTOR PROTECTIONS**Motor Protections**

Ground Fault
 Motor Stall
 Motor Over Temperature (Predictive and Sensor Based)
 Motor Condensation (Motor Preheat Circuit)
 Motor Overload (Programmable Action)

Pump Protections

Pump No-Flow
 Under Pressure
 No Water / Loss of Prime
 Short-Cycle
 Vibration (Programming Automated)

WEATHER SHIELD

The weather shield is intended to provide additional protection of outdoor rated drives when there is a risk of snow collecting on the top of the drive or excessive rain, which could sub cool the drive, leading to internal condensation. The weather shield is made of corrosion resistant stainless and AISI316 and is also suitable for installation in coastal areas and marine environments.

The weather shield is also to be used if there is a risk of direct sunlight on the display, since heat generated by the sun radiation might damage the LCD as well as limit the maximum ambient temperature.

NOTE: The weather shield should only be used together with outdoor rated drives and will not provide sufficient protection for outdoor installation of drives not designed for this purpose.

Weather shield selection:

Frame Size	Ordering Number
A4, A5, B1, B2	9K655
C1, C2	9K698

TYPE 3R COVER KIT

The TYPE 3R Cover Kits are designed for TYPE 3R base model drives with AVAXXXXXC... part numbers. These kits add a cover to the outside vents of the IPC and provides TYPE 3R compliant protection against weather and hosed water. The kit is used only with IPC drives that have the enclosure code "C".

The TYPE 3R Cover Kit includes:

- Top Plate
- Gland plate with attached gasket
- TYPE 3R Cover
- Adhesive label
- Installation hardware



Cover Kit Selection:

Frame Size	Ordering Number
D1	9K715
D2	9K716

AQUAVAR expansion cards can be included in the drive using the smart part number on page 4.

Expansion cards can also be ordered as a field installable option using the "K" part numbers listed.

COMMUNICATION OPTIONS (Repair Part Number)

MODBUS TCP (9K667)	LonWorks (9K670)
Profibus (9K668)	Profinet (9K671)
DeviceNet (9K669)	Ethernet IP (9K672)

INPUT/OUTPUT OPTIONS (Repair Part Number)

ANALOG I/O CARD (9K783) OPTION B

- Includes: 3 Analog IN for 0 - 10VDC
OR
0-20mA*
4-20mA*
Ni1000 Temperature Sensor
Pt1000 Temperature Sensor
3 Analog OUT for 0 - 10VDC
Battery backup for real-time clock



Used for: Providing battery backup of clock function during loss of power (real-time clock is native to the drive, and will reset to zero during power outage without Analog I/O card.)
Extension of analog I/O on control card (multi zone with 3 sensors)
Extended PID controllers with I/O's (set point inputs, sensor inputs and outputs)

AIN	GND	AIN	GND	AIN	GND	AOUT 0-10VDC	GND	AOUT 0-10VDC	GND	AOUT 0-10VDC	GND
1	2	3	4	5	6	7	8	9	10	11	12

* Requires 510Ω resistor

GENERAL I/O CARD (9K789) OPTION B

- Includes: 3 Digital IN, 2 Digital OUT, 2 Analog IN (voltage), 1 Analog OUT (current)
Used for: Extension of number of digital and analog inputs and outputs


COM	DIN	DIN7	DIN8	DIN9	GND(1)	DOUT3	DOUT4	AOUT2	24V	GND(2)	AIN3	AIN4
X30/	1	2	3	4	5	6	7	8	9	10	11	12

INPUT/OUTPUT OPTIONS (continued)

PTC THERMISTOR CARD (9K785) OPTION B

Includes: Twelve terminal PTC card


Used for: Monitor temperature of electric motor with PTC thermistor input (PTC Thermistor Card option is Certified for ATEX for use with motors in potentially explosive atmospheres.)



PT100 SENSOR INPUT CARD (9K786) OPTION B

Includes: Twelve terminal PTC100 card

Used for: Sensor Input for PT100 and PT1000 temperature sensors for motor bearing temperatures




INPUT/OUTPUT OPTIONS *(continued)*

RELAY CARD (9K787) OPTION B

Includes: 3 standard Form C, 240 VAC, 2 A

Used for: Extension of the number of output relays




BACKUP OPTIONS

24VDC BACKUP (9K659)

Includes: Pos and Neg Terminals for 24VDC

Used for: Interface to external 24 VDC auxiliary power supply
(Enables full LCP operation without line voltage supplied.)



Connection to 24V
Backup Supplier (A5-C2)

AQUAVAR IPC

DISCONNECT OPTIONS**FUSED AND STANDARD (NON-FUSED) DISCONNECT**

Includes: Fused disconnect enclosure includes fused disconnect in 3 phase TYPE 1, TYPE 12 & TYPE 4X. Standard disconnect available in single phase enclosures only.

Used for: Local disconnect of supply power to the drive.

COATING/EMC FILTER OPTIONS**3C3 BOARD COATING**

Includes: Additional protection for printed circuit board (PCB) above the standard protection to 3C2.

Used for: Aggressive environments where drive may be subject to corrosive gases. **NOTE:** THIS IS NOT A SUBSTITUTE FOR SIZING THE PROPER ENCLOSURE. ENCLOSURE SHOULD BE SELECTED BASED UPON ENVIRONMENT.

EMC OPTIONS

Includes: H2 filter (EN 55011 Class A2) standard on all models except 575V and single phase, 10, 20 and 30 hp. 575V and single phase, 10, 20 and 30 HP drives are not available with EMC filter.

Options: H1 or H3 (EN 55011 Class A1/B)

Used for: Increased level of EMC and RFI noise dampening

MOTOR MOUNTING OPTIONS**MOTOR MOUNTING**

Includes: Two motor mounting plate adapters sized for motors 56C through 440 frame

Used for: Intended for motor mounting of the VFD. Requires a vertical configuration and the vertical motor to have a mounting foot. The AQUAVAR with adapter plates mounts right to the motor foot!

DV/DT FILTERS* (ORDER SEPARATELY)

Includes: TYPE 3R dv/dt filter

Used for: Provides motor protection by limiting voltage spikes below 1,000 volts for long lead (submersible) applications.

FEATURES:

- 2 - 130 amps; 240V - 600V; 2 - 125 hp
- TYPE 3R Enclosure
- Carrier Frequency: 1 - 12 kHz
- Fundamental Frequency: 0 - 60 Hz
- Efficiency: > 98%
- Insulation Rating 600V Class
- Agency Approvals: UL, cUL
- Maximum Altitude: 6,000 feet
 - (Derate for applications above 6,000 feet)

* dv/dt filters are recommended on all pumping applications with Motor leads longer than 50'



DV / DT filters have been sized in the outdoor rated Product Charts (Page 8). DV /DT filters to be ordered separately to mount near the drive.







AQUAVAR IPC




MECHANICAL DIMENSIONS

Frame size (HP):	A2		A3		A4	A5	B1	B2	B3	B4	C1	C2	C3	C4
208-230V	1.5-3		5		1.5-3	1.5-5	7.5-15	20	7.5-15	20-25	25-40	50-60	30-40	50-60
380-460V	1.5-5		7.5-10		1.5-5	1.5-10	15-25	30-40	15-25	30-50	50-75	100-125	60-75	100-125
1.5-10			1.5-10	15-25		15-40	15-25	30-50	50-75	50-125	60-75	100-125		
Enclosure Options	IP20 OPEN	TYPE 1	IP20 OPEN	TYPE 1	TYPE 12 TYPE 3R TYPE 4X	TYPE 12 TYPE 3R TYPE 4X	TYPE 1 TYPE 12 TYPE 3R TYPE 4X	TYPE 1 TYPE 12 TYPE 3R TYPE 4X	IP20 OPEN	IP20 OPEN	TYPE 1 TYPE 12 TYPE 3R TYPE 4X	TYPE 1 TYPE 12 TYPE 3R TYPE 4X	IP20 OPEN	IP20 OPEN
Height in (mm)														
Enclosure	9.69 (246)	14.65 (372)	9.69 (246)	14.65 (372)	15.35 (390)	16.54 (420)	18.90 (480)	25.59 (650)	13.78 (350)	18.11 (460)	26.77 (680)	30.31 (770)	19.29 (490)	23.62 (600)
with De-coupling Plate	14.72 (374)	-	14.72 (374)	-	-	-	-	-	16.5 (419)	23.43 (595)	-	-	24.8 (630)	31.5 (800)
Backplate	10.55 (268)	14.76 (375)	10.55 (268)	14.76 (375)	15.35 (390)	16.54 (420)	18.90 (480)	25.59 (650)	15.71 (399)	20.47 (520)	26.77 (680)	30.31 (770)	21.65 (550)	25.98 (660)
Distance Between Mounting Holes	10.12 (257)	13.78 (350)	10.12 (257)	13.78 (350)	15.79 (401)	15.83 (402)	17.87 (454)	24.57 (624)	14.96 (380)	19.49 (495)	25.51 (648)	29.09 (739)	20.51 (521)	24.84 (631)
Width in (mm)														
Enclosure	3.54 (90)	3.54 (90)	5.12 (130)	5.12 (130)	7.87 (200)	9.53 (242)	9.53 (242)	9.53 (242)	6.50 (165)	9.09 (231)	12.13 (308)	14.57 (370)	12.13 (308)	14.57 (370)
Backplate	3.54 (90)	3.54 (90)	5.12 (130)	5.12 (130)	7.87 (200)	9.53 (242)	9.53 (242)	9.53 (242)	6.50 (165)	9.09 (231)	12.13 (308)	14.57 (370)	12.13 (308)	14.57 (370)
Distance Between Mounting Holes	2.76 (70)	2.76 (70)	4.33 (110)	4.33 (110)	6.73 (171)	8.46 (215)	8.27 (210)	8.27 (210)	5.51 (140)	7.87 (200)	10.71 (272)	13.15 (334)	10.63 (270)	12.99 (330)
Depth in (mm)														
Without A/B Option Card*	8.07 (205)	8.07 (205)	8.07 (205)	8.07 (205)	6.89 (175)	7.87 (200)	10.24 (260)	10.24 (260)	9.76 (248)	9.53 (242)	12.20 (310)	13.19 (335)	13.11 (333)	13.11 (333)
With A/B Option Card*	8.66 (220)	8.66 (220)	8.66 (220)	8.66 (220)	6.89 (175)	7.87 (200)	10.24 (260)	10.24 (260)	10.31 (262)	9.53 (242)	12.20 (310)	13.19 (335)	13.11 (333)	13.11 (333)
Screw Holes inches (mm)														
Screw Hole c	0.31 (8)	0.31 (8)	0.31 (8)	0.31 (8)	0.32 (8.2)	0.32 (8.2)	0.47 (12)	0.47 (12)	0.31 (8)	-	0.47 (12)	0.47 (12)	-	-
Screw Hole d	0.43 (11)	0.43 (11)	0.43 (11)	0.43 (11)	0.47 (12)	0.47 (12)	0.75 (19)	0.75 (19)	0.47 (12)	-	0.75 (19)	0.75 (19)	-	-
Screw Hole e	0.22 (5.5)	0.22 (5.5)	0.22 (5.5)	0.22 (5.5)	0.26 (6.5)	0.26 (6.5)	0.35 (9)	0.35 (9)	0.27 (6.8)	0.33 (8.5)	0.35 (9)	0.35 (9)	0.33 (8.5)	0.33 (8.5)
Screw Hole f	0.35 (9)	0.35 (9)	0.35 (9)	0.35 (9)	0.24 (6)	0.35 (9)	0.35 (9)	0.35 (9)	0.31 (7.9)	0.59 (15)	0.39 (9.8)	0.39 (9.8)	0.67 (17)	0.67 (17)
Max. Weight - lb (kg)	11 (5)	12 (5.5)	15 (6.8)	16 (7.3)	22 (10)	31 (14.1)	51 (23.1)	60 (27.2)	27 (12.2)	52 (23.6)	100 (45.4)	144 (65.3)	78 (35.4)	111 (50.4)







* Depth of enclosure will vary with different options installed.

DIMENSIONS


 A2 IP20/21*	 A3 IP20/21*	 A4 IP55/66 TYPE 12/4X	 A5 IP55/66 TYPE 3R/12/4X	 B1 IP21/55/66 TYPE 1/3R/12/4X	 B2 IP21/55/66 TYPE 1/3R/12/4X
OPEN/TYPE 1					



Top and bottom
mounting holes

 B3 IP20/21*	 B4 IP20/21*	 C1 IP21/55/3R/66 TYPE 1/3R/12/4X	 C2 IP21/55/3R/66 TYPE 1/3R/12/4X	 C3 IP20/21*	 C4 IP20/21*
OPEN/TYPE 1				OPEN/TYPE 1	

Top and bottom mounting holes
(B4 + C3 + C4 only)




AQUAVAR IPC


DIMENSIONS

Please note airflow directions

D1 ENCLOSURE, CABINET MOUNT - Dimensions in mm (in.)



D2 ENCLOSURE, CABINET MOUNT - Dimensions in mm (in.)




AQUAVAR IPC


DIMENSIONS

Please note airflow directions

EXTERIOR DIMENSIONS FOR D1H WITH TYPE 3R KIT (9K715) - Dimensions in mm (in.)



EXTERIOR DIMENSIONS FOR D2H WITH TYPE 3R KIT (9K716) - Dimensions in mm (in.)




AQUAVAR IPC


DIMENSIONS

Please note airflow directions

D3 ENCLOSURE, CABINET MOUNT - Dimensions in mm (in.)




D4 ENCLOSURE, CABINET MOUNT - Dimensions in mm (in.)




AQUAVAR IPC

DIMENSIONS

D5 ENCLOSURE - Dimensions in mm (in.)



D7 ENCLOSURE - Dimensions in mm (in.)



Xylem |'zīləm|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating advanced technology solutions to the world's water challenges. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. Our products and services move, treat, analyze, monitor and return water to the environment, in public utility, industrial, residential and commercial building services settings. Xylem also provides a leading portfolio of smart metering, network technologies and advanced analytics solutions for water, electric and gas utilities. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise with a strong focus on developing comprehensive, sustainable solutions.

For more information on how Xylem can help you, go to www.xylem.com

Xylem Product Cybersecurity:

Xylem values your system security and the availability of your critical services. For more information on Xylem cybersecurity practices or to contact the cybersecurity team please visit xylem.com/security.



Xylem Inc.

www.xylem.com

Xylem and AQUAVAR, are trademarks of Xylem Inc. or one of its subsidiaries.
MODBUS is a registered trademark of Schneider Electric USA, Inc.
© 2022 Xylem Inc. BCPAQIPC R8 January 2022