



X-Pro all-in-one Integrated Self-Priming Booster

Package Solution for Residential Applications



Other plug types available – see Features

How does the Lowara X-Pro improve water pressure in homes?

Its features enhance residential water pressure with programmable settings, a built-in pressure tank, and a high-efficiency motor, ensuring consistent flow and quiet operation.


Xylem is introducing Lowara X-Pro, the all-new Residential Booster Package: the perfect solution for homes with low water pressure. This integrated, self-priming, compact water booster pump is designed to provide ideal pressure inside your home, so you can enjoy all the benefits of a strong, consistent water flow. With its programmable pressure, you can set the pump to turn on and off automatically. And because it's whisper-quiet, you won't even notice its presence. The Residential Booster Package is also easy to install, allowing you to get up and running in no time.

Benefits

- Easy to install and use
- Whisper-quiet operation
- Compact design
- Highly efficient

Applications


- Water pressure in single or two-family houses
- Garden irrigation



Features

- Max head: 45 m
- Max flow: 5 m³/h
- Max rated pressure: 10 bar
- Pumped liquids:
 - fresh water
 - temperature range: 0 to +50°C
 - PH: 6.5 - 8.5
 - Hardness: 25°dH
- Environment temperature range: 0 to +55°C
- Humidity: ≤95%
- Max noise: ≤57 dB(A)
- High-efficiency variable speed synchronous motor
- Motor Power: 600W
- PCB and motor cooled by water fluid circulation
- IP rating: 44
- Winding insulation class: F
- Separate drainage hole is on the base to prevent condensation
- Built-in pressure tank that stabilizes the pressure during operation
- Self-priming pump with 8 m suction head
- Available with Schuko Type F plug, Type I plug (Australia), and Type G plug (U.K. and Saudi Arabia)

Performance Curve



Product Display

