



LSW Series Self-Priming Jet Pump

The LSW series clean water electric centrifugal pump is used for water transfer and pressure boosting purposes across a wide range of household applications.

Engineered for enduring reliability, the pump has a robust design with a cast iron pump body and casing, and bronze impeller. Its built-in Venturi Jet provides optimal water flow and self-priming capabilities, enhancing the adaptability of the LSW Series for various applications.

All LSW Series pumps are subjected to rigorous testing and stringent quality checks, assuring the highest standard of quality and providing you with peace of mind.

Key Features



Long-lasting
and reliable



Easy to
install and
maintain



Self-priming

Applications



Water supply
and boosting
pressure



Washing
purposes



Lawn & garden
sprinkling



Car wash



 **LOWARA**
a xylem brand

Product Information


Specification	LSW075	LSW100
Max. Flow Rate	39 litres/min	48 litres/min
Max. Head	37m	40m
Motor Power	0.75HP	1HP
Voltage	220~240V / 60Hz	220~240V / 60Hz
Ambient Temperature	0° - 40°C	0° - 40°C
Speed	3400 (r/min)	3400 (r/min)
Suction & Discharge Diameter	NPT 1"	NPT 1"
Recommended Fittings	  	   

Xylem reserves the right to modify specifications

Model	H (mm)	W (mm)	L (mm)
LSW075/ LSW100	215	181	435



Performance Curves



Regional Headquarters

Xylem Water Solutions Singapore Pte Ltd
 3A International Business Park,
 Tower B, #10-10/18, ICON@IBP
 Singapore 609935
xylem.asia@xylem.com
www.xylem.com/sg

Follow us on LinkedIn

