



Full Circle® Redi-Clamp®

All Stainless Steel

247

IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)

[Sales Terms & Conditions](#)

[Freight Policy](#)

[Returns Policy](#)

[Corrosion & Product Selection Notice](#)



THIS PRODUCT DOES NOT RESTRAIN PIPE MOVEMENT. Proper anchoring is required to prevent pipe pullout. Failure to anchor or improper anchoring can result in dangerous pipe content escape, property damage, serious injury, or death. Read the product installation instructions prior to installing this product.

Description: A repair clamp designed to repair pin holes, punctures or splits in rigid pipe, like Steel, plastic, or Copper tube.

Application: Works on Steel, Copper, and IPS-sized PVC and HDPE.

Key Features:

- Built to a specific pipe O.D.
- Drop-in bolts help ease installation
- Standard widths are 3", 6" and 12"
- Available in IPS and Copper tube sizes
- Provides 360° coverage, covering the full pipe surface
- Use 6" long or longer clamps to join pipe ends of like size
- 18-8 Type 304 Stainless Steel band for corrosion resistance
- Economical means of repairing pin hole leaks, punctures and splits in pipe

Materials Specifications (subject to change):

BAND: Stainless Steel Type 304

LUGS: ASTM A743 GRCF8 Stainless Steel (304 Equivalent)

GASKET: Nitrile (Buna N) compounded to produce resist oil, natural gas, acids, alkalies, most (aliphatic) hydrocarbon fluids, water and many chemicals

NUTS/BOLTS: 304 Stainless Steel with fluoropolymer coated nuts to prevent galling

Working Pressure: Up to 150 PSI

Pipe Applications: Steel, Copper, and IPS-sized PVC and HDPE

Sizes (in inches): 10, 12, 14, 16, 18, 20, 22, 24, 30



Full Circle® Redi-Clamp®

All Stainless Steel

247

STANDARD				CATALOG NUMBER	QTY. PER CTN.	METRIC			
NOMINAL PIPE SIZE INCHES	O.D. INCHES	WIDTH INCHES	WT. EACH LBS.			NOMINAL PIPE SIZE MM	O.D. MM	WIDTH MM	WT. EACH KG.
1/2	0.63	3	.70	247-00006303-000	6	15	16.00	76	0.32
		6	1.40	247-00006306-000	6			152	0.64
1/2	0.84	3	.80	247-00008403-000	6	15	21.30	76	0.36
		6	1.60	247-00008406-000	6			152	0.73
		12	3.20	247-00008412-000	4			305	1.46
3/4	0.88	3	.80	247-00008803-000	6	20	22.35	76	0.36
		6	1.60	247-00008806-000	6			152	0.73
3/4	1.05	3	.85	247-00010503-000	6	20	26.70	76	0.39
		6	1.70	247-00010506-000	6			152	0.77
		12	3.40	247-00010512-000	9			305	1.54
1	1.13	3	.87	247-00011303-000	6	25	28.70	76	0.39
		6	1.70	247-00011306-000	6			152	0.77
1	1.32	3	.90	247-00013203-000	6	25	33.53	76	0.41
		6	1.70	247-00013206-000	6			152	0.82
		12	3.60	247-00013212-000	9			305	1.63
1 1/4	1.38	3	.90	247-00013803-000	6	32	35.05	76	0.41
		6	1.80	247-00013806-000	6			152	0.82
1 1/4	1.66	3	.95	247-00016603-000	6	32	42.20	76	0.88
		6	1.95	247-00016606-000	6			152	0.43
		12	3.90	247-00016612-000	6			305	1.77
1 1/2	1.63	3	.95	247-00016303-000	6	40	41.40	76	0.43
		6	1.95	247-00016306-000	6			152	0.88
1 1/2	1.90	3	1.00	247-00019003-000	6	40	48.30	76	0.45
		6	2.00	247-00019006-000	6			152	0.91
		12	4.00	247-00019012-000	6			305	1.81
2	2.13	3	1.30	247-00021303-000	6	50	54.10	76	0.59
		6	2.60	247-00021306-000	6			152	1.18
2	2.38	3	1.60	247-00023803-000	8	50	60.45	76	0.73
		6	3.20	247-00023806-000	6			152	1.45
		12	6.40	247-00023812-000	4			305	2.90