



e-XC Single Stage, Double Suction Split Case Pump

60Hz Performance Range by Size

2-Pole




4-Pole



Every e-XC pump has two distinct impeller designs - i.e. the 3x5x8.5 model is also available as 3x5x8. See individual performance curves for more details.


60Hz Performance Range by Size

6-Pole




Comparison to Previous Models

60 Hz – e-XC & AC 8100/AC 9100, 890 rpm




60 Hz – e-XC & AC 8100/AC 9100, 1180 rpm



Comparison to Previous Models

60 Hz – e-XC & AC 8100/AC 9100, 1780 rpm



60 Hz – e-XC & AC 8100/AC 9100, 3560 rpm

