



AquaBox Compact & Space Saver Series

A COMPACT SYSTEM DESIGNED FOR TRANSPORTING CLEAN WATER.

AquaBox System

Compact design, Constant pressure

The all in one Aquabox System for Domestic and Commercial clean water applications. A compact system designed for transporting clean water with constant pressure. The Aquabox System makes plumbing easy, with less work, creating more space and less noise for greater comfort. A cost effective plug n'play system from Southern Pumps Ltd

Components Tanks

- 180 Litre Cylindrical
- 180 Litre Rectangular
- 300 Litre Triangular
- 500 Litre Triangular
- Lowara SC205 Stainless Steel Submersible Scuba Pump
- Auto Genyo Controller
- Ball Valve & Float
- 1" FM LA Ballvalve



SCUBA Series

The Lowara SC205 Scuba, is a 5" Close Coupled Multistage submersible pump (0.55kw) with Electrical motor cooled by pumped liquid which is FDA compliant. The Lowara Scuba can be installed in vertical and horizontal positions. The pumps low noise tolerance, stainless steel structure, Double Mechanical Seals system and engineered motor is designed for constant use.


GENYO Series

The Lowara Genyo electronic control and protection system designed with pressure sensors, delivers constant water pressure on demand. The Genyo enables automatic control of pump start up and shut down based on actual water demand, preventing any pressure fluctuations. The Genyo has built in dry run protection and auto-restart.

Please Note: Overfl ow connection not supplied

Test performance data

Flow rate Q (l/min)	1	2	3	4	5				
Total head Ht (m)	76.91	56.87	33.1	16.51	7E-06				
	10.71	20.16	28.68	32.42	35				



Tank Dimensions Dimensions in mm



Capacity 180 Litre

Height 920mm Width 670mm
Diameter 575mm including handles



Capacity 180 Litre

Length 700mm Height 610mm
Width 590mm



Capacity 300 Litre

Length 1150mm Height 690mm
Width 610mm



Capacity 500 Litre

Length 1300mm Height 860mm
Width 700mm

Tank Details

The Tanks are manufactured from linear low density polyethylene with UV light stabilizer for outdoor endurance, they are compact and strong. The Tanks light weigh design makes for easy transportation and installation.