



Xylem Rental Guide

Xylem Rental Solutions for Your Pumping or
Treatment Challenges

0845 707 8012

24/7 Rapid Response

xylem

rental
solutions

Welcome to our Rental Guide



Xylem is a force to be reckoned with when providing total solutions for fluid handling and control. With a history spanning 100 years, it is a company passionate about innovation and determined to solve the most challenging water issues. Xylem's powerful combination of products, services and applications expertise serves market sectors including Public Utilities, Infrastructure, Municipal, Building Services and Industry.

Our Rental division, specialises in the rental of Flygt electric submersible pumps, Godwin prime assisted diesel pumps, Wedeco and Sanitaire treatment systems. Xylem remain unique in the market place supporting rental applications with the products that Xylem also manufacture as Original Equipment Manufacturers of each of the famous brands included in the range. Our skilled team of engineers offer unprecedented technical backup and design of bespoke pumping and treatment systems, whether temporary or semi-permanent, for anything from a small amount of nuisance water to the movement of sewage and major flow diversion schemes.

By choosing Xylem Water Solutions for your rental requirements, you gain automatic access to a wealth of experience and technical knowledge. Our engineers can assess your needs, design your pumping or treatment system and install it. Offering a 24/7 rapid response service, with fully owned transportation including lifting cranes and strategically located regional depots throughout the UK and Ireland, you can be confident in our ability to react quickly to your rental needs.



4	General Guide to Pump Selection
5	Guide to Performance Data
6	Pumping Definitions
7 - 14	2000/BS Series - Drainers
15 - 20	2600 Range - Drainers
21 - 24	2800 Range - Drainers
25	Flygt 2000 Series Electrical Information
26 - 29	Flygt Concertor™
30 - 36	3000/N Series - Sewage
37 - 38	N Type Chopper Pumps
39 - 47	Great and Grey – Sewage
48	Flygt 3000 Series Electrical Information
49	Lowara Clean Water Booster Sets
50	Monitoring & Control
51	Electrical Equipment
52 - 53	Soft Start Control Panels - Specification
54 - 57	VFD Starter Panel - Specification
58 - 65	Godwin CD series
66 - 68	Godwin HL series
69 - 72	Godwin NC series
73 - 75	UV Water Treatment
76 - 79	Mixers
80 - 81	Aeration - Radial Aerators
82	Radial Aerators - Oxygen Transfer Rate
83	Aeration - Flyjet
84	Pump Flotation Modules
85 - 86	Hoses and Fittings
87	Friction Loss in Pipe Fittings Chart
88 - 89	Weight Reference Guide
90 - 91	Conversion Factors
92	Flange Sizes
93	Case Study - Temporary Over Pumping
94	Case Study - UV Treatment Project
95	Contact Us

General Guide to Pump Selection

Check:-

The Electrical Supply available – What Voltage, Single or 3 Phase and the Maximum Amperage. If the Power Supply is inadequate, please ask for details of Generators or consider using a Godwin Prime Assisted Diesel Pump.

Total Head Requirement – The most important calculation to get right! It is the sum of the Total Static Head (the vertical distance from the Suction Strainer to the point of Discharge) plus any Friction Loss allowances. When sizing a pump, the critical thing to determine is the Total Generated Head (TGH) requirement.

Calculation:-

Static Suction (strainer to the pump) + **Static Delivery** (from pump to the point of Discharge) + **Friction Loss** (resistance incurred by liquid when flowing through hoses) = **Total Generated Head**.

Dirty Water or Solids Handling?


Use Drainer Submersibles (BS Series) and General Purpose Diesels for Dirty Water pumping and where particles are relatively small e.g. sand and gravel.

Use Sewage Submersibles (N Series) and Solids Handling Diesels for Sewage pumping and where particles are larger e.g. stones and debris.

Guide to Performance Data


The following curves are QH charts showing the performance of the hydraulic unit at constant shaft speeds. Q is represented as litres per second, and total head, H, is in metres.

The data represented in this section is for your guidance only. Detailed information can be obtained from your local Xylem Sales Engineer.



BS Pumps

The curve is the specified performance of the impeller selected. The values shown are for a BS 2125 pump. Impeller characteristics are coded as follows: LT=Low head. MT=Medium head. HT=High head. SH=Super High Head.



N Pumps

The power consumption is shown on the chart. The power consumption values for two selected performance duty points are shown by plotted straight lines from the lower to the upper chart. The lower chart and corresponding table provide performance data for different impellers used in a high head 3102 pump. Additional charts for LT, MT and SH models are shown for each respective pump type.

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Through let, mm	Motor rating kW	rpm	Available versions
252	1	80	Ø52	4.4	2850	NP/NS
254	1	80	Ø46	4.4	2850	NP/NS

Pumping Definitions

Pumping is the addition of energy to a fluid, which is used mainly for the purpose of moving the fluid from one point to another.

Centrifugal Pumps

One which transfers energy to the liquid by means of an impeller; i.e. "A rotating device equipped with suitable vanes". (The liquid is therefore delivered in a continuous and uninterrupted flow).

Positive Displacement Pumps

One which transfers energy to a liquid by means of a reciprocating piston, or similar device, giving an intermittent or "pulsed flow".

Ejector or Jet Pumps

By mixing a high speed drive medium with a low velocity pumped medium, an energy exchange is achieved converting velocity energy into pressure, giving a continuous flow.

Q = Capacity or Volume

H = Total Head

Total Head = Static Head + Friction loss head.

Static Head

The head against which the pump must work when the liquid is stationary.

Friction loss head

The head generated by friction of moving liquid, against the walls of the discharge pipes.

Net Positive Suction Head (npsh)

Energy from an outside source i.e. static head or atmosphere pressure required to ensure liquid enters the pump volute.

Cavitation

Cavitation occurs when there is insufficient n.p.s.h. i.e., Too low a suction pressure induces cavitation. This causes erosion to the metal surfaces due to the vapour bubble collapsing, allowing the liquid to rush into the subsequent spaces at high velocity, thus creating a water hammer effect.

Flygt 2000 Series Dewatering Pumps



Introduction

Flygt Type BS - Pumps are suitable for a very broad field of application. They are used for dewatering on construction sites for houses, streets and roads, tunnels and rock caverns, harbours and dams, for drainage and ballast pumping in shipyards, for drainage in the event of flooding in mines and industrial plants, for cooling, clean water and raw water supply, water spraying, etc.

The Type BS - Pump is of transportable design and requires no installation. All you need to do is to lower it into water and start it. There is a type BS pump suitable for all applications - be it for high capacities, high heads, confined spaces or explosive environments.

The Type BS - Impeller is an open or semi-open channel impeller, made of abrasion resistant high chromium steel and designed specifically for handling media containing highly abrasive materials, such as clay, sand and drilling fines etc.



Flygt 2000 Series Dewatering Pumps

Can be installed in a variety of applications



The Type BS - Pump can stand directly on the sump floor



or can be suspended from a rope or chain





The compact design enables Type BS - Pumps to be used in confined spaces - a 200mm diameter pipe is sufficient for the slimmest pump



The head generated can be increased by connecting two or more Type BS - Pumps in series


Flygt 2000 Series Dewatering Pump Dimensions

Pump type	A (mm)	B (mm)	Strainer Opening (mm)
BS2052	530	200	5x18
BS2066	520	385/405/288	7x21
BS2102			
MT	505	390/430	7x40
HT	505	375/390/335	7x40
BS2125			
MT	710	485/515/535	6x50
HT	710	465/390	6x50
BS2151			
LT	745	640/655	10x42
MT	745	640/655	10x42
HT	745	570/590	10x42
BS2201			
Cast Iron			
MT	1200	620	15x45
HT	1050	430	10x10
Aluminium			
MT	1253	500	15x45
HT	1050	430	10x10
BS2250			
MT	1144	885/912	15x45
HT	1144	830	15x45
BS2400			
MT	1250	780	10x10
HT	1250	680	10x10
BS2610	570	230	7 x 16
BS2620	620	275	7 x 16
BS2640			
MT	760	375	8 x 18
HT	760	342	8 x 18
BS2660			
MT	832	430	9 x 18
HT	832	430	9 x 18
BS2670			
MT	955	500	10 x 20
HT	955	480	10 x 20
BS2840			
MT	762	592	10mm Dia
HT	762	553	10mm Dia
BS2860			
MT	889	668	10mm Dia
HT	889	646	10mm Dia
BS2870			
MT	991	740	12mm Dia
HT	991	719	12mm Dia



Flygt BS2052 and BS2066

BS 2052




Motor 1kW, 2700rpm
Max. power input 1.4kW
Weight 18kg

Dimensions:
A - 530mm
B - 200mm
Hose Size: 50mm



BS 2066




Motor 2.2kW, 2800rpm
Max. power input 2.8kW
Weight 30kg

Dimensions:
A - 520mm
B - 362/375mm
Hose Size: 75mm



Flygt BS2102 and BS2125


BS 2102 MT & HT



Motor 3.7kW/ 5.2kW, 2850rpm
Max. power input 4.5kW/6.3kW
Weight 50kg

Dimensions:
A - 505mm
B - MT - 395/430mm HT - 375/390mm Hose
Size: HT 75mm MT 100mm

BS 2125 MT & HT




Motor MT 8.0kW, 2800rpm
Max. power input 9.5kW
Weight MT 83kg HT 92kg

Dimensions:
A - 710mm
B - MT 485/515/535mm HT 465mm
Hose Size: HT 75mm MT 150mm

Flygt BS2151 and BS2201

BS 2151 MT & HT




Motor 20kW, 2900rpm
Max. power input 23kW
Weight 165kg



Dimensions:
A - 745mm
B - MT 640/655mm MT - 570/590mm
Hose Size: HT 100mm LT 150mm

BS 2201 LT



Motor 37kW, 1465rpm
Max. Power input 41kW
Weight - 280kg




Dimensions:
A - 1330mm
B - 500mm
Hose Size: 200mm

Flygt BS2201 and BS2250



BS 2201 MT & HT




Motor 37kW, 2920rpm
Max. power input 41kW
Weight - 280kg



Dimensions:
A - 1330mm
B - 500mm
Hose Size: MT 200mm, HT 100mm

BS 2250 MT/HT




Motor 54kW, 1470rpm
Max. power input 58kW
Weight 540kg



Dimensions:
A - 1100mm
B - 950mm
Hose Size: HT 150mm, MT 200mm, MT 250mm

Flygt BS2400

BS 2400 MT & HT



Motor 90kW, 2970rpm
Max. power input 97kW
Over temperature protection in
stator windings
Weight MT 900kg HT 985kg



Dimensions:
A - MT 1250mm HT 1251mm
B - MT 778mm HT 680mm
Hose size: HT - 100mm MT - 150mm



Introduction

Clearing your worksite of unwanted water is critical to productivity. Flooding means time delays, cost overruns and unsafe working conditions. To get to the bottom of any dewatering job, rely on Flygt 2600 pumps.


Undertaking tough dewatering jobs is what the Flygt 2600 series does best. It ensures that you can get on with the work at hand safely and reliably. All this, thanks to extreme portability, automatic operation, easy maintenance, lasting performance.

The Flygt 2600 series is built to last. Radically engineered from the ground up, these robust dewatering pumps feature innovative hydraulics, durable materials and a practical, ergonomic design. The result is unmatched wear resistance, consistent performance over time.

Flygt 2600 pumps cover low, medium, high and super-high pressures to handle most any application for worksites of every size.

Flygt BS2610

BS 2610 MT 110V Single Phase




Rated Power 0.85kW
Weight 21kg



Dimensions:
Max. Height - 570mm
Max. Width - 230mm
Discharge Ø - 2"
Strainer Hole: 7x16mm

BS 2610 MT 400V 3 Phase



Rated Power 1.2kW
Weight 21kg




Dimensions:
Max. Height - 570mm
Max. Width - 230mm
Discharge Ø - 2"
Strainer Hole: 7x16mm

Flygt BS2620 and BS2640



BS 2620 MT




Rated Power 2.2kW
Weight 32kg



Dimensions:
Max. Height - 620mm
Max. Width - 275mm
Discharge Ø - 3"
Strainer Hole: 7x16mm

BS 2640 MT




Rated Power 5.6kW
Weight 51kg



Dimensions:
Max. Height - 760mm
Max. Width - 375mm
Discharge Ø - 4"
Strainer Hole: 8x18mm

Flygt BS2640 and BS2660

BS 2640 HT




Rated Power 5.6kW
Weight 51kg



Dimensions:
Max. Height - 760mm
Max. Width - 342mm
Discharge Ø - 3"
Strainer Hole: 8x18mm

BS 2660 MT




Rated Power 10kW
Weight 78kg



Dimensions:
Max. Height - 832mm
Max. Width - 430mm
Discharge Ø - 6"
Strainer Hole: 9x18mm

Flygt BS2660 and BS2670

BS 2660 HT




Rated Power 10kW
Weight 78kg



Dimensions:
Max. Height - 832mm
Max. Width - 430mm
Discharge Ø - 4"
Strainer Hole: 9x18mm

BS 2670 MT




Rated Power 18kW
Weight 141kg



Dimensions:
Max. Height - 955mm
Max. Width - 500mm
Discharge Ø - 6"
Strainer Hole: 10x12mm

Flygt BS2670

BS 2670 HT



Rated Power 18kW
Weight 141kg



Dimensions:
Max. Height - 955mm
Max. Width - 480mm
Discharge Ø - 4"
Strainer Hole: 10x12mm

Flygt BIBO 2800 Range

For decades whenever a dewatering challenge seemed too tough or too harsh, the answer has been simple; Flygt BIBO.


From the product brand and pumps that set the standard in dewatering comes a new and superior series of submersible dewatering pumps: Flygt BIBO 2800 series. It still has the iconic look; a shape that means stability and robustness. Inside the pumps you will find the latest technology such as the Dura-Spin hydraulic system and Plug-In seal. The range handles flows of up to 100 l/s with heads to 90 m and available with power ratings from 3.7 to 18kW.

Specifically targeted at mining operations, tunnelling and construction site applications.



Flygt BS2840

BS2840 MT




Rated Power - 5kW
Weight - 56kg



Dimensions:
Height - 762mm
Width - 367mm
Discharge - 100mm

BS2840 HT




Rated Power - 6kW
Weight - 56kg



Dimensions:
Height - 762mm
Width - 367mm
Discharge - 80mm



BS2860 MT




Rated Power - 10kW
Weight - 91kg



Dimensions:
Height - 889mm
Width - 425mm
Discharge - 150mm

BS2860 HT




Rated Power - 10kW
Weight - 91kg



Dimensions:
Height - 889mm
Width - 425mm
Discharge - 100mm

Flygt BS2870

BS2870 MT




Rated Power - 18kW
Weight - 125kg



Dimensions:
Height - 991mm
Width - 500mm
Discharge - 150mm

BS2870 HT



Rated Power - 18kW
Weight - 125kg



Dimensions:
Height - 991mm
Width - 500mm
Discharge - 100mm

Flygt 2000 Series Electrical Information

Pump Model	kW (Shaft Power)	Voltage	Phase	FLC Amps	DOL Starting Current AMPS	Starting Method	Minimum Generator in kVA to Start/Run
BS2052	1.0	110	1	14.0	46	CAP	5
BS2052	1.0	230	1	3.8	17	CAP	5
BS2052	1.0	400	3	2.2	9.9	DOL	7.5
BS2066	2.2	400	3	4.5	26	DOL	20
BS2071	3.0	400	3	6.6	43	DOL	30
BS2075	3.7	400	3	7.1	36	DOL	25
BS2075	5.5	400	3	11.0	50	DOL	35
BS2084	7.5	400	3	13.0	78	DOL	55
BS2102	5.2	400	3	10.0	71	DOL	50
BS2125	8.0	400	3	15.0	125	DOL	90
BS2151	20.0	400	3	35.0	281	SOFT	100
BS2201	37.0	400	3	65.0	430	SOFT	150
BS2250	54.0	400	3	104.0	590	SOFT	450
BS2400	90.0	400	3	148.0	1245	SOFT	425
KS2610	0.9	110	1	11.0	38	CAP	5
KS2610	1.2	400	3	2.7	12	DOL	10
BS2620	2.2	400	3	4.7	27	DOL	20
BS2640	5.6	400	3	11.0	48	DOL	35
BS2660	10.0	400	3	19.0	107	DOL	75
BS2670	18.0	400	3	32.0	213	DOL	150
BS2840	5.6	400	3	11.0	78	DOL	55
BS2860	10.0	400	3	19.0	115	DOL	80
BS2870	18.0	400	3	33.0	238	SOFT	85

When two pumps are driven by the same generator, the rating required is 1.5 times that indicated for a single pump

Some form of time lag should be connected to prevent both pumps from starting simultaneously, unless the generator has been selected for pumps to start simultaneously.

The Information contained within this document is for guidance only and is accurate to the best of our knowledge at time of going to print.

Flygt Concertor™

To meet the growing challenges of modern wastewater, we're proud to introduce Flygt Concertor™, a breakthrough in wastewater pumping.

A new way of thinking

Using a combination of advanced software functions and state-of-the-art hardware, Concertor senses the operating conditions of its environment and adapts the pumping performance in real time, making smart decisions and providing feedback to pumping station operators.

One powerful solution, unlimited possibilities

Concertor combines a fully integrated control system with IE4 equivalent motor efficiency, our patented Adaptive N-hydraulics and intelligent functionalities such as clog detection and pump cleaning as well as soft start and motor protection.



Concertor™ N - State-of-the-art N-hydraulics

A new generation of our Adaptive N-technology enables high efficiency and lower energy usage. The Adaptive N-impeller moves axially upward when needed, allowing bulky fibrous material and debris to pass through smoothly. After the debris has passed, the hydraulic pressure returns the impeller to its original position. Not only does this prevent clogging and reduce stress on the shaft, seals and bearings, but it enables a sustained low usage of energy. As with all Flygt N-pumps, this feature delivers constant self-cleaning functionality.

Flygt Concertor™ offers a pump performance field covering a wide range of pump curves. No need for the perfect station design data. No need for a large inventory. One pump can be adjusted to suit specific conditions without having to change impeller diameters or motor sizes.

- Selection from a performance field instead of a fixed performance curve allows for enhanced operational flexibility.
- Performance can be fine-tuned and pre-selected without changing the impeller.
- Allows direct connection of the motor cable to the existing control panel contactor. Supply requires short circuit protection.
- Connects to DOL starter (No overload required) can also be connected to star delta starter provided the configuration meets with certain criteria – please contact Xylem for details.
- Anti-clogging protocol.
- Advanced motor protection
- Adjustable performance with service tool via Laptop.



Flygt Concenteror™


Easier product selection and reduced inventory

With Flygt Concenteror™, pump selection has never been easier due to the unlimited number of performance curves and enables pump performance to be easily changed on site or remotely.

Choose from a performance field

With Concenteror, you can now choose the exact pump performance from a field rather than from fixed curves.

This simplifies the selection process, since calculating your exact duty point is no longer critical.



Model	Kw (shaft)	Discharge Size		
		80mm	100mm	150mm
N6020	2.2	X	X	X
N6020	4.0	X	X	X
N6020	5.5	X	X	X
N6020	7.3	X	X	N/A

Guide rail sliding bracket/flange 80mm dia. Adapter Claw
Guide rail sliding bracket/flange 100mm dia. Adapter Claw
Guide rail sliding bracket/flange 150mm dia. Adapter Claw



Supply: 400/3/50.

Motor: IE4 Synchronous concentrated windings, Permanent Magnet Motor.

Rated Power: 2.2kW – 7.3kW depending on model.

Hydraulics: Adaptive N Impeller c/w Guide Pin.

Discharge Size: 80mm – 150mm depending on model.

Speed Range: 500-3600 RPM

Cooling System: Liquid free heat conduction technology.



Replacement of 3000 series by Concertor™ N

Xylem Rental will configure the Concertor pump with the correct motor rating and performance characteristics to enable it to replace the conventional Flygt 3085, 3102, 3127 and 3153 pump models.

Model	Impeller	Rated Shaft Power	DN	Concertor	DN	* Concertor Maximum Shaft Power
N 3085 MT	462	1.3	80	Concertor N 80	80	2.2
N 3085 MT	463	1.3	80	Concertor N 80	80	2.2
N 3085 MT	460	2.0	80	Concertor N 80	80	2.2
N 3085 MT	461	2.0	80	Concertor N 80	80	2.2
N 3085 MT	462	2.0	80	Concertor N 80	80	2.2
N 3085 MT	463	2.0	80	Concertor N 80	80	2.2
N 3085 SH	253	2.4	80	Concertor N 80	80	4.0
N 3085 SH	254	2.4	80	Concertor N 80	80	4.0
N 3085 SH	255	2.4	80	Concertor N 80	80	2.2
N 3085 SH	256	2.4	80	Concertor N 80	80	2.2
N 3102 LT	420	3.1	100	Concertor N 100	100	4.0
N 3102 LT	421	3.1	100	Concertor N 100	100	4.0
N 3102 LT	423	3.1	100	Concertor N 100	100	2.2
N 3102 LT	420	3.1	150	Concertor N 150	150	4.0
N 3102 LT	421	3.1	150	Concertor N 150	150	4.0
N 3102 LT	423	3.1	150	Concertor N 150	150	2.2
N 3102 SH	255	4.2	80	Concertor N 80	80	4.0
N 3102 SH	256	4.2	80	Concertor N 80	80	4.0
N 3102 MT	460	3.1	100	Concertor N 100	100	4.0
N 3102 MT	461	3.1	100	Concertor N 100	100	4.0
N 3102 MT	462	3.1	100	Concertor N 100	100	4.0
N 3102 MT	463	3.1	100	Concertor N 100	100	2.2
N 3102 MT	464	3.1	100	Concertor N 100	100	2.2
N 3127 HT	488	4.7	100	Concertor N 100	100	4.0
N 3127 HT	489	4.7	100	Concertor N 100	100	4.0
N 3127 HT	486	5.9	100	Concertor N 100	100	7.3
N 3127 HT	487	5.9	100	Concertor N 100	100	5.5
N 3127 HT	488	5.9	100	Concertor N 100	100	4.0
N 3127 HT	489	5.9	100	Concertor N 100	100	4.0
N 3127 SH	245	7.4	80	Concertor N 80	80	7.3
N 3127 SH	246	7.4	80	Concertor N 80	80	7.3
N 3127 SH	247	7.4	80	Concertor N 80	80	5.5
N 3127 SH	248	7.4	80	Concertor N 80	80	5.5
N 3127 LT	424	5.9	150	Concertor N 150	150	5.5
N 3127 LT	425	4.7	150	Concertor N 150	150	4.0
N 3127 LT	425	5.9	150	Concertor N 150	150	4.0
N 3127 LT	426	4.7	150	Concertor N 150	150	4.0
N 3127 LT	426	5.9	150	Concertor N 150	150	4.0
N 3127 MT	437	5.9	100	Concertor N 100	100	5.5
N 3127 MT	437	5.9	150	Concertor N 150	150	5.5
N 3127 MT	438	4.7	100	Concertor N 100	100	5.5
N 3127 MT	438	4.7	150	Concertor N 150	150	5.5
N 3127 MT	438	5.9	100	Concertor N 100	100	5.5
N 3127 MT	438	5.9	150	Concertor N 150	150	5.5
N 3127 MT	439	4.7	100	Concertor N 100	100	4.0
N 3127 MT	439	4.7	150	Concertor N 150	150	4.0
N 3127 MT	439	5.9	100	Concertor N 100	100	4.0
N 3127 MT	439	5.9	150	Concertor N 150	150	4.0
N 3153 MT	436	7.5	150	Concertor N 150	150	7.3
N 3153 HT	454	7.5	100	Concertor N 100	100	7.3
N 3153 HT	455	7.5	100	Concertor N 100	100	7.3
N 3153 HT	456	7.5	100	Concertor N 100	100	7.3
N 3153 SH	275	11.0	80	Concertor N 80	80	7.3
N 3153 SH	276	11.0	80	Concertor N 80	80	7.3

*Xylem Rental will configure the Concertor pump with the correct Motor rating and performance characteristics prior to delivery.

Flygt 3000 N Series Solids Handling Pumps

N Pump Technology

Sustained high efficiency for wastewater handling

With its unique semi-open, self-cleaning impeller, the N-pump series can handle fluids with high concentrations of fibrous material, whilst still maintaining a high level of pumping efficiency over long duty periods. The special relief groove in the volute reduces the risk of clogging by creating a self-cleaning flow path through the pump.

N Series Pumps

N series pumps are available, contact your local Flygt Rental Centre for curve details: N 3085, N 3102, N 3127, N 3153, N 3171, N 3202, N 3301



Adaptive N-impellers




The Adaptive N-hydraulics further improves the self-cleaning characteristics of N-technology with unmatched clog-free performance. This is achieved through the unique axial movement of the Adaptive N-impeller.

The Adaptive N-impeller is designed to move axially upwards when needed, allowing the most bulky of rags and toughest of debris to pass through smoothly. After the debris has passed, the hydraulic pressure returns the impeller to its original position.

The axial movement of this hydraulic reduces stress on the shaft, seals, and bearings, thereby extending their lifespan. Ultimately clog-free performance requires almost none, or at the very most, simple maintenance and servicing. All in all, the Adaptive N-hydraulics is your assurance of highly economical and reliable pumps that give you peace of mind.




N3085 MT



Discharge size: 75mm
 Height: 655mm
 Motor rating: 2.0kW
 Weight: 71kg
 Maximum width: 450mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
460 MT	2	80	2.0	1400	NP/NS/NT

N3102 MT/SH




Discharge size: 80mm/100mm
 Height: 705mm
 Motor rating: 3.1/4.2kW
 Weight: 116kg
 Maximum width: 610mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
461 MT	2	100	3.1	1440	NP/NS
255 SH	2	80	4.2	2890	NP/NS

Flygt N3127 and N3153


N3127 MT/HT



Discharge size: 100/150mm
 Height: 765mm
 Motor rating: 5.9kW
 Weight: 170kg
 Maximum width: 725mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
437 MT	2	100/150	5.9	1450	NP/NS/NT
487 HT	2	100	5.9	1450	NP/NS/NT

N3153 LT/MT




Discharge size: 150/200mm
 Height: 1068mm
 Motor rating: 13.5kW
 Weight: 252kg MT 279kg LT
 Maximum width: 834mm

Impeller rpm Code	No. of Available vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	versions
412 LT	2	200	13.5	1455	NP/NT/NS
431 MT	2	150	13.5	1455	NP/NT/NS
433 MT	2	150	13.5	1455	NP/NT/NS

Flygt N3153 and N3171


N3153 HT/SH



Discharge size: 80/100mm
Height: 1052mm
Motor rating: 13.5/15.0kW
Weight: 242kg
Maximum width: 763mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
451 HT	2	100	13.5	1455	NP/NT/NS
272 SH	2	80/100	15.0	2910	NP/NT/NS

N3171 LT MT and HT




Discharge size: 100/250mm
Height: 1299mm
Motor rating: 15/22kW
Weight: 460kg
Maximum width: 1151mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
611 LT	2	250	15.0	965	NP/NS/NT
431 MT	2	150	22.0	1460	NP/NS/NT
452 HT	2	100	22.0	1460	NP/NS/NT

Flygt N3171 and N3202


N3171 SH



Discharge size: 100mm
Height: 1179mm
Motor rating: 22kW
Weight: 366kg
Maximum width: 884mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
274 SH	2	108	22.0	2925	NP/NS/NT

N3202 LT MT and HT





Discharge size: 150/300mm
Height: 1571mm
Motor rating: 22/45kW
Weight: 900kg
Maximum width: 1439mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
617 LT	2	250	22.0	970	NP/NS/NT
433 MT	2	200	30.0	1475	NP/NS/NT
454 HT	2	150	45.0	45.0	NP/NS/NT



N3301 LT and MT 55kW




Discharge size: 250mm
 Height NS: 1705mm
 Motor rating: 55kW
 Weight: 1110kg
 Maximum width NS: 1439mm


Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
620 LT	2	250	55	985	NP/NT/NS/NZ
630 MT	2	250	55	985	NP/NT/NS/NZ
632 MT	2	250	55	985	NP/NT/NS/NZ

Flygt N3301

N3301 HT 55kW



N3301 454 HT Impeller 70kW VFD Curves



Discharge size: 150mm
 Height NS: 1641mm
 Motor rating: 55/70kW
 Weight: 920kg
 Maximum width NS: 1242mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
454 HT	2	150	70	1475	NP/NT/NS/NZ
454 HT	2	150	55	1400	NP/NT/NS/NZ
456 HT	2	150	55	1400	NP/NT/NS/NZ
458 HT	2	150	55	1400	NP/NT/NS/NZ

A Selection of impellers are available on request; also Variable Frequency Drive Starters

Flygt N Type Chopper Pumps

Introduction

Chopper pumps with N Impeller Technology

Flygt Chopper pumps have the unique patented N Impeller along with a Hard Iron chopper ring which drastically reduces the risk of clogging. Rugged, wear resistant and self cleaning, it cuts through solids without clogging or sacrificing pump efficiency.


The Flygt Chopper pump range brings to an end troublesome and costly clogging with its heavy-duty and highly dependable chopping abilities. By adding the chopper function to the well proven Flygt N-pump, outstanding performance in heavy duty applications has been achieved. This new pump design has undergone extensive testing in the field. The results from these tests show considerably fewer running problems and considerably lower energy consumption.

Typical applications:

- Agriculture
- Aquaculture
- Food processing
- Pulp and paper
- Harsh wastewater facilities.



N3127 Chopper MT




Discharge size: 100/150mm
Height NS: 765mm
Motor rating: 4.7kW
Weight: 170kg
Maximum width NS: 725mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
428 MT	2	100/150	4.7	1455	NP/NS/NT/NZ

Flygt N Type Chopper Pumps


N3153 Chopper MT and HT



Discharge size: 100/150mm
Height NS: 1068mm
Motor rating: 13.5kW
Weight: 252kg
Maximum width NS: 763mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
431 MT	2	150	13.5	1455	NP/NS/NT
451 HT	2	100	13.5	1455	NP/NS/NT

N3171 Chopper MT and HT



Discharge size: 100/150mm
Height NS: 1225mm
Motor rating: 22.0kW
Weight: 362kg
Maximum width NS: 884mm

Impeller Code	No. of vanes	Outlet dia. mm NP vers	Motor rating kW	rpm	Available versions
431 MT	2	150	22.0	1460	NP/NS/NT
451 HT	2	100	22.0	1460	NP/NS/NT

Flygt Great and Grey Solids Handling Pumps



Introduction

After revolutionising the market for small and midrange wastewater pumps, the Flygt N Pumps are now available in the larger units.

- Incorporating the N Pump technology the potential for blockage is substantially reduced
- Due to sustained efficiency, energy costs can be cut by up to 50%
- Heads of up to 90mts achieved
- Flows in excess of 700l/s

Applications

- General by-pass over-pumping
- Pump replacement
- Application proving
- Storm water handling
- Industrial effluent handling
- Irrigation

Pumps from 90 to 250kW available to rent in NP/NS/NT and NZ build (see Page 40).
Ex units available on request.



Flygt N Great and Grey Installation Methods

Flygt centrifugal pumps are designed to pump wastewater containing solids and fibres in suspension. The pump can also be used for pumping raw water.

Liquid temperature:	max 40°C (105°F)
Liquid density:	max 1100kg/m ³
The pH of the pumped liquid:	6 - 11
Depth of immersion:	max 20 m (65 ft)

For pumping in an explosive or flammable environment the pump can be ATEX certified.

The Flygt pump is fully submersible, compact and easy to install. It is available in four versions, depending of the type of installation:




NP: This system with guide bars and discharge connection permits automatic connection of the pump to the discharge line. The pump can be lifted up for inspection without anyone having to enter the sump. The pump works completely or partially submerged under water.

NS: A transportable pump designed for operating completely or partially submerged in the pump liquid. It is equipped with base stand and hose connection.

NT: The pump is installed vertically dry on a base stand and connected directly to the inlet and outlet lines. The submersible design of the pump prevents damage in the event of flooding.


NZ: The pump is installed Horizontally dry on a base stand and connected directly to the inlet and outlet lines. The submersible design of the pump prevents damage in the event of flooding.

For other applications, contact your local Flygt Rental Centre for information.






N3315 90kW 620/470mm



Rated Power: 90kW
 Weight: 1330kg
 Dimensions:
 Height - 2056mm
 Width - 1330mm
 Discharge - 300mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
620	3	300	90	985	NP/NS/NT/NZ

N3315 105kW 451/440mm




Rated Power: 105kW
 Weight: 1150kg
 Dimensions:
 Height - 1992mm
 Width - 1017mm
 Discharge - 150mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
451	3	150	105	1480	NP/NS/NT/NZ

Flygt N3231


N3231 85kW 480/360mm



Rated Power: 85kW
Weight: 1380kg
Dimensions:
Max. Height - 2060mm
Max. Width - 1570mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
480-360	3	200	85	1475	NP/NS/NT/NZ


N3231 105kW 480/400mm



Rated Power: 105kW
Weight: 1590kg
Dimensions:
Max. Height - 2060mm
Max. Width - 1570mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
480-400	3	200	105	1480	NP/NS/NT/NZ

N3231 125kW 470/370mm



Rated Power 125kW

Weight 1760kg


Dimensions:

Max. Height - 2185mm

Max. Width - 1390mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
470-370	3	200	125	1450	NP/NT/NS/NZ

N3231 170kW 470/490mm



Rated Power 170kW

Weight 1760kg

Dimensions:

Max. Height - 2305mm


Max. Width - 1570mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
470-490	3	200	170	1480	NP/NT/NS/NZ

A Selection of impellers are available on request; also Variable Frequency Drive Starters

Flygt N3231


N3231 170kW 480/490mm



Rated Power 170kW
Weight 1760kg
Dimensions:
Max. Height - 2305mm
Max. Width - 1570mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
480-490	3	200	170	1480	NP/NS/NT/NZ


N3231 215kW 480/490mm



Rated Power 215kW
Weight 1910kg
Dimensions:
Max. Height - 2305mm
Max. Width - 1570mm


Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
480-490	3	200	215	1485	NP/NS/NT/NZ

N3312 100kW 670/450mm



Rated Power: 100kW
 Weight: 1975kg
 Dimensions:
 Max. Height - 2240mm
 Max. Width - 1650mm

N3312 180kW 670/545mm




Rated Power: 180kW
 Weight: 2275kg
 Dimensions:
 Max. Height - 2975mm
 Max. Width - 1875mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
670-450	3	300	100	985	NP/NT/NS/NZ
670-545	3	300	180	990	NP/NT/NS/NZ

A Selection of impellers are available on request; also Variable Frequency Drive Starters

Flygt N3312 / N3356


N3312 250kW 670/585mm



Rated Power: 250kW
Weight: 3125kg
Dimensions:
Max. Height - 2975mm
Max. Width - 1875mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
670-585	3	300	250	990	NP/NS/NT/NZ

N3356 90kW 670/470




Rated Power: 90kW
Weight: 2200kg
Dimensions:
Max. Height - 2400mm
Max. Width - 1875mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
670-470	3	350	90	985	NP/NT/NS/NZ

Flygt N3356 / N3400


N3356 100kW 670/475mm



Rated Power: 100kW
Weight: 1750kg
Dimensions:
Max. Height - 2275mm
Max. Width - 1900mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
670-475	3	350	100	985	NP/NT/NZ

N3400 250kW 670/575mm



Rated Power: 250kW
Weight: 3750kg
Dimensions:
Max. Height - 3428mm
Max. Width - 1900mm

Impeller Code	No. of vanes	Outlet dia. mm NS vers	Motor rating kW	rpm	Available versions
670-575	3	400	250	990	NP/NT/NZ

Flygt 3000 Series Pumps Electrical Information

Pump Model	kW (Shaft Power)	Voltage	Phase	FLC Amps	DOL Starting Current AMPS	Starting Method	Minimum Generator in kVA to Start/Run
3085	1.3	400	3	3.1	19	DOL	15
3085	2.0	400	3	4.5	19	DOL	15
3085	2.4	400	3	4.7	28	DOL	20
3102	3.1	400	3	6.9	33	DOL	25
3102	4.2	400	3	8.3	72	DOL	50
3127	4.7	400	3	9.6	56	DOL	40
3127	5.9	400	3	12.0	77	DOL	55
3127	7.4	400	3	14.0	114	DOL	80
3152 - 4 Pole	13.5	400	3	27.0	162	SOFT	40
3152 - 2 Pole	15.0	400	3	28.0	229	SOFT	55
3153	7.5	400	3	16.0	91	SOFT	25
3153	9.0	400	3	19.0	107	SOFT	25
3153	11.0	400	3	24.0	132	SOFT	35
3153 - 4 Pole	13.5	400	3	28.0	150	SOFT	35
3153 - 2 Pole	15.0	400	3	27.0	213	SOFT	50
3170	15.0	400	3	31.0	210	SOFT	50
3171	22.0	400	3	41.0	248	SOFT	60
3201	30.0	400	3	56.0	365	SOFT	85
3202	37.0	400	3	66.0	460	SOFT	110
3202	45.0	400	3	82.0	605	SOFT	150
3300	44.0	400	3	82.0	515	SOFT	150
3300	54.0	400	3	100.0	535	SOFT	150
3301 - 6 Pole LT	55.0	400	3	113.0	660	SOFT	225
3301 - 4 Pole MT	55.0	400	3	103.0	435	SOFT	150
3301	70.0	400	3	132.0	565	SOFT	195
3315LT - 6 Pole	90.0	400	3	185.0	1160	VFD	195
3315 HT - 4 Pole	105.0	400	3	199.0	1105	VFD	210
3231 - 4 Pole	85.0	400	3	159.0	710	VFD	170
3231 - 4 Pole	105.0	400	3	200.0	955	VFD	210
3231 - 4 Pole	125.0	400	3	234.0	1525	VFD	245
3231 - 4 Pole	170.0	400	3	300.0	2020	VFD	315
3231 - 4 Pole	215.0	400	3	395.0	2945	VFD	415
3312 - 6 Pole	100.0	400	3	202.0	1150	VFD	210
3312 - 6 Pole	180.0	400	3	360.0	2215	VFD	375
3312 - 6 Pole	250.0	400	3	465.0	2645	VFD	485
3356 - 6 Pole	90.0	400	3	185.0	1160	VFD	195
3356 - 6 pole	100.0	400	3	202.0	1150	VFD	210
3400 - 6 Pole	250.0	400	3	465.0	2645	VFD	485

When Two pumps are driven by the same Generator, the rating required is approximately 1.5 times that indicated for a Single Pump.

Some form of time lag should be connected to prevent both pumps from starting simultaneously, unless the Generator has been selected for that number of pumps to start simultaneously.

The Information contained within this document is for guidance only and is accurate to the best of our knowledge at time of going to print.

Lowara GHV20 Booster Set

Lowara GHV series booster sets are designed to transfer and increase the pressure of water, in the following applications:

- Hospitals
- Schools
- Public buildings
- Industries
- Hotels
- Sports facilities
- Mains water systems

The GHV series booster set is a variable speed pump set with two e-SV series multistage vertical pumps. Each pump is equipped with a HYDROVAR® frequency converter. This means the pumps are capable of variable speed operation. The pumps are installed on a single skid base and connected to each other by means of suction and delivery pipes complete with manifolds and isolation and non-return valves.

Technical Information

Model: GHV20/66SV3/2AG150T - 2 pumps Skid mounted c/w with Panel and Hydrovar Unit

Supply: 400/3/50

Pump FLC: 27A, per pump

Motor: IE3 Three phase surface motor

Shaft Power: 13kW

Inlet: 150mm

Discharge: 125mm

Nominal Flow: 15l/s

Maximum Flow: 23l/s

Nominal Head: 50m

Maximum Head: 76m

Maximum Working pressure: 7.7 Bar

Panel & Pumps protected to IP55

Dimensions: 1551 L x 960 W x 1376 H

Weight: 860kg



Monitoring & Control

The same great knowledge and experience that builds the best pumps in the world lets you control and monitor your assets.

At Xylem we are continually striving to find ways to improve our customer experience, through the development of new systems and products to remotely monitor and control essential equipment, providing cost effective intelligent solutions.

As well as supplying the hardware such as pump controllers, sensors, electrical start equipment and control panels; we also have software for running the system.

The Flygt SCADA software provides PC based SCADA (Supervision, Control and Data Acquisition) know-how. The applications range from those operating in wastewater treatment plants and pump stations to products pumping ground water from building sites.

By combining these new system controls with our TotalCare provision, we can help to ensure the on-going quality and life of customers' pumps, whilst weekly electronic preventative checks increase the pumps operational effectiveness.

- Pump control panels
- Starters
- Level/pump / flow sensors
- Pump controller / supervision
- SCADA software systems
- Inverters VFD/VSD – PumpSmart/Smartrun
- WITS accredited Telemetry Outstations / RTU's / Pump Controllers
- Harmonic surveys for drive installations
- System design / integration
- Design consultancy
- Energy audits
- Optimisation of assets
- Reduction of OPEX leading to better TOTEX
- Project management inc. CDM
- Solar panel demand calculation



Electrical Equipment

We specialise in electrical submersible pumps, therefore, it is logical that we are the experts when it comes to the starter and controls that are required for a temporary pumping installation. From a simple single phase starter to a complex multi pump 3 phase control panel, Rental Engineers are available to give advice on all aspects of electromotive power.

Our Rental team carry a comprehensive range of starters, isolators, control equipment, alarm and monitoring devices. Also, sufficient cable to suit day to day usage is stocked both at Nottingham and at all Rental Depot locations. For the larger and more complex installations we are able to select and supply the appropriate extension cables and junction boxes to connect the pump to the control panel.

We can also supply ATEX Certified "Ex" junction boxes and cables glands for use in hazardous areas. If level regulators (floats) are used as the level control we can supply the required I/S protection relays.



Soft Starter Panel 2.2-15kW - Pump FLC 32A

Specification :

- IP54 Zintex Panel
- Load break door interlocked isolator
- Soft starter
- Special wide ranging overload unit (WOL) to protect different size pumps
- Pump setting via keypad
- Earth leakage protection
- 1000 event data log
- USB port for up loading and downloading parameters
- Hand/auto switch
- Door mounted Alphanumerical keypad
- Door mounted emergency stop (also to terminals)
- Klixon thermal trip circuit
- Inter-panel interlock system
- Motor & control connections wired to terminals
- 24vdc control for floats
- 24vdc , 100ma for alarm
- 24vdc , 500ma for the ultrasonic unit
- 24vac power supply customer use
- Ear stud terminal
- Main contractor (to provide isolation when WOL detects short circuit setting level)



The Heart of the Panel

- Pin locked menu
- Adjustable pump range by amps
- Adjustable too many starts protection
- Electric overload
- Underload trip
- Electronic shear pin
- Thermal switch connections

Dimensions

- Height 925mm
- Width 400mm
- Depth 400mm
- Weight 30kg

Digital Display

- Running amps
- Hand, auto, running and tripped LED
- Start and stop pushbutton
- Last eight fault history
- Motor current
- Run hours
- Motor status
- Printable 1000 event data log

Soft Starter Panel 22-90kW - Pump FLC 170A



Specification :

- IP54 Zintex panel
- Load break door interlocked isolator
- Soft starter c/w bypass contractor
- Wide ranging overload system which will protect from 22kW to 90kW
- Earth leakage protection
- Hand/auto switch
- Door mounted alphanumeric keypad
- Door mounted emergency stop (also to terminals)
- Klixon thermal trip circuit
- Inter-panel interlock system
- Lifting hooks
- Motor and control connections wired to terminals
- 24vdc control for floats
- 24vdc , 100ma for alarm
- 24vdc , 500ma for the ultrasonic unit
- 24vac power supply customer use
- Eart stud terminal
- Main contractor (to provide isolation when WOL detects short circuit setting level)



The Heart of the Panel

- Pin locked menu
- Adjustable pump range by amps
- Adjustable too many starts protection
- Electronic overload
- Under load trip
- Electronic shear pin
- Thermal switch connection

Dimensions

- Height 1570mm
- Width 1000mm
- Depth 400mm
- Weight 160kg

Digital Displays

- Running amp
- Hand, auto, running and tripped LED
- Start and stop push button
- Last eight fault history
- Motor current
- Run hours
- Motor status
- Printable 1000 event data log

VFD Starter Panel 22kW - Pump FLC 48A

The Variable speed drive multifunctional control panel for motors rated up to 22KW. The control panel is floor standing suitable for outdoor use.

Specification :

- 415V AC Transformers
- Fuse protection for control circuit
- Thermostat controller
- Anti condensation heater
- Door mounted potentiometer
- Hand/Auto selector switch
- Pot/4-20mA selector switch
- 4-2mA input terminals
- Start/stop push buttons
- Running LED indicator
- Door safety micro switch
- Pad-lockable door clasps
- IP54 Zintex steel enclosure
- Load break door interlocked 63A MCCB
- Frame, enclosure and lifting facility
- Main contactor
- Emergency stop facility (Cat0)
- Intake filter and exhaust top box
- Door mounted keypad
- 22kW VLT Aqua drive VSD
- 24vac control circuit
- 110vac control circuit
- Provision for ultra-sonic input
- Stud terminals for motor connection
- Steel document holder for drawings and manual



Dimensions

- Height 1400mm
- Width 800mm
- Depth 400mm
- Weight 120kg

VFD Starter Panel 75kW - Pump FLC 145A

The Variable speed drive multifunctional control panel for motors rated up to 75KW. The control panel is floor standing suitable for outdoor use.

Specification :

- 415V AC Transformers
- Fuse protection for control circuit
- Thermostat controller
- Anti condensation heater
- Hand/Auto selector switch
- 4-20mA selector
- 4-2mA input terminals
- Start/stop push button
- Running LED indicator
- Door safety micro switch
- Pad-lockable door clasps
- IP54 Zintex steel enclosure
- Load break door interlocked
- 250A S/FUSE
- Frame, enclosure and lifting facility
- Emergency stop facility (Cat0)
- Door mounted keypad
- 110vac control circuit
- Provision for ultra-sonic input
- Stud terminals for motor connection
- I/S barrier for float switches

Dimensions

- Height 1830mm
- Width 700mm
- Depth 600mm
- Weight 205kg



VFD Starter Panel 90kW - Pump FLC 169A

The Variable speed drive multifunctional control panel for motors rated up to 90KW. The control panel is floor standing suitable for outdoor use.

Specification :

- 415V AC Transformers
- Fuse protection for control circuit
- Thermostat controller
- Anti condensation heater
- Hand/Auto selector switch
- 4-20mA selector
- 4-2mA input terminals
- Start/stop push button
- Running LED indicator
- Door safety micro switch
- Pad-lockable door clasps
- IP54 Zintex steel enclosure
- Load break door interlocked
- 250A S/FUSE
- Frame, enclosure and lifting facility
- Emergency stop facility (Cat0)
- Door mounted keypad
- 110vac control circuit
- Provision for ultra-sonic input
- Stud terminals for motor connection
- I/S barrier for float switches



Dimensions

- Height 1830mm
- Width 700mm
- Depth 600mm
- Weight 230kg

VFD Starter Panel 30kW-160kW-Pump FLC280A

The Variable speed drive multifunctional control panel for motors rated from 30kW and up to and including 160kW. The control panel is floor standing suitable for outdoor use.

Specification :

- Weather proof enclosure to IP65 rating and complete with mounting stand and lifting eye bolts
- Incoming mains isolator
- Line contactor
- ABB 160kW, 415V, 3 phase, 50Hz ACS800 type variable speed drive
- Multifunction control
- Motor thermal switch relay
- Mains and motor terminals
- Telemetry control terminals
- Remote control terminals
- Door mounted indication lamps
- Door mounted VSD keypad
- Door mounted start, stop, reset and E Stop pushbuttons
- E stop to category 0
- Hand / off / auto selector switch



Dimensions

- Height 1800mm
- Width 800mm
- Depth 600mm
- Weight 400kg

Godwin

Godwin Pumps one of our own market leading brands, has over 100 years of experience in the design, manufacture, and supply of diesel pumps. Godwin Pumps is renowned for quality, reliability, and long life.

Today, the product range is used throughout the world, in construction, industry, oil refineries, chemical plants, mines, specialist offshore pumping, irrigation and water distribution.

Our Rental division offers Godwin's range of automatic self-priming pumps with an additional and wider range of Diesel driven Dri - Prime® pumps. The new Godwin pumps can be skid or trailer mounted for use in mobile applications which can provide exceptional energy efficiency and a significantly reduced clogging capability.

Godwin CD series

The Godwin CD range is ideal for high volume, medium head pumping and is capable of handling large solids.

Godwin HL series

The Godwin HL range is ideal for medium volume, high head pumping and is also capable of handling large solids-handling.


Godwin CD, HL, Heidra and NC series pumps are now available to rent from Xylem.

All models are available trailer mounted for safe on site transportation or with a skid base. Cast Iron pump end construction, and sound attenuated enclosures.



CD80D Dri-Prime® Hush-Pac

The CD80M can handle solids up to 40mm in diameter. Allows for dry running for prolonged periods while automatically priming and repriming. This makes it an extremely effective pump, suitable for both slurry, clean water applications as well as small dewatering and bypass applications.



Overall dimensions

Length 1621mm
Width 853mm
Height 1333mm

Engine Option

 Kubota Z482


CD80M Kubota Z482

Suction connection	80mm	Wet Weight	725kgs
Delivery connection	80mm	Impeller diameter	166mm
Max capacity	65m³/hr	Max working pressure	4.0bar
Max Head	15M	Max operating speed	2000rpm
Max Solids	40mm	Engine	Kubota Z482
Max Suction Lift	8.5M	DbA rating (at 3m)	65

Godwin CD series

CD100M Dri-Prime® Hush-Pac

Able to perform in the toughest conditions, the CD100M can handle solids up to 45mm in diameter. Allows for dry running for prolonged periods while automatically priming and repriming. This makes it an extremely effective pump, suitable for both slurry, clean water, sewer bypass and general dewatering and many other applications.



Overall dimensions

Length
1940mm
Width
1050mm
Height
1500mm

Engine Option


 Perkins 403D-15

CD100M Perkins 403D-15

Suction connection	100mm	Wet Weight	1168kgs
Delivery connection	100mm	Impeller diameter	220mm
Max capacity	200m³/hr	Max working pressure	3.8bar
Max Head	29M	Max operating speed	2000rpm
Max Solids	45mm	Engine	Perkins 403D-15
Max Suction Lift	8.5M	Dba rating (at 3m)	70

CD150M Dri-Prime® Hush-Pac

Able to perform in the toughest conditions, the CD150M can handle solids up to 75mm in diameter. Allows for dry running for prolonged periods while automatically priming and repriming. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful CD150M has proven itself a pump of choice for contractors, local authorities, industrial and environmental companies.



Overall dimensions

Length
2190mm
Width
1050mm
Height
1500mm

Engine Options

- Perkins 404D-22
- Perkins 1104D-44TA


CD150M Perkins 404D-22

Suction connection	150mm	Wet Weight	1403kgs
Delivery connection	150mm	Impeller diameter	260mm
Max capacity	329m³/hr	Max working pressure	4.8bar
Max Head	19M	Max operating speed	1500rpm
Max Solids	75mm	Engine	Perkins 404D-22
Max Suction Lift	8.5M	DbA rating (at 3m)	70

Godwin CD series

CD225M Dri-Prime® Hush-Pac

The Godwin Dri-Prime CD225M pump is an extremely powerful yet compact pump with flow capabilities to 735 m³/hr and discharge heads to 49 metres. The CD225M features the unique Godwin liquid bath mechanical seal design. This allows for dry running for prolonged periods while automatically priming and repriming. Able to perform in the toughest conditions, the CD225M can handle solids up to 75 mm in diameter. This makes it an extremely effective pump, suitable for both slurry and cleanwater applications.



Overall dimensions

Length
3110mm
Width
1300mm
Height
2200mm

Engine Option


- JCB 444 TA4i-81
- JCB 444 TA4i-93

CD225M JCB 444 TA4i-93

Suction connection	200mm	Wet Weight	2660kgs
Delivery connection	200mm	Impeller diameter	290mm
Max capacity	735m ³ /hr	Max working pressure	5.0bar
Max Head	49M	Max operating speed	2200rpm
Max Solids	75mm	Engine	JCB 444 TA4-93
Max Suction Lift	8.5M	DbA rating (at 3m)	TBC

CD300M Dri-Prime® Hush-Pac

The CD300M can handle solids up to 95mm in diameter. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful CD300M has proven itself a pump of choice for mines, quarries and many other high capacity applications.



Overall dimensions

Length
4850mm
Width
2065mm
Height
2545mm

Engine Options

- Perkins 1106D-E66TA
- Caterpillar C9


CD300M Caterpillar C9

Suction connection	300mm	Wet Weight	6620kgs
Delivery connection	300mm	Impeller diameter	362mm
Max capacity	1380m³/hr	Max working pressure	6.0bar
Max Head	54M	Max operating speed	1800rpm
Max Solids	95mm	Engine	Caterpillar C9
Max Suction Lift	8.5M	DbA rating (at 3m)	80

Godwin CD series

CD400 Dri-Prime® Open Set

The CD400 can handle solids up to 125mm in diameter. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful CD400 has proven itself a pump of choice for Mines, Quarries, and environmental companies.



Overall dimensions

- Length 5000mm
- Width 2205mm
- Height 2405mm

Engine Options


- Perkins 1106D-E66TA
- Caterpillar C9

CD400 Caterpillar C9

Suction connection	450mm	Wet Weight	7750kgs
Delivery connection	400mm	Impeller diameter	500mm
Max capacity	2218m³/hr	Max working pressure	4.4bar
Max Head	42M	Max operating speed	1200rpm
Max Solids	125mm	Engine	Caterpillar C9
Max Suction Lift	8.5M		

CD500 Dri-Prime® Open Set

The CD500M features the unique Godwin high pressure oil bath mechanical seal design. This allows for dry running for prolonged periods while automatically priming and repriming. Able to perform in the toughest conditions, the CD500M can handle solids up to 80 mm in diameter. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful CD500M has proven itself a pump of choice for mines, quarries and many other high capacity applications.



Overall dimensions

Length
5400mm
Width
2670mm
Height
2500mm

Engine Options

- Caterpillar C15
- Caterpillar C18


CD500 Caterpillar C18

Suction connection	500mm	Wet Weight	11750kgs
Delivery connection	450mm	Impeller diameter	610mm
Max capacity	3357m³/hr	Max working pressure	6.0bar
Max Head	50M	Max operating speed	1100rpm
Max Solids	80mm	Engine	Caterpillar C18
Max Suction Lift	8.5M		

Godwin HL series

HL160M Dri-Prime® Open Set

The HL160M can handle solids up to 35mm in diameter. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful HL160M has proven itself a pump of choice for mines, quarries and many other high capacity applications.



Overall dimensions

Length
4000mm
Width
1950mm
Height
2350mm

Engine Options

-  Volvo TAD951VE
-  Caterpillar C15


HL160M Caterpillar C15

Suction connection	200mm	Wet Weight	6442kgs
Delivery connection	150mm	Impeller diameter	508mm
Max capacity	486m³/hr	Max working pressure	18.5bar
Max Head	187M	Max operating speed	2000rpm
Max Solids	35mm	Engine	Caterpillar C15
Max Suction Lift	8.5M		



HL250M Dri-Prime® Open Set

The HL250M features the unique Godwin high pressure oil bath mechanical seal design. This allows for dry running for prolonged periods while automatically priming and repriming. Able to perform in the toughest conditions, the HL250M can handle solids up to 65mm in diameter. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful HL250M has proven itself a pump of choice for mines, quarries and many other high capacity applications.



Overall dimensions

Length
4000mm

Width
1950mm

Height
2350mm

Engine Options

 Volvo TAD951VE

 Caterpillar C15


HL250M Caterpillar C15

Suction connection	300mm	Wet Weight	9072kgs
Delivery connection	250mm	Impeller diameter	440mm
Max capacity	1224m³/hr	Max working pressure	12.1bar
Max Head	117M	Max operating speed	2000rpm
Max Solids	65mm	Engine	Caterpillar C15
Max Suction Lift	8.5M		

Godwin HL series

HL260M Dri-Prime® Open Set

The HL260M features the unique Godwin high pressure Glycol mechanical seal design. This allows for dry running for prolonged periods while automatically priming and repriming. Able to perform in the toughest conditions, the HL260M can handle solids up to 50mm in diameter. This makes it an extremely effective pump, suitable for both slurry and clean water applications. The powerful HL260M has proven itself a pump of choice for mines, quarries and many other high capacity applications.



Overall dimensions

Length
4300mm
Width
1980mm
Height
2525mm

Engine Options

- Volvo TAD1215VE
- Caterpillar C18

HL260M Caterpillar C18

Suction connection	250mm	Wet Weight	7000kgs
Delivery connection	200mm	Impeller diameter	540mm
Max capacity	1260m³/hr	Max working pressure	16bar
Max Head	147M	Max operating speed	1800rpm
Max Solids	50mm	Engine	Caterpillar C18
Max Suction Lift	8.5M		



Godwin NC series

With two of the world's market leading pump brands, Flygt and Godwin, now under the Xylem umbrella, we have combined the world's most reliable portable pumps with the world's most efficient self-cleaning hydraulics to bring you the most efficient and reliable Godwin pumps ever.

The new range of Godwin NC pumps are not only reliable, they come equipped with the non-clogging, performance of the proven Flygt N-technology.



This breakthrough combination gives you a best-in-class portable pump that delivers sustained hydraulic efficiency to handle tough wastewater pumping applications.

Self-cleaning Flygt N-technology saves costs

The high efficiency of Flygt N-technology is sustained over time due to its self-cleaning ability, keeping energy/fuel costs to a minimum.

Without a doubt, no matter what the challenge, you will always have the peace of mind knowing that our Godwin NC Series Dri-Prime® pumps are on the job.


Godwin pumps, now with sustained high efficiency N hydraulics

- Self-cleaning reliability
- Hydraulic efficiency
- Non-stop optimum performance
- Long term energy/fuel savings
- Optimized operating speed for low energy/fuel consumption
- Low downtime
- Extended service intervals
- Minimum maintenance
- Service friendly

Godwin NC series

NC100 Dri-Prime® Hush-Pac

Features the unique patented N-technology with its innovative self-cleaning impeller. Able to perform in the toughest conditions, the NC100 can handle solids up to 35mm in diameter. This makes it an extremely effective pump, suitable for both sewage and clean water applications. The powerful NC100 has proven itself a pump of choice when pumping stringy material and general dewatering applications.



Overall dimensions

Length
2190mm
Width
1050mm
Height
1500mm

Engine Options


- Perkins 403D-15
- Perkins 404D-22

NC100 Perkins 403D-15

Suction connection	100mm	Impeller diameter	256mm
Delivery connection	100mm	Max working pressure	5.0bar
Max capacity	188 m³/hr	Max operating speed	1800rpm
Max Head	27M	Engine	Perkins 403D-15
Max Suction Lift	8.5M	DbA rating (at 3m)	69
Wet Weight	1345kgs		

NC150 Dri-Prime® Hush-Pac

Features the unique patented N-technology with its innovative self-cleaning impeller. Able to perform in the toughest conditions, the NC150 can handle solids up to 42mm in diameter. This makes it an extremely effective pump, suitable for both sewage and clean water applications. The powerful NC150 has proven itself a pump of choice when pumping stringy material and general dewatering applications.



Overall dimensions

Length
2190mm
Width
1050mm
Height
1500mm

Engine Options

- Perkins 404D-22
- Perkins 1104D-44T

NC150 Perkins 404D-22


Suction connection	150mm	Impeller diameter	265mm
Delivery connection	150mm	Max working pressure	6.0bar
Max capacity	241m³/hr	Max operating speed	1600rpm
Max Head	26M	Engine	Perkins 404D-22
Max Suction Lift	8.5M	DbA rating (at 3m)	68
Wet Weight	1410kgs		

Godwin Dri-Prime® Pump

NC150S Dri-Prime® Pump

The Godwin NC150S Dri-Prime pump is designed for use in municipal wastewater applications that contain stringy, modern waste. This unique self-cleaning, non-clog pump is recommended for sewer, lift station, and bypass applications, and is ideal for permanent installations where reliability is absolutely critical, e.g. Diesel Backup Systems (DBS).

This is the first in a series of Godwin S Series 'Smart' pumps, with significantly improved pumping efficiency, greater fuel economy, easier operation, and reduced maintenance.



Overall dimensions

- Length 2460mm
- Width 1045mm
- Height 1743mm

Engine Options

- Perkins 404D-22T FC

NC150S Perkins 404D-22T FC

Suction connection	150mm	Impeller diameter	286mm
Delivery connection	150mm	Max working pressure	6.0bar
Max capacity	370 m³/hr	Max operating speed	2200rpm
Max Head	50M	Engine	Perkins 404D-22T FC
Max Suction Lift	8.5M	DbA rating (at 7m)	63
Wet Weight	1570kgs		

Water Treatment

Our new Treatment Rental division has a vast range of treatment products available for short term or semi-permanent treatment requirements in the event of compliance failure, short term outages or planned maintenance work. Xylem has the technology available to ensure you maintain consent whatever your needs.

Our range incorporates a number of the premium Xylem brands with market leading technology in both Water & Wastewater Treatment combined with our nationwide service centres and 24/7 call out make Xylem truly a one-stop shop for both transport & treatment of both water & wastewater.



Wedeco Spektron - Clean Water

The Wedeco Spektron shines new light on the environmentally friendly process of using UV disinfection for drinking water. Featuring highly efficient UV lamp technology and advanced flow distribution, the Spektron series suits modern drinking water treatment plants and covers a wide array of applications from domestic water supply and industrial uses to large municipal water plants with a capacity of more than one thousand m³/h per unit.

Xylem now has Wedeco Spektron UV reactors available to rent together with their own control panel for ease of use and inspection. The Spektron range can be used in a number of applications where water treatment is needed.



Description	kW	Voltage	Max flow rate m ³ /h
Clean Water Applications			
UV Spektron 250e-EW Skid 4 x 290w ECORAY® VLR30 UV lamps Dimensions: 2500 L x 700 W x 1750 H Weight: 330Kg	1.5	230/1/50	377
UV Spektron 650e-EW Skid 8 x 290w ECORAY® VLR30 UV lamps Dimensions: 2900 L x 900 W x 1880 H Weight: 620Kg	3	400/3/50	846
UV Spektron 900e Skid 12 x 290w ECORAY® VLR30 UV lamps Dimensions: 2900 L x 900 W x 1880 H Weight: 620Kg	4	400/3/50	1,037

Wedeco Containerised LBX 850e UV Treatment



LBX 850e Containerised UV Rig - Wastewater

The LBX reactor is a compact wastewater UV Disinfection system suitable for low UV transmissivity applications. The reactor includes high efficiency low pressure Ecoray UV lamps and includes its own dedicated smart dose controller including SCADA connection. Housed in a dedicated enclosure for ease of installation and transport the unit is a self-contained UV disinfection solution for wastewater applications.



- Container Size – Standard 20 Foot ISO shipping container – 6.05m L, 2.44m W, 2.59m H
- Container Weight – 3,800Kg - Dry
- Inlet Connection – DN400 PN16
- Outlet Connection – DN400 PN16
- Electrical Supply – TP&N – 40A (400/3/50)
- Lamps – 32 x 285W Ecoray Lamps
- Total load in kW drawn by panel & lamps – 13kW
- Max flow rate 1,356 m³/h



Flygt Mixers

Flygt Submersible Mixers consist of a drive unit and propeller, integrated into a compact unit. The mixer is mounted on a guide bar, to enable it to be raised and lowered, to operate at different depths. It can also be angled upwards or downward and can be swivelled to the sides. Its mixing action can therefore be directed to any point in a lagoon or tank.

This flexibility aided by the large blade propeller, running at relatively low speeds, sets in motion large volumes of sludge and water. The Flygt submersible mixer is at least three times as efficient as a conventional mixer. This is due to the high efficiency hydraulic design and the fact that the motor and propeller are integrated into a lightweight, compact unit. No energy is lost in complicated gearing, support bearings and heavy shafts. Also, the mixer can be run intermittently, thus providing further energy savings.

Compact design

The machines are either direct-driven or include a reduction gearbox between the motor and the propeller. However, all models are well integrated into a compact unit. So no energy is lost in long heavy shafts and support bearings.

Circular tanks

One mixer is normally sufficient for tank volumes up to 2,000m³. Depending on the characteristics of the liquid and the desired degree of agitation, more than one mixer may be necessary for larger tank volumes.

Rectangular tanks

If the length, width and depth dimensions of the tank differ considerably, several mixers may be necessary to ensure good results. Rectangular tanks are often located underground. Since Flygt Mixers are installed from the top, installation in underground tanks is easy.

For specific duties on the range of Flygt Submersible Mixers please contact your local service centre.



Homogeneous liquid manure in a couple of hours.

Flygt Submersible Mixers have an important role to play in agriculture, for homogenising liquid manure. Even if the manure is old, with a thick dry crust and all the solids have settled at the bottom of the tank, it will be possible by mixing for the whole tank contents to become homogeneous. This is due to the fact that the mixer can operate at different depths, can be orientated in any direction and will quickly set in motion large volumes of the manure.

Wide field of applications in industry

Flygt Submersible Mixers are used for keeping liquids of different viscosities in suspension, for mixing dry solids into liquids, for thickening after sedimenting and decanting, and for transporting liquids,

Good environment in fish farming

Whether in netting enclosures in open water or in dammed bays, Flygt submersible mixers will maintain ideal fish farming conditions at a modest cost. The mixer will supply a briskly-flowing current of fresh water with good oxygen contents and an abundance of natural food. At the same time, fish droppings will be removed. The risk of rotting and formation of decay gases is eliminated. By establishing circulation between the bottom and the surface, the mixer also evens out the water temperature, which favours the growth of the fish.

Improving the efficiency in sewage treatment plants

Flygt Submersible Mixers have been widely adopted in sewage treatment plants throughout the world. Particularly in thickening, sludge and storm water ponds, in buffer tanks and in the mixing of chemicals and lime into the water, the efficiency and low operating costs of the mixers can be utilised to the greatest possible extent.

Flow creation

For low head, high capacity laminar flows the large propeller mixer can be used in lake reservoirs, fish farms as well as process mixing.

Flygt Mixers





As shown:

4620 1.5kW mixer fitted on a portable, free standing steelwork - available to rent.



Available Flygt Mixers

Type	A Max Ø mm	B Max Ø mm	C mm	D mm	E mm	F mm	G mm	H mm	I mm	Weights (max) kg (lbs)
4410	2500	-	-	-	-	-	1110	1010	100	230(507)
4430	2500	-	-	-	-	-	1110	1010	100	263 (580)
4630	390	636	405	559	469	117	574	457	50	61(134)
4640	390	636	405	559	509	117	614	497	50	64 (141)
4650	650	1027	675	931	721	195	878	700	100	177 (390)
4660	650	1027	675	931	831	195	988	810	100	218 (481)
4670	880	1372	908	1256	835	264	992	816	100	363 (800)
4680	880	1372	908	1256	985	264	1192	966	100/150	482 (1063)



Aeration - Flygt Radial Aerators

Fields of application

The efficient mixing characteristics and the simple design of our Ejectors and Aerators make them suitable for aerating biological ponds, fishfarm ponds, lakes and waterways.

The function of the ejectors

The principle on which the Ejector operates is simple and well-known. A drive jet from a Flygt Submersible pump is led into the Ejector. The drive jet flows through a nozzle into the ejector housing, which has a delivery pipe for the medium, e.g. air, which is to be pumped (the secondary flow). A drop in pressure occurs when the drive jet passes through the mixing tube. This partial vacuum automatically entrains the pump medium with the drive jet and the contents of the primary and secondary flows are mixed intensively with each other.

The function of the Radial Aerator

Aeration by means of high efficiency mixing.

Air dispersion by the same method as the Ejector is distributed radially within a tank, basin or lagoon, via the series of diffusers mounted around a central turbine impeller. As with the Ejectors, being totally submerged significant advantages arise over other forms of aeration.

Low noise levels.

No sprays or liquid dispersion in the atmosphere.

Installation

Installation of these aeration products is straightforward either by bolting to the tank floor or they even will be suspended by their own weight in certain circumstances.


Applications

Subject to the tank configuration the ejector or aerator can be selected to:

- Replace existing aeration equipment during breakdown or maintenance periods.
- Upgrade existing treatment capacity without major investment. Increase oxygen levels. Reduce ammonia levels.




Dimensions and Weight - Flygt Radial Aerators



Type	Power	Current	Dimensions (mm)			Weight kg*
			a	b	c	
308	2.4	4.5	610	660	50	75
310	4.4	8.5	700	660	50	105
312	5.9	11.0	800	950	80	180
315	13.5	25.0	1130	995	100	295
320	22	42.0	1320	1150	150	500

* Weight includes 10m of cable

Flygt Radial Aerators - Oxygen Transfer Rate





Utilising the principles of an Ejector; the Flyjet can be used to resuspend solids which have settled in storage tanks.

They can be used in storm water retention tanks at sewage works; for example. 4" and 6" jet pipes are available.



Pump Flotation Modules

The concept

Our range of pump flotation modules has been developed to provide a light-weight and cost-effective alternative to the traditional steel pontoon. The flotation modules are prefabricated from light-weight, foam-filled, GRP (Glass fibre Reinforced Polymer) and are available in four sizes.

General applications

Pump Flotation Modules can be supplied to suit Flygt 2000 Series / BS dewatering pumps, C/N-series wastewater pumps and slurry pumps.

• Applications include:

- Mine dewatering
- Tailing dams
- Underground dams
- Sewage treatment
- Quarries
- Aeration ponds
- Construction site dewatering
- Flooding control


Installation

The pump and integral module can be simply installed by use of a central lifting attachment. Once in the water, the module can be towed by boat, if required, and secured in position by anchor or guy ropes. The float module remains visible above the water surface for easy recovery.

Design features:

- Compact and lightweight
- Stainless steel metal parts
- Easily mounted to pumps on site
- Lifting points for easy installation
- Easy to transport as an integral unit
- Foam filled to prevent sinking

By having the pump floating close to the surface, it increases service life through reduced maintenance since it is no longer working within high solids environment.



PFM550

PFM550

PFM 550	Part Number
2201	691 69 00
3140	*
3152/3153	*
3170/3171	*
5100 (<52kW)	*
5150 (<52kW)	*



* On request

1400 x 1400 x 540mm 20kg

Hoses and Fittings

To complement our comprehensive range of pumps, extensive stocks of pipework and hoses are held. Our Rental engineers can supply all your needs from 50mm hose increasing in size to steel pipes in excess of 450mm.

Also BSP pipe and cast iron fittings to suit most applications including valve, taper, hose spigot, flexible couplings and hose clamps, specialised hoses for high pressure applications are also stocked.



Hoses and Fittings

A pump relies on a secure link between the source and the discharge point. Poor hoses will leak, collapse and cause unwanted problems. So, at Xylem we only sell those hoses we use ourselves – “Cheap hose is expensive hose in the long run”.



Wire-armoured
Suction Hose

Specification			
Bore dia. mm	Outside dia. mm	Working Pressure bars	Weight per 6m incl. cpgs kg
51	63	8	12
76	89	8	26
102	116	8	35
150	169	5	60

A tough hose developed for the construction industry, with a tube of smooth synthetic rubber, covered with weather resistant synthetic rubber, reinforced with cords of synthetic textile and an embedded helix of high-tensile steel wire. It is flexible and heavy, yet easy enough to manoeuvre. It seals well onto the pipe fittings, withstands high pressure and is also tough. It is ideal for suctions and for discharge where the bend must not collapse.



PVC Suction and
Discharge Hose

Specification			
Bore dia. mm in.	Outside dia. mm	Working Pressure bars	Weight per 6m incl. cpgs kg
50 2	58	5	6
75 3	87	5.5	10
100 4	115	4.5	25
150 6	167	3	40

PVC is a high grade hose, flexible, lightweight, with exceptional resistance to abrasion and weathering. The smooth bore offers minimum resistance to flow. The strengthened PVC helix is embedded in the hose wall for extra strength.



Polythene Delivery Hose

Specification			
Bore dia. mm in.	Outside dia. mm in.	Working Pressure bars psi	Weight per 6m incl. cpgs kg
50 2	65 2.5	6 90	8
75 3	90 3.5	4 60	14
100 4	115 4.5	3 50	18
150 6	170 6.75	3 50	43

This is a proven semi-rigid delivery hose, which is well known throughout the industry. It is damage resistant, but also lightweight and simple to handle. Friction loss is kept to a minimum in this smooth bore hose.

Friction Loss in Pipe Fittings Chart



Friction Loss In Smooth Bore Pipe

Losses in m/100 or ft./100ft

I.G.P.M.	2"	3"	4"	6"	8"	10"	12"	m ³ /h
50	10	1.4	0.3					10
75	20	3	0.7					15
100	35	5	1	0.1				20
150		12	2.5	0.35				30
200		18	4.5	0.6				50
300		40	10	1.2	0.4			75
400			18	2.2	0.7			100
500			28	3.5	1.1	0.35		125
600			38	4.5	1.5	0.5		150
700				6.5	2	0.7		175
800				8	2.7	0.8		200
900				10	3.4	1	0.4	225
1000				13	4	1.4	0.5	250
1200				18	6	2	0.8	300
1400				26	8	3	1	350
1600				32	11	4	1.5	400
1800				36	14	4.5	2	450
2000				38	17	5	2.5	500
2500					25	9	4	650
3000					38	12	5	750
4000						21	8	1000
5000						32	13	1250

m³/h x 4 = g.p.m. approx

The table refers to new pipes and moderate corrosion could increase resistance by 30%. To calculate resistance of Bends and Fittings, an 'equivalent length' for each accessory needs to be added to the actual length of pipe. The equivalent length in feet can be estimated by multiplying the factors in the adjacent table by the pipe diameter in inches.

Example :- A 6" Gate Valve is equivalent to 12 ft of extra pipe

Mitre elbow or tee	5
Round elbow	3
Slowbend	2
Square edged entrance	3
Gate valve fully open	2
Globe valve fully open	10
Non-return valve (flap type)	3
Foot-valve and strainer (clean)	5

Weight Reference Guide - Pumps and Starters

Pump Type	BS/NS Weight Inc. Base Stand	Pump Type	Weight
2052	18kgs	Large Submersible Pump Range	
2066	30kgs	3231 85Kw	1,380kgs-Pump Only
2102	50kgs	3231 105Kw	1,590kgs-Pump Only
2125 Aluminium	89kgs	3231 125Kw	1,530kgs-Pump Only
2125 Cast Iron	180kgs	3231 170Kw	1,760kgs-Pump Only
2151	165kgs	3231 215Kw	1,910kgs-Pump Only
2201MT Aluminium	280kgs	3312 100Kw	1,975kgs-Pump Only
2201MT Cast Iron	445kgs	3312 180Kw	2,275kgs-Pump Only
2201HT Aluminium	240kgs	3312 250Kw	3,125kgs-Pump Only
2201HT Cast Iron	350kgs	3356 100Kw	1,750kgs-Pump Only
2250	540kgs	3400 75Kw	2,700kgs-Pump Only
2400	985kgs	3400 250Kw	3,750kgs-Pump Only
2610 MT	21kgs	Godwin Diesel Range - Open Set or HushPac	
2620 MT	32kgs	CD80D-Kubota Z482 Engine-Wet Weight HushPac	725kgs
2640 MT & HT	51kgs	CD100M-Perkins 403D-15 Engine-Wet Weight HushPac	1'168kgs
2660 MT & HT	78kgs	CD150M-Perkins 404D-22 Engine-Wet Weight HushPac	1'403kgs
2670 MT & HT	141kgs	CD225M-JCB 444Ti Engine-Wet Weight HushPac	2'660kgs
3085MT	71kgs	CD300M-Caterpillar C9 Engine-Wet Weight HushPac	6'620kgs
3102MT	116kgs	CD400M-Caterpillar C9 Engine-Wet Weight Open Set	7'750kgs
3102SH	114kgs	CD500M-Caterpillar C18 Engine-Wet Weight Open Set	11'750kgs
3127MT	170kgs	HL160M-Wet Weight Open Set	6'442kgs
3127HT	155kgs	HL250M-Wet Weight Open Set	9'072Kgs
3152LT	426kgs	HL260M-Wet Weight Open Set	7'000Kgs
3152MT	321kgs	NC100-Perkins 403D-15 Engine-Wet Weight HushPac	1'345kgs
3152HT	280kgs	NC150-Perkins 404D-22 Engine-Wet Weight HushPac	1'410kgs
3153 LT	379kgs	NC150S-Perkins 404D-22T Engine-Wet Weight HushPac	1'570kgs
3153MT	252kgs	Heidra 150 Deutz FM2011 Power Pack-Wet Weight HushPac	1'500kgs
3153HT	232kgs	HNC100 Pump Only	135kgs
3153SH	242kgs	HNC150 Pump Only	155kgs
Concertor 5.5kW 150mm	130kgs	Mixers	
Concertor 7.3kW 100mm	112kgs	4620	18kgs
3171LT	460kgs	4630	60kgs
3171MT	362kgs	4640	63kgs
3171HT	321kgs	4650	174kgs
3201MT	588kgs	4660	209kgs
3201HT	540kgs	4670	345kgs
3202LT	900kgs	Starters	
3202MT	610kgs	15kW Soft Start	30kgs
3202HT	580kgs	90kW Soft Start	160kgs
3300LT	1,175kgs	22kW VFD	120kgs
3300MT	1,188kgs	75kW VFD	205kgs
3300HT	988kgs	90kW VFD	230kgs
3301LT	1,110kgs	160kW VFD	400kgs
3301MT	1,030kgs	Treatment Plant	
3301HT	920kgs	LBX850 UV Plant-20' Container-Dry Wight	3,800kgs Approx.
3315LT 90kW	1,330kgs	Spektron 250e UV-Skid-Dry Weight	330kgs Approx.
3315HT 105kW	1,220kgs	Spektron 650e UV-Skid-Dry Weight	620kgs Approx.
		Spektron 900e UV-Skid-Dry Weight	620kgs Approx.
		SAF Plant 20' Container-Dry Weight	9,500kgs Approx.

The weights above
DO NOT include Cable,
 Chains or Hoses

The weights contained within this guide are an estimate only and the actual weight of the item to be lifted must be separately assessed and verified

The Information contained within this document is for guidance only and is accurate to the best of our knowledge at time of going to print.

Weight Reference Guide - Accessories


Cast Iron Pipe & Fittings	Size (M)	2" - 50mm kg	3" - 80mm kg	4" - 100mm kg	6" - 150mm kg	8" - 200mm kg	10" - 250mm kg	12" - 300mm kg
Gate Valve Metal Wedge		17	23	35	65	104	170	228
NRV Cast Iron Flap Type		12	16	21	37	69	132	187
D/F Bend Short			11	13	22	34	55	77
D/F Bend Long			16	21	34	52	74	101
Duck Foot Bend			15	19	33	50	82	116
Equal Tee			17	21	36	54	87	115
Radial Tee			26	34	55	83	121	164
"Y" Piece			17	20	36	54	89	127
Taper			8	10	15	22	33	46
VJFA			4	5	7	11	15	20
Cast Iron Pipe Cement lined kg/M.No Flanges			16	20	30	40	52	66
NP 16 Flange			5	6	8	10	15	19
Hoses								
Wire Armoured Hose C/W Bauers	6	12	26	35				
PVC Suction & Discharge Hose C/W Bauers	6	6	10	25				
Polythene Semi Rigid Hose C/W Bauers	6	8	14	18	43			
Wire Armoured Hose C/W Bauers	3				35	50	95	
Wire Armoured Hose C/W Flanges	3				65	95	125	
Steel "Bauer" Type Pipe & Fittings								
		2" - 50mm	3" - 76mm	4 1/4" - 108mm	6 1/4" - 159mm	7 7/8" - 194mm		
Galvanised pipe	1	3	5	8	15	20		
Galvanised pipe	2	3	7	12	20	30		
Galvanised pipe	3	7	11	16	32	40		
Bauer Ball Connector		0.2	0.3	1	1.5	2		
Bauer Level Closure Ring		0.5	1	1.5	4	6		
Bauer Socket		0.1	0.3	0.6	1.2	2.5		
Bauer 90 Deg C/W Closure Ring	1	2.5	5.5	11	13			
Bauer Equal Tee C/W 2 Closure Rings		1.5	4	8	15			
Bauer Flanged with ball & Closure Ring	3	5	8	14		22		
Bauer Flanged with Socket		3	4	5	7	15		

The weights contained within this guide are an estimate only and the actual weight of the item to be lifted must be separately assessed and verified


Conversion Factors

Inches	x	25.4	=	mm	x	0.0394	=	Inches
Feet	x	0.3048	=	m	x	3.281	=	Feet
Yards	x	0.9144	=	m	x	1.0936	=	Yards
Miles	x	1.609	=	km	x	0.6214	=	Miles
Ft ²	x	0.0929	=	m ²	x	10.764	=	Ft ²
Miles ²	x	2.59	=	km ²	x	0.3861	=	Miles ²
In ³	x	16387	=	mm ³	x	0.000061	=	In ³
Ft ³	x	0.02832	=	m ³	x	35.31	=	Ft ³
Gals (Imp)	x	4.546	=	L	x	0.22	=	Gals (Imp)
Gals (Imp)	x	0.004546	=	m ³	x	220	=	Gals (Imp)
Gals (US)	x	3.785	=	L	x	0.2642	=	Gals (US)
LBS	x	0.4536	=	kg	x	2.2046	=	LBS
Tons	x	1016	=	kg	x	0.000984	=	Tons
Gal/Min (Imp)	x	0.2727	=	m ³ /h	x	3.6667	=	Gal/Min (Imp)
Gal/Min (Imp)	x	0.0757	=	L/Sec	x	13.21	=	Gal/Min (Imp)
L/Sec	x	3.6	=	m ³ /h	x	0.277	=	L/Sec
Gal/Min (Imp)	x	1.2	=	USGPM	x	0.833	=	Gal/Min (Imp)
PSI	x	0.06895	=	Bar	x	14.504	=	PSI
PSI	x	0.703 S.G	=	M Liquid	x	1.422xS.G	=	PSI
Ft Liquid	x	0.02989xS.G	=	Bar	x	33.456 SG	=	Ft Liquid
STD. ATM	x	1.01225	=	Bar	x	0.9879	=	STD. ATM
HP	x	0.7457	=	kW	x	1.341	=	HP

Flow Conversions



Head/Pressure Conversions



Flange Sizes

Normal Bore	Table	Dia. Flange	P.C.D	Bolt Dia.	No. of Bolts	Flange Thickness Grey Cast Iron
1"	D&E	4.50"	3.25"	.50"	4	.50"
1.25"	D&E	4.75"	3.44"	.50"	4	.625"
1.5"	D	6.00"	4.50"	.625"	4	.688"
2"	E	6.00"	4.50"	.625"	4	.750"
50mm	NP16	165mm	125mm	M16	4	20mm
2.5"	D	6.50"	5.00"	.625"	4	.688"
3" 80mm	E	6.50"	5.00"	.625"	4	.750"
	D&E	7.25"	5.75"	.625"	4	.750"
	NP10	200 (7.87)	160 (6.30)	M16	8	21 (.83)
	NP16	200 (7.87)	160 (6.30)	M16	8	21 (.83)
4"	D	8.50"	7.00"	.625"	4	.750"
	E	8.50"	7.00"	.625"	8	8.75"
100mm	NP10	220 (8.66)	180 (7.09)	M16	8	22 (.87)
	NP16	220 (8.66)	180 (7.09)	M16	8	22 (.87)
5"	D	10.00"	8.25"	.625"	8	.813"
	E	10.00"	8.25"	.625"	8	.875"
6"	D	11.00"	9.25"	.625"	8	.813"
	E	11.00"	9.25"	.750"	8	8.75"
150mm	NP10	285 (11.22)	240 (9.49)	M20	8	23 (.91)
	N16	285 (11.22)	240 (9.49)	M20	8	23 (.91)
7"	D	12.00"	10.25"	.625"	8	.875"
	E	12.00"	10.25"	.750"	8	1.00"
8"	D	13.25"	11.50"	.675"	8	.875"
	E	13.25"	11.50"	.750"	8	1.00"
200mm	NP10	340 (12.38)	295(11.61)	M20	8	245 (.96)
	NP16	340 (12.38)	295(11.61)	M20	12	245 (.96)
9"	D	14.50"	12.75"	.625"	8	.875"
	E	14.50"	12.75"	.750"	12	1.00"
10"	D	16.00"	14.00"	.750"	8	1.00"
	E	16.00"	14.00"	.750"	12	1.00"
250mm	NP10	400 (15.75)	350(13.78)	M20	12	26 (1.02)
	NP16	400 (15.75)	355 (13.98)	M25	12	26 (1.02)
12"	D	18.00"	16.00"	.750"	12	1.00"
	E	18.00"	1.00"	.875"	12	1.125"
300mm	NP10	455 (17.91)	400 (15.75)	M20	12	27.5 (1.08)
	NP16	455 (17.91)	410 (16.14)	M25	12	27.5 (1.08)

NP10 and NP16 are for cold water pressure of 10 bar and 16 bar and are the current British Standard. They are unnecessarily heavy for most contractors' pumps.

Case Story - Temporary Over Pumping

A very successful period of production for companies in the area had resulted in increased quantities of industrial effluent being discharged. This effluent, which varied widely in pH, was causing challenges for the established pumping station. Indeed, upon inspection of the station the variation in types of inflow was found to be causing further problems. The lack of additional storm water to assist the system's self-flushing cycles meant both capacity and mix of inflows needed to be addressed. The noise from the old struggling pumping station was disturbing the busy residential area in which it was located.

With this in mind, the client wanted a solution that could upgrade the station while eliminating downtime. The client approached Xylem, who divided the challenge in two stages.

Stage one required the immediate deployment of an over-pumping system into Station A's wet well to resolve the collapse of the existing duty assist system. Such a situation was ideally suited for the Xylem-manufactured Flygt pump. The company's qualified electrical and engineering installation teams were on site quickly to set up a full replacement pumping system. As part of this installation, the pump was connected and commissioned to the control panel. The team ensured the telemetry signals were online for real-time monitoring and alarm notification, and that the new temporary rising main was connected to the discharge point.

The installation was carried out with a full system check to ensure the air relief valves, non-return valves and pump sequencing for automatic starting were correct. With the Xylem submersible rental pump installed in the wet well, the pumping station's operations and noise levels returned to normal.

Stage two of the project concerned a disused 12m diameter chamber that was situated on a small plot of land 300 yards upstream of the existing station, next to a very busy road. Xylem identified this chamber as an ideal location for a temporary pumping station that would allow the existing station to be taken offline and fully refurbished.

The disused well needed to be connected to a new rising main to become viable. Because no site drawings were available, Xylem engineers met with the client onsite to develop a plan and carry out a detailed site survey beforehand.

These calculations showed that thanks to Xylem's readily-available stock of new Flygt pumps, no technical issues would be encountered during installation. However, practical concerns, such as being able to access the site, the absence of a power source and the pipe configurations required, presented challenges.

As a result, a detailed onsite walkthrough was needed during each stage of the installation. Xylem implemented a solution using multiple smaller pumps that came into duty in progressive stages of flow, creating further efficiency savings for the client. This also allowed the company to stage the removal of the overpumping system and rental pumps. These pumps would be powered by secure generators linked to operational telemetry and a diesel supply plan to ensure power continuity.

Refurbishment - The original station was fully refurbished and an offsite-built packaged pumping station was installed as a liner within the old well. Although the original well was slightly smaller in diameter, its capacity was increased by the insertion of the new Flygt pumps. Both orders were placed with Xylem Rental, and it has been a system in use throughout the project. Xylem's 24/7 response centre was permanently linked to the project, so Xylem had full visibility and hard copy record of its progress. This data has also been invaluable for understanding what the network and downstream treatment demands were and continue to be.

Case Story - UV Treatment Project

Xylem was able to quickly overhaul treatment processes at one of the first full-scale membrane bioreactor plants in Europe, which was struggling to meet the area's increasing demand for potable water.

Built and operational in early 1998, the plant is an enclosed, small-scale installation situated in a picturesque village on the edge of a national park. Housed in a stone-faced building in-keeping with the character of the village, the site's effluent discharges into the sea near a designated bathing beach.

Demand on the water treatment works has escalated in the 20 years since installation, necessitating a major increase in plant capacity and treatment process quality. It was vital that potable water remained available and water purification processes would be uninterrupted during this upgrade.

The client engaged Xylem Rental to review the plant and carry out this work, due to its experience supplying containerised treatment plants all over the world. These units have very low power requirements and very high throughput, making them ideal for both potable water and effluent discharge solutions. Crucially, they can also be deployed and connected immediately upon arrival at the site.

Because the plant on this particular project had no final system for pathogen removal, Xylem UV units were also installed. These units removed cryptosporidium, a pathogen that can still be found in drinking water even after early treatment processes.

UV units are one of many portable treatment plant solutions available from Xylem Rental, alongside submerged aerations filters, ozone treatment technology and other aeration systems. The Xylem Group own many famous brands in the world of water and effluent treatment, including Flygt and Lowara, and can manufacture a wide variety of solutions. As such, Xylem Rental can offer water treatment as a complimentary service complementing its multi-depot Pump Rental operation.

Temporary plants are often used to gauge and provide enough time for permanent solutions. These permanent solutions can be designed by Xylem, which can then take on the full MEICA installation of the project in collaboration with civil partners.

On this particular project, Xylem rental engineers delivered the units to site, lifted them onto pre-prepared hardstanding areas and connected inlet and outlet pipework to the Flygt pumps supplying inlet water. Inside the container, the advanced Wedeco programmable logic controller (PLC) ensured the correct dosage of UV light is constantly provided for the flow.

The Wedeco reactor vessel's advanced design assured smooth laminar flow. Sampling points were also provided for full digital measurements of quality, with hard copy records supplied to ensure continued compliance. As a result, the client was able to identify immediate improvements in the treatment works within 24 hours of the container's arrival and installation.

If you have an application that requires an abstraction or discharge licence for water or effluent, then contact us for a review. We can help provide immediate solutions that can be quickly delivered and installed to site, improving site processes with minimal disruption.

Head Office

UK
Private Road No.1
Colwick Nottingham
NG4 2AN
Tel: 0115 940 0111

Ireland
50 Broomhill Close
Airton Road
Tallaght
D24 APP8
Tel: 353 1 452 4444

National Call Centre

0845 707 8012

Email: fgb.rental@xyleminc.com

Web: www.xylem.com/uk

Xylem |'zīl m|

- 1) The tissue in plants that brings water upward from the roots;
- 2) a leading global water technology company.

We're a global team unified in a common purpose: creating advanced technology solutions to the world's water challenges. Developing new technologies that will improve the way water is used, conserved, and re-used in the future is central to our work. Our products and services move, treat, analyze, monitor and return water to the environment, in public utility, industrial, residential and commercial building services settings. Xylem also provides a leading portfolio of smart metering, network technologies and advanced analytics solutions for water, electric and gas utilities. In more than 150 countries, we have strong, long-standing relationships with customers who know us for our powerful combination of leading product brands and applications expertise with a strong focus on developing comprehensive, sustainable solutions.

For more information on how Xylem can help you, go to www.xylem.com



Xylem Water Solutions UK Ltd

Colwick
Nottingham
NG4 2AN

Tel: 0115 940 0111
Fax: 0115 940 0444
Email: fgb.rental@xyleminc.com
www.xylem.com/uk

0845 707 8012

Reg. No: 479504